

■目盛付スチールビームトランメル OS-162 GRADUATED STEEL BEAM TRAMMEL OS-162



● OS-162 寸法表 Dimensions OS-162

品番 Part no.	呼寸法 Nominal size (mm)	ビーム長 Beam length (mm)	巾 Width (mm)	厚 Thickness (mm)	ポイント Point φ (mm)	製品質量 Weight (kg)	定価 Price (円)
162-300	300	390	20	4	6.8 × 70	1.5	40,000
162-500	500	660	30	6	9 × 72	2.5	50,000
162-1000	1000	1165	30	6	9 × 72	4	93,000
162-1500	1500	1665	32	6	9 × 72	6	ご照会ください
162-2000	2000	2165	40	8	12 × 100	12	
162-3000	3000	3165	50	10	12 × 100	21	

■スチールビームトランメル OS-163 STEEL BEAM TRAMMEL OS-163



● OS-163 寸法表 Dimensions OS-163

品番 Part no.	呼寸法 Nominal size (mm)	ビーム長 Beam length (mm)	本体直径 Diameter of the main unit φ (mm)	ポイント Point φ (mm)	製品質量 Weight (kg)	定価 Price (円)
163-500	500	600	25.4	15 × 70	1	30,000
163-1000	1000	1100	25.4	15 × 70	3	36,000
163-1500	1500	1600	25.4	15 × 70	4.5	42,000
163-2000	2000	2100	25.4	15 × 70	6.5	80,000
163-3000	3000	3100	31.8	15 × 70	16	164,000
163-4000	4000	4100	31.8	15 × 70	21	340,000

■サーフェスゲージ(トースカン) OS-164 SURFACE GAUGE OS-164

● OS-164 寸法表 Dimensions OS-164



品番 Part no.		高さ Height (mm)	角台 Square stand				丸台 Round stand			
角台 Square stand	丸台 Round stand		台長×巾×高 Stand length Width Height (mm)	製品質量 Weight (kg)	定価 Price (円)	柱径 Pole diameter φ (mm)	台径×高 Stand diameter Height (mm)	製品質量 Weight (kg)	定価 Price (円)	
164-150S	164-150R	150	70 × 45 × 25	0.7	5,260	8	60 × 36	0.5	5,260	
164-200S	164-200R	200	70 × 45 × 25	1	6,100	8	55 × 29	0.7	6,100	
164-250S	164-250R	250	80 × 55 × 25	1.3	7,360	8	72 × 36	1	7,360	
164-300S	164-300R	300	80 × 55 × 26	1.5	10,100	8	72 × 36	1.2	10,100	
164-350S	164-350R	350	90 × 58 × 27	2.1	16,800	9.5	85 × 34	1.35	16,800	
164-400S	164-400R	400	102 × 72 × 30	2.6	20,000	9.5	110 × 36	1.5	20,000	
164-450S	164-450R	450	102 × 72 × 30	3.6	26,000	13	110 × 36	2	26,000	
164-500S	164-500R	500	130 × 95 × 45	4.5	32,000	13	110 × 36	2.5	32,000	
164-600S	164-600R	600	130 × 95 × 45	8	38,000	13	110 × 36	3	38,000	
164-750S	164-750R	750	165 × 113 × 55	10	70,000	16	140 × 60	5.5	70,000	
164-1000S	164-1000R	1000	210 × 140 × 80	16	100,000	16	165 × 60	8	100,000	
164-1500S	164-1500R	1500	270 × 175 × 100	25	280,000	19	200 × 65	13	280,000	
164-2000S	-	2000	320 × 190 × 100	37	400,000	-	-	-	-	