

表25 : LFK, MLFK, ULFK, UMLFKシリーズ寸法表

スタンダード		ウルトラシリーズ		主 要 寸 法 (mm)		玉 質				基本定格荷重					
標準型 シールなし 両シール付	防錆型 シールなし 両シール付	標準型 両シール付	防錆型 両シール付	d	D	フ ラ ン ジ				量 (kg)	C (N)	Co (N)			
						L	D _f	K	t	D _p	S	数			
LFK6	MLFK6	ULFK6-UU	UMLFK6-UU	6	12	19	28	22	5	20	M3	4	0.023	218	160
LFK6-UU	MLFK6-UU														
LFK8	MLFK8	ULFK8-UU	UMLFK8-UU	8	16	25	32	25	5	24	M3	4	0.039	258	220
LFK8-UU	MLFK8-UU														
LFK8B	MLFK8B	ULFK8B-UU	UMLFK8B-UU	8	15	24	32	25	5	24	M3	4	0.029	258	220
LFK8B-UU	MLFK8B-UU														
LFK10	MLFK10	ULFK10-UU	UMLFK10-UU	10	19	29	39	30	6	29	M4	4	0.061	532	430
LFK10-UU	MLFK10-UU														
LFK12	MLFK12	ULFK12-UU	UMLFK12-UU	12	22	32	42	32	6	32	M4	4	0.081	549	430
LFK12-UU	MLFK12-UU			0 -0.009	0 -0.021										
LFK12B	MLFK12B	ULFK12B-UU	UMLFK12B-UU	12	21	30	42	32	6	32	M4	4	0.070	549	430
LFK12B-UU	MLFK12B-UU														
LFK13	MLFK13	ULFK13-UU	UMLFK13-UU	13	23	32	43	34	6	33	M4	4	0.080	555	440
LFK13-UU	MLFK13-UU														
LFK16	MLFK16	ULFK16-UU	UMLFK16-UU	16	26	36	46	35	6	36	M4	5	0.100	768	650
LFK16-UU	MLFK16-UU														
LFK16B	MLFK16B	ULFK16B-UU	UMLFK16B-UU	16	28	37	48	37	6	38	M4	5	0.109	768	650
LFK16B-UU	MLFK16B-UU														
LFK20	MLFK20	ULFK20-UU	UMLFK20-UU	20	32	42	54	42	8	43	M5	5	0.176	1282	1010
LFK20-UU	MLFK20-UU														
LFK25	MLFK25	ULFK25-UU	UMLFK25-UU	25	40	58	62	50	8	51	M5	6	0.300	2164	1790
LFK25-UU	MLFK25-UU			0 -0.010	0 -0.025										
LFK30	MLFK30	ULFK30-UU	UMLFK30-UU	30	47	64	76	60	10	62	M6	6	0.55	3245	2510
LFK30-UU	MLFK30-UU														
LFK30B	MLFK30B	ULFK30B-UU	UMLFK30B-UU	30	45	64	74	58	10	60	M6	6	0.43	3245	2510
LFK30B-UU	MLFK30B-UU														
LFK35	MLFK35	ULFK35-UU	UMLFK35-UU	35	52	70	82	64	10	67	M6	6	0.59	3521	3090
LFK35-UU	MLFK35-UU														
LFK40	MLFK40	ULFK40-UU	UMLFK40-UU	40	60	80	96	75	13	78	M8	6	1.21	4844	4040
LFK40-UU	MLFK40-UU			0 -0.012	0 -0.030										
LFK50	MLFK50	ULFK50-UU	UMLFK50-UU	50	80	100	116	92	13	98	M8	6	1.99	8272	6430
LFK50-UU	MLFK50-UU														
LFK60	MLFK60	ULFK60-UU	UMLFK60-UU	60	90	110	134	106	18	112	M10	6	3.20	9847	7270
LFK60-UU	MLFK60-UU			0 -0.015	0 -0.035										

* M2シリーズ : 外筒にはOZAK, Mシリーズの防錆処理を施し, ボールはSUJ-2を使用した, より経済的なシリーズです。
(例) M2LFK16-UUと御指定下さい。

呼び番号 U LFK20 -UU -G -4-M5×20

ウルトラ

型番

標準型

M-防錆型

シール

無記号

UU

シールなし

両シール付

グリス

無記号 グリスなし

G 標準グリス

CG クリーングリス


VG 真空グリス

HG 高温グリス

FG 食品グリス

※グリスの性状P40参照

ボール本数-ボルトサイズ



推奨六角穴付ボール

軸径 (d)	六角穴付ボール	
	呼び径	長さ
6.8	M3	10, 12, 16
10~16	M4	12, 16, 20
20.25	M5	16, 20, 25
30.35	M6	20, 25, 30
40.50	M8	25, 30, 35
60	M10	35, 40, 45

※上記以外の長さをご希望の場合は, 別途お問い合わせ下さい。