



表1：LMシリーズ寸法表

軸径 (mm)	スタンダード 標準型 両シール付	主要寸法 (mm)								玉列数	質量 (kg)	基本定格荷重			
		d	D		L		ℓ		w			Do	C (N)	Co (N)	
6	LM6-UU	6	0 -0.009	12	0 -0.011	19	0 -0.2	13.5	0 -0.2	1.1	11.5	4	0.007	218	160
8	LM8-UU	8		15		24		17.5		1.1	14.3	4	0.014	258	220
10	LM10-UU	10		19		29		22		1.3	18.0	4	0.026	532	430
12	LM12-UU	12		21	0 -0.013	30		23		1.3	20.0	4	0.032	549	430
13	LM13-UU	13		23		32		23		1.3	22.0	4	0.040	555	440
16	LM16-UU	16		28		37		26.5		1.6	26.6	5	0.07	768	650
20	LM20-UU	20	0 -0.010	32	0 -0.016	42	0 -0.3	30.5	0 -0.3	1.6	30.3	5	0.09	1282	1010
25	LM25-UU	25		40		59		41		1.85	38.0	6	0.21	2164	1790
30	LM30-UU	30		45		64		44.5		1.85	43.0	6	0.24	3245	2510
35	LM35-UU	35		52		70		49.5		2.1	49.0	6	0.35	3521	3090
40	LM40-UU	40		60	0 -0.019	80		60.5		2.1	57.0	6	0.77	4844	4040
50	LM50-UU	50		80		100		74		2.6	76.5	6	1.43	8272	6430
60	LM60-UU	60	90	0 -0.022	110	85	3.15	86.5	6	2.20	9847	7270			

* 標準品材質：SUJ-2

