



表4：LFKM, MLFKMシリーズ寸法表

スタンダード		主要寸法 (mm)										玉列数	質量 (kg)	基本定格荷重	
標準型 両シール付	防錆型 両シール付	d	D	L	D _r	K	t	D _p	S	C (N)	Co (N)				
LFKM6-UU	MLFKM6-UU	6	12	19	28	22	5	20	M3	4	0.023	218	160		
LFKM8-UU	MLFKM8-UU	8	15	24	32	25	5	24	M3	4	0.029	258	220		
LFKM10-UU	MLFKM10-UU	10	19	29	39	30	6	29	M4	4	0.061	532	430		
LFKM12-UU	MLFKM12-UU	12	21	30	42	32	6	32	M4	4	0.070	549	430		
LFKM13-UU	MLFKM13-UU	13	23	32	43	34	6	33	M4	4	0.080	555	440		
LFKM16-UU	MLFKM16-UU	16	28	37	48	37	6	38	M4	5	0.109	768	650		
LFKM20-UU	MLFKM20-UU	20	32	42	54	42	8	43	M5	5	0.176	1282	1010		
LFKM25-UU	MLFKM25-UU	25	40	58	62	50	8	51	M5	6	0.300	2164	1790		
LFKM30-UU	MLFKM30-UU	30	45	64	74	58	10	60	M6	6	0.43	3245	2510		
LFKM35-UU	MLFKM35-UU	35	52	70	82	64	10	67	M6	6	0.59	3521	3090		
LFKM40-UU	MLFKM40-UU	40	60	80	96	75	13	78	M8	6	1.21	4844	4040		
LFKM50-UU	MLFKM50-UU	50	80	100	116	92	13	98	M8	6	1.99	8272	6430		
LFKM60-UU	MLFKM60-UU	60	90	110	134	106	18	112	M10	6	3.20	9847	7270		

