

Couplers

PACKAGING

- Packing unit: 1 (SBV: 10)



12 631 252

PRODUCTS

Figure	Item-No.	Description 1	Description 2	M 10 x 1	G 1/8"	H	K	D	SBV
	12 002	Hollow/universal coupler	M 10 x 1 female-H+K-nipple	×		×	×		
	12 072	Hollow/universal coupler	G 1/8" female-H+K-nipple		×	×	×		
	12 003	Funnel type coupler-M 10 x 1 female	D-nipple	×				×	
	12 073	Funnel type coupler-G 1/8" female	D-nipple		×			×	
	12 626	Precision coupler-M 10 x 1 female	SW 13 mm-Ø 13 mm	×		×			
	12 726	Precision coupler-G 1/8" female	SW 13 mm-Ø 13 mm		×	×			
	12 150	Precision coupler-M 10 x 1 female	SW 13 mm-Ø 13 mm-SB-package	×		×			×
	12 151	Precision coupler-G 1/8" female	SW 13 mm-Ø 13 mm-SB-package		×	×			×
	12 643	Precision coupler-M 10 x 1 female	SW 13 mm-Ø 15 mm	×		×			
	12 743	Precision coupler-G 1/8" female	SW 13 mm-Ø 15 mm		×	×			
	12 156	Precision coupler-M 10 x 1 female	SW 13 mm-Ø 15 mm-SB-package	×		×			×
	12 157	Precision coupler-G 1/8" female	SW 13 mm-Ø 15 mm-SB-package		×	×			×
	12 631	Hydraulic coupler-M 10 x 1 female	SW 13 mm-Ø 15mm	×		×			
	12 731	Hydraulic coupler-G 1/8" female	SW 13 mm-Ø 15mm		×	×			
	12 152	Hydraulic coupler-M 10 x 1 female	SW 13 mm-Ø 15 mm-SB-package	×		×			
	12 153	Hydraulic coupler-G 1/8" female	SW 13 mm-Ø 15 mm-SB-package		×	×			
	12 642	Hydraulic coupler-M 10 x 1 female	SW 13 mm-Ø 15 mm-with valve	×		×			
	12 631 252	Hydraulic coupler-M 10x1 female	and universal-funnel type-MU-set	×		×	×	×	

Abbreviations

D	for funnel type grease nipples	G	Whitworth Pipe Thread, cylindrical, ISO 228 (DIN 259)
H	for Taper type grease nipples	i	Inside / Female
K	for ball-type grease nipples	M	Metric thread, cylindrical, DIN 13
SBV	Packaging for self-service	SW	Wrench size