


ST56B

Ø56mm Bulb Steady/Flashing Tower Lights



- ST56B** Steady
- ST56B-BZ** Built-in Buzzer Steady
- ST56BF** Steady/Flashing
- ST56BF-BZ** Built-in Buzzer Steady/Flashing



ST56B series

Built-in buzzer output holes formed on the housing of the product.



ST56B Ø56mm Pole Mount, Bulb Steady/Flashing

Model number	Layer	Voltage	Current	Bulb			Certificates	Weight	Color
				Spec	Standard	Parts no#			
ST56B Steady ST56B-BZ Steady /w built-in buzzer ST56BF Steady/ Flashing ST56BF-BZ Steady/ Flashing /w built-in buzzer	1	AC/DC12V	0.925A	12V10W	T16x35 15S	9	CE DC only	0.45kg	● R-Red
		AC/DC24V	0.514A	24V10W	T16x35 15S	10		0.45kg	
		AC110V	0.095A	110V10W	T16x35 15S	12		0.45kg	
		AC220V	0.046A	220V10W	T16x35 15S	13		0.45kg	
	2	AC/DC12V	1.851A	12V10W	T16x35 15S	9		0.53kg	● R-Red
		AC/DC24V	1.028A	24V10W	T16x35 15S	10		0.53kg	● G-Green
		AC110V	0.191A	110V10W	T16x35 15S	12		0.53kg	
		AC220V	0.093A	220V10W	T16x35 15S	13		0.53kg	
	3	AC/DC12V	2.776A	12V10W	T16x35 15S	9		0.61kg	● R-Red
		AC/DC24V	1.543A	24V10W	T16x35 15S	10		0.61kg	● A-Amber
		AC110V	0.286A	110V10W	T16x35 15S	12		0.61kg	● G-Green
		AC220V	0.140A	220V10W	T16x35 15S	13		0.61kg	
4	AC/DC12V	3.702A	12V10W	T16x35 15S	9	0.69kg	● R-Red		
	AC/DC24V	2.057A	24V10W	T16x35 15S	10	0.69kg	● A-Amber		
	AC110V	0.382A	110V10W	T16x35 15S	12	0.69kg	● G-Green		
	AC220V	0.186A	220V10W	T16x35 15S	13	0.69kg	● B-Blue		
5	AC/DC12V	4.627A	12V10W	T16x35 15S	9	0.77kg	● R-Red		
	AC/DC24V	2.572A	24V10W	T16x35 15S	10	0.77kg	● A-Amber		
	AC110V	0.477A	110V10W	T16x35 15S	12	0.77kg	● G-Green		
	AC220V	0.233A	220V10W	T16x35 15S	13	0.77kg	● B-Blue ● W-White		

※ Please refer to page 268 ST56MB type for signal/ audible line current.

Mounting Bracket

Standard	LB18	LW18	QZ18	SZ18	QL18	SL18	QLA18
Steel	Steel	PC	PC	Al	PC	Al	PC

※ Please refer to page 34-39 for detailed dimensions.

Customization

- Customized pole length available
- 2 buzzer sound types : Both prolonged (beep, beep) and staccato (beep, beep, beep) buzzer output available

Ordering Specification

ST56B	-	3	-	24	-	RAG	-	LW18
[Model number]		[Layer]		[Voltage]		[Color]		[Mounting bracket]
<ul style="list-style-type: none"> • ST56B • ST56B-BZ • ST56BF • ST56BF-BZ 		<ul style="list-style-type: none"> • 1-1Layer • 2-2Layers • 3-3Layers • 4-4Layers • 5-5Layers 		<ul style="list-style-type: none"> • 12-DC12V • 24-DC24V • 110-AC110V • 220-AC220V 		<ul style="list-style-type: none"> • R-Red • A-Amber • G-Green • B-Blue • W-White 		<ul style="list-style-type: none"> • None • Standard • Bracket • LB18 • LW18 • QZ18 • SZ18 • QL18 • SL18 • QLA18