

## ■ミリサイズ部品番号及び寸法

サイズ		フリーレーニング			ロックタイプ			MA規格			
径	長さ	Part.No.	自由外径	自由巻数	Part.No.	自由外径	自由巻数	Part.No.	Part.No.	自由外径	自由巻数
			最小/最大			最小/最大				最小/最大	
M2-0.40	1D	05022	2.50 2.70	3.250				05022MA		2.50 2.70	3.250
	1.5D	05023		5.500			05023MA		5.500		
	2D	05024		7.750			05024MA		7.750		
	2.5D	05025		10.125			05025MA		10.125		
	3D	05026		12.375			05026MA		12.375		
M2.2-0.45	1D	05012	2.80 3.00	3.125	15012	2.80 2.95	3.000	05012MA	15012MA	2.80 3.00	3.125
	1.5D	05013		5.375	15013		5.250	05013MA	15013MA		5.375
	2D	05014		7.625	15014		7.550	05014MA	15014MA		7.625
	2.5D	05015		9.875	15015		9.750	05015MA	15015MA		9.875
	3D	05016		12.125	15016		12.000	05016MA	15016MA		12.125
M2.5-0.45	1D	05252	3.10 3.20	3.400	15252	3.25 3.45	3.200	05252MA	15252MA	3.20 3.70	3.375
	1.5D	05253		6.200	15253		5.600	05253MA	15253MA		5.750
	2D	05254		8.950	15254		8.000	05254MA	15254MA		8.125
	2.5D	05255		11.450	15255		10.350	05255MA	15255MA		10.500
	3D	05256		14.050	15256		12.600	05256MA	15256MA		12.750
M2.6-0.45	1D	05262	3.20 3.50	4.400							
	1.5D	05263		7.500							
	2D	05264		8.950							
	2.5D	05265		11.000							
	3D	05265		13.000							
M3-0.50	1D	05032	3.65 3.80	4.150	15032	3.80 3.95	3.600	05032MA	15032MA	3.80 4.35	3.750
	1.5D	05033		6.950	15033		6.220	05033MA	15033MA		6.375
	2D	05034		9.750	15034		8.730	05034MA	15034MA		8.875
	2.5D	05035		12.550	15035		11.220	05035MA	15035MA		11.375
	3D	05036		15.350	15036		13.720	05036MA	15036MA		13.875
M3.5-0.60	1D	05352	4.30 4.36	4.000	15352	4.40 4.55	3.600	05352MA	15352MA	4.40 4.95	3.750
	1.5D	05353		6.750	15353		6.230	05353MA	15353MA		6.375
	2D	05354		9.450	15354		8.600	05354MA	15354MA		8.625
	2.5D	05355		12.150	15355		11.230	05355MA	15355MA		11.375
	3D	05356		14.850	15356		13.600	05356MA	15356MA		13.625
M4-0.70	1D	05042	4.90 5.15	3.850	15042	5.05 5.60	3.625	05042MA	15042MA	5.05 5.60	3.625
	1.5D	05043		6.550	15043		6.125	05043MA	15043MA		6.125
	2D	05044		9.150	15044		8.625	05044MA	15044MA		8.625
	2.5D	05045		11.850	15045		11.125	05045MA	15045MA		11.125
	3D	05046		14.450	15046		13.625	05046MA	15046MA		13.625
M5-0.80	1D	05052	6.00 6.20	4.450	15052	6.25 6.80	4.125	05052MA	15052MA	6.25 6.80	4.125
	1.5D	05053		7.350	15053		6.875	05053MA	15053MA		6.875
	2D	05054		10.250	15054		9.625	05054MA	15054MA		9.625
	2.5D	05055		13.150	15055		12.375	05055MA	15055MA		12.375
	3D	05056		16.050	15056		15.125	05056MA	15056MA		15.125