

■UNCサイズ部品番号及び寸法

サイズ		フリー	ロック		
径	長さ	Part.No.	Part.No.	自由外径 最小/最大	自由巻数
#2-56	1D	03522	13522	2.79 3.02	3.000
	1.5D	03523	13523		5.250
	2D	03524	13524		7.375
	2.5D	03525	13525		9.625
	3D	03526	13526		11.875
#3-48	1D	03532	13532	3.25 3.53	2.875
	1.5D	03533	13533		5.000
	2D	03534	13534		7.250
	2.5D	03535	13535		9.375
	3D	03536	13536		11.500
#4-40	1D	03542	13542	3.65 4.04	2.750
	1.5D	03543	13543		4.750
	2D	03544	13544		6.750
	2.5D	03545	13545		8.875
	3D	03546	13546		10.875
#5-40	1D	03552	13552	4.01 4.39	3.250
	1.5D	03553	13553		5.500
	2D	03554	13554		7.750
	2.5D	03555	13555		10.000
	3D	03556	13556		12.250
#6-32	1D	03562	13562	4.52 4.90	2.750
	1.5D	03563	13563		4.750
	2D	03564	13564		6.875
	2.5D	03565	13565		8.875
	3D	03566	13566		10.750
#8-32	1D	03582	13582	5.20 5.58	3.500
	1.5D	03583	13583		6.000
	2D	03584	13584		8.375
	2.5D	03585	13585		10.750
	3D	03586	13586		13.250
#10-24	1D	03602	13602	6.19 6.57	2.875
	1.5D	03603	13603		5.000
	2D	03604	13604		7.125
	2.5D	03605	13605		9.250
	3D	03606	13606		11.375
#12-24	1D	03622	13622	6.85 7.23	3.500
	1.5D	03623	13623		6.000
	2D	03624	13624		8.375
	2.5D	03625	13625		10.625
	3D	03626	13626		13.125
1/4-20	1D	03042	13042	7.87 8.38	3.375
	1.5D	03043	13043		5.750
	2D	03044	13044		8.000
	2.5D	03045	13045		10.375
	3D	03046	13046		12.750
5/16-18	1D	03052	13052	9.65 10.16	4.000
	1.5D	03053	13053		6.625
	2D	03054	13054		9.250
	2.5D	03055	13055		11.875
	3D	03056	13056		14.625
3/8-16	1D	03062	13062	11.48 11.98	4.375
	1.5D	03063	13063		7.250
	2D	03064	13064		10.000
	2.5D	03065	13065		12.875
	3D	03066	13066		15.750
7/16-14	1D	03072	13072	13.36 13.99	4.500
	1.5D	03073	13073		7.375
	2D	03074	13074		10.250
	2.5D	03075	13075		13.125
	3D	03076	13076		16.125

サイズ		フリー	ロック		
径	長さ	Part.No.	Part.No.	自由外径 最小/最大	自由巻数
1/2-13	1D	03082	13082	15.16 15.79	4.875
	1.5D	03083	13083		7.875
	2D	03084	13084		11.000
	2.5D	03085	13085		14.125
	3D	03086	13086		17.125
9/16-12	1D	03092	13092	16.99 17.62	5.125
	1.5D	03093	13093		8.250
	2D	03094	13094		11.500
	2.5D	03095	13095		14.750
	3D	03096	13096		17.125
5/8-11	1D	03102	13102	18.84 19.48	5.250
	1.5D	03103	13103		8.500
	2D	03104	13104		11.750
	2.5D	03105	13105		15.000
	3D	03106	13106		18.375
11/16-11	1D	03112	13112	20.54 20.98	5.750
	1.5D	03113	13113		9.800
	2D	03114	13114		12.950
	2.5D	03115	13115		16.550
	3D	03116	13116		20.150
3/4-10	1D	03122	13122	22.37 23.01	5.875
	1.5D	03123	13123		9.375
	2D	03124	13124		13.000
	2.5D	03125	13125		16.500
	3D	03126	13126		20.125
7/8-9	1D	03142	13142	25.95 26.72	6.250
	1.5D	03143	13143		10.000
	2D	03144	13144		13.750
	2.5D	03145	13145		17.500
	3D	03146	13146		21.250
1"-8	1D	03162	13162	29.61 30.37	6.375
	1.5D	03163	13163		10.125
	2D	03164	13164		14.000
	2.5D	03165	13165		17.750
	3D	03166	13166		21.625
1-1/8-7	1D	03182	13182	33.40 34.41	6.125
	1.5D	03813	13183		9.875
	2D	03184	13184		13.625
	2.5D	03185	13185		17.500
	3D	03186	13186		21.250
1-1/4-7	1D	03202	13202	36.65 37.66	7.000
	1.5D	03203	13203		11.250
	2D	03204	13204		15.375
	2.5D	03205	13205		19.500
	3D	03206	13206		23.750
1-3/8-6	1D	03222	13222	40.58 41.73	6.500
	1.5D	03223	13223		10.500
	2D	03224	13224		14.375
	2.5D	03225	13225		18.375
	3D	03226	13226		22.250
1-1/2-6	1D	03242	13242	43.86 45.00	7.250
	1.5D	03243	13243		11.500
	2D	03244	13244		15.875
	2.5D	03245	13245		20.125
	3D	03246	13246		24.500