

# PC/SC Type



■ Insert (      Coated Carbide /      Cermet /  Carbide /      SUMIBORON)

● 7° Relief M-Class

CCMT FB		Stock					Dimensions (mm)		
		AC530U	T1500Z	T3000Z	T1000A	T1500A	Inscribed Circle	Thickness	Nose Radius
Cat. No.									
CCMT 060202N-FB		●	●	●	●	●	6.35	2.38	0.2
060204N-FB		●	●	●	●	●			0.4
CCMT 09T304N-FB		●	●	●	●	●	9.525	3.97	0.4
09T308N-FB		●	●	●	●	●			0.8

CCMT LU		Stock								Dimensions (mm)							
		AC810P	AC820P	AC2000	AC630M	AC6030M	AC6040M	AC530U	T1500Z	T3000Z	T2000Z	T1000A	T1500A	T1200A	Inscribed Circle	Thickness	Nose Radius
Cat. No.																	
CCMT 060202N-LU		●	●	●	●	●	●	●	●	●	●	●	●	●	6.35	2.38	0.2
060204N-LU		●	●	●	●	●	●	●	●	●	●	●	●	●			0.4
CCMT 09T304N-LU		●	●	●	●	●	●	●	●	●	●	●	●	●	9.525	3.97	0.4
09T308N-LU		●	●	●	●	●	●	●	●	●	●	●	●	●			0.8

CCMT LUW		Stock					Dimensions (mm)					
		AC810P	AC820P	AC2000	AC630M	T1500Z	T3000Z	T1000A	T1500A	Inscribed Circle	Thickness	Nose Radius
Cat. No.												
CCMT 09T304N-LUW		●	●	▲	●	●	●	●	●	9.525	3.97	0.4
09T308N-LUW		●	●	▲	●	●	●	●	●			0.8

CCMT FP		Stock		Dimensions (mm)		
		T1500A	T1200A	Inscribed Circle	Thickness	Nose Radius
Cat. No.						
CCMT 060202N-FP		●	●	6.35	2.38	0.2
060208N-FP		●	▲			0.8
CCMT 09T302N-FP		●	▲	9.525	3.97	0.2
09T304N-FP		●	▲			0.4

CCMT LB		Stock						Dimensions (mm)				
		AC820P	AC830P	AC6030M	AC6040M	T1500Z	T3000Z	T1000A	T1500A	Inscribed Circle	Thickness	Nose Radius
Cat. No.												
CCMT 060202N-LB		●	●	●	●	●	●	●	●	6.35	2.38	0.2
060204N-LB		●	●	●	●	●	●	●	●			0.4
060208N-LB		●	●	●	●	●	●	●	●			0.8
CCMT 09T302N-LB		●	●	●	●	●	●	●	●	9.525	3.97	0.2
09T304N-LB		●	●	●	●	●	●	●	●			0.4
09T308N-LB		●	●	●	●	●	●	●	●			0.8

CCMT SU		Stock								Dimensions (mm)							
		AC810P	AC820P	AC830P	AC610M	AC630M	AC6030M	AC6040M	AC520U	T1500Z	T3000Z	T1000A	T1500A	Inscribed Circle	Thickness	Nose Radius	
Cat. No.																	
CCMT 060202N-SU		●	●	●	●	●	●	●	●	●	●	●	●	●	6.35	2.38	0.2
060204N-SU		●	●	●	●	●	●	●	●	●	●	●	●	●			0.4
060208N-SU		●	●	●	●	●	●	●	●	●	●	●	●	●			0.8
CCMT 09T302N-SU		●	●	●	●	●	●	●	●	●	●	●	●	●	9.525	3.97	0.2
09T304N-SU		●	●	●	●	●	●	●	●	●	●	●	●	●			0.4
09T308N-SU		●	●	●	●	●	●	●	●	●	●	●	●	●			0.8

CCMT SC		Stock			Dimensions (mm)		
		AC820P	AC2000	A30	Inscribed Circle	Thickness	Nose Radius
Cat. No.							
CCMT 060204N-SC		●	▲	●	6.35	2.38	0.4

● 7° Relief M-Class

CCMT MU		Stock						Dimensions (mm)					
		AC810P	AC820P	AC830P	AC630M	AC6030M	AC405K	AC415K	AC420K	Inscribed Circle	Thickness	Nose Radius	
Cat. No.													
CCMT 09T304N-MU		●	●	●	●	●	●	●	●	●	9.525	3.97	0.4
09T308N-MU		●	●	●	●	●	●	●	●	●			0.8

CCMW		Stock			Dimensions (mm)		
		AC405K	AC415K	AC420K	Inscribed Circle	Thickness	Nose Radius
Cat. No.							
CCMW 060204		●	●	●	6.35	2.38	0.4
CCMW 09T304		●	●	●	9.525	3.97	0.4
09T308		●	●	●			0.8

● 7° Relief G-Class

● Uncoated SUMIBORON One-use Type

(●▲mark: Only 1pc. per package in stock, ●▲mark: Both 1pc. per package and 10pc. per package in stock)

NU-CCGW		Stock					Dimensions (mm)		
		BN1000	BN2000	BN250	BN7000	BN700	Inscribed Circle	Thickness	Nose Radius
Cat. No.									
NU-CCGW 060202		●	●	▲	●	●	6.35	2.38	0.2
060204		●	●	▲	●	●			0.4
060208		●	●	▲	●	●			0.8
060202LT		—	●	—	—	—			0.2
060204LT		—	●	—	—	—			0.4
060208LT		—	●	—	—	—			0.8
060202LS		—	—	▲	—	—			0.2
060204LS		—	—	▲	—	—			0.4
060208LS		—	—	▲	—	—			0.8
060202HS		—	—	—	—	—			0.2
060204HS		—	—	—	—	—	0.4		
NU-CCGW 09T302		●	●	▲	●	●	9.525	3.97	0.2
09T304		●	●	▲	●	●			0.4
09T308		●	●	▲	●	●			0.8
09T302LT		—	●	—	—	—			0.2
09T304LT		—	●	—	—	—			0.4
09T308LT		—	●	—	—	—			0.8
09T302LS		—	—	▲	—	—			0.2
09T304LS		—	—	▲	—	—			0.4
09T308LS		—	—	▲	—	—			0.8
09T302HS		—	—	—	—	—			0.2
09T304HS		—	—	—	—	—	0.4		
09T308HS		—	—	—	—	—	0.8		

\* LT: Small Edge Treatment Type, LS: Continuous Cutting General Type, HS: Strong Edge Type

● Uncoated SUMIBORON One-use Type/Multi-corner

2NU-CCGW		Stock			Dimensions (mm)		
		BN2000	BN7000	BN7500	Inscribed Circle	Thickness	Nose Radius
Cat. No.							
2NU-CCGW 060204		●	●	●	6.35	2.38	0.4
2NU-CCGW 09T304		●	●	●			0.4
09T308		●	●	●			0.8
09T304WG		●	—	—	9.525	3.97	0.4
09T308WG		●	—	—			0.8
09T304WH		●	—	—			0.4
09T308WH		●	—	—			0.8

\* WG/WH: Wiper Insert

● Uncoated SUMIBORON Break Master

2NU-CCGT FV/LV		Stock			Dimensions (mm)		
		BN2000			Inscribed Circle	Thickness	Nose Radius
Cat. No.							
2NU-CCGT 060204N-FV		●			6.35	2.38	0.4
2NU-CCGT 09T304N-FV		●					0.4
09T308N-FV		●					0.8
09T304N-LV		●			9.525	3.97	0.4
09T308N-LV		●					0.8

D Small Product Machining