

## ■C.T.C薄鋼電線管ねじタップ



●SKH

呼び寸法		形状 (各部の寸法)					価格	下穴径 (計算値)
DIA	Pitch	全長	刃長	シャンク径	角長	角厚		
C-15	18	95	45	12	12	9	14.85	
C-19	16	95	45	14	14	11	17.92	
C-25	16	95	45	20	18	15	24.22	
C-31	16	105	45	24	22	19	30.62	
C-39	16	115	45	30	26	23	36.92	
C-51	16	130	55	40	35	32	41.62	
C-63	16							
C-75	16							

## ■C.T.G厚鋼電線管ねじタップ

●SKH

呼び寸法		形状 (各部の寸法)					価格	下穴径 (計算値)
DIA	Pitch	全長	刃長	シャンク径	角長	角厚		
G-16	14	80	35	18	17	14	19.0	
G-22	14	82	35	23	20	17	24.5	
G-28	11	95	45	26	24	21	30.7	
G-36	11	100	45	32	30	26	39.4	
G-42	11	120	45	38	32	29	45.3	
G-54	11	120	50	46	38	35	57.1	
G-70	11	145	65	50	42	38	73.0	
G-82	11	155	65	65	52	50	85.7	
G-92	11	165	68	68	58	54	98.2	
G-104	11	170	70	75	62	58		

## ■Pgコンジットねじタップ (ドイツ規格)

●SKH

呼び寸法		形状 (各部の寸法)					価格	下穴径 (計算値)
DIA	Pitch	全長	刃長	シャンク径	角長	角厚		
Pg-7	20	85	42	9	10	7	11.3	
Pg-9	18	95	45	12.5	13	10	13.9	
Pg-11	18	100	45	14	14	11	17.3	
Pg-13.5	18	105	45	15	15	12	19.1	
Pg-16	18	105	45	17	16	13	21.2	
Pg-21	16	105	45	21	20	17	26.8	
Pg-29	16	115	45	28	24	21	35.3	
Pg-36	16	125	45	38	32	29	45.5	
Pg-42	16	135	55	44	38	35	52.5	
Pg-48	16	135	55	46	38	35	57.8	