

極重荷重
극중하중
EXTRA HEAVY LOAD



하중 荷重 ±10%
직각도 直角度 2° 以下
자유장 自由長 50m/m 以下 ±0.5m/m
55m/m 以上 ± 1%

呼稱 호 칭 Model	外徑 외경(mm) Outer Dia.	內徑 내경(mm) Inner Dia.	自由長 자유장(mm) Free length	定數 정수(kgf/mm) spring constant	30万 (0.3million)		50万 (0.5 million)		100万 (1 million)	
					變形量 변형량(mm) Deflection	荷重 하중(kgf) Load	變形量 변형량(mm) Deflection	荷重 하중(kgf) Load	變形量 변형량(mm) Deflection	荷重 하중(kgf) Load

SB 8×10	8	4	10	16.94	2.0	35	1.8	31	1.6	26
15			15	11.30	3.0		2.7		2.4	
20			20	8.47	4.0		3.6		3.2	
25			25	6.78	5.0		4.5		4.0	
30			30	5.65	6.0		5.4		4.8	
35			35	4.84	7.0		6.3		5.6	
40			40	4.24	8.0		7.2		6.4	
45			45	3.77	9.0		8.1		7.2	
50			50	3.39	10.0		9.0		8.0	
55			55	3.08	11.0		9.9		8.8	
60			60	2.82	12.0		10.8		9.6	
65			65	2.61	13.0		11.7		10.4	
70			70	2.42	14.0		12.6		11.2	
75			75	2.26	15.0		13.5		12.0	
80			80	2.12	16.0		14.4		12.8	
90			90	1.88	18.0		16.2		14.4	
SB 10×10	10	5	10	22.78	2.0	45	1.8	41	1.6	36
15			15	15.19	3.0		2.7		2.4	
20			20	11.25	4.0		3.6		3.2	
25			25	9.00	5.0		4.5		4.0	
30			30	7.50	6.0		5.4		4.8	
35			35	6.43	7.0		6.3		5.6	
40			40	5.63	8.0		7.2		6.4	
45			45	5.00	9.0		8.1		7.2	
50			50	4.50	10.0		9.0		8.0	
55			55	4.09	11.0		9.9		8.8	
60			60	3.75	12.0		10.8		9.6	
65			65	3.47	13.0		11.7		10.4	
70			70	3.21	14.0		12.6		11.2	
75			75	3.00	15.0		13.5		12.0	
80			80	2.82	16.0		14.4		12.8	
90			90	2.50	18.0		16.2		14.4	
100	100	2.25	20.0	18.0	16.0					