










TP5000 Series

Threaded | MIR Wheel | 70Kg - 110Kg



Model Descriptions

									
			inch(mm)	inch(mm)			kg	mm	mm
TP5030-2*-MIR TG			3" (76)		Rubber / Plastic	Ball	70	104	78
TP5040-2*-MIR TG			4" (102)	1 1/4" (32)	Rubber / Plastic	Ball	100	129	89
TP5050-2*-MIR TG			5" (127)		Rubber / Plastic	Ball	110	156	101

Specification

Part	Component	Remark
Swivel	Threaded Stem	S10C
	Cup	2.6t PO Steel
	Body	2.6t PO Steel
Wheel	MIR TG	TPR Tread on Plastic Center with bearing
	Shaft	3/8" Bolt & Lock Nut

Options

Code	Description
TLB	Top Lock Brake
CR	Chrome Plating
TG	Thread Guard
LN	Lower Nut
SWB	Swivel Lock & Wheel Brake

Fastening Option

Type	Code	Size(mm)
Threaded Stem	21	1/2" x 12 TPI x 25mm
	23	5/8" x 11 TPI x 27mm
	24	5/8" x 11 TPI x 16mm