

Deluxe Total Lock Caster

TP8700 Series / Capacity up to 240 Lbs.



Features

- **Finish:** Chrome Plated Finish Standard
- **Swivel:** Double ball swivel raceway
- **SWB Brake:** Total Lock - Swivel and Wheel
- **Axle & Nut:** 5/16" diameter Axle with lock nut

Applications

- Hospital Equipment
- Medical Equipment
- Institutional Equipment
- Movie Equipment
- Food Service

Caster Options

- SWB: Swivel Wheel Brake



Wheel Diameter	Tread Width	Wheel Type	Swivel Number	Rigid Number	Wheel Bearing	Load Capacity	Overall Height	Swivel Radius
3	1-1/4	Mirage (TPR)	TP8730-**-MIR-TG-SWB	TP8730R-01-MIR-TG	Precision Ball	110	4-1/2	3-1/16
		Hi Elastic Polyurethane	TP8730-**-PLE-SWB	TP8730R-01-PLY	Precision Ball	125		
4	1-1/4	Mirage (TPR)	TP8740-**-MIR-TG-SWB	TP8740R-01-MIR-TG	Precision Ball	150	5-1/2	3-3/8
		Hi Elastic Polyurethane	TP8740-**-PLY-SWB	TP8740R-01-PLY	Ball	150		
		Hi Elastic Polyurethane	TP8740-**-PLE-SWB	TP8740R-01-PLY	Precision Ball	165		
5	1-1/4	Mirage (TPR)	TP8750-**-MIR-TG-SWB	TP8750R-01-MIR-TG	Precision Ball	200	6-1/2	3-5/8
		Hi Elastic Polyurethane	TP8750-**-PLY-SWB	TP8750R-01-PLY	Ball	200		
		Hi Elastic Polyurethane	TP8750-**-PLE-SWB	TP8750R-01-PLY	Precision Ball	175		
6	1-1/4	Mirage (TPR)	TP8760-**-MIR-TG-SWB	TP8760R-01-MIR-TG	Precision Ball	240	7-1/2	4-1/8

Fastenings

TYPE	CODE	SIZE(Inch)	
Stemless	00	1/2" hole -- add your own stem	
Top Plate	01	Overall Size	2-3/8 x 3-5/8
		Bolt Hole Spacing	1-3/4 x 2-15/16
		Attaching Bolt Size	5/16
Grip Ring Stem	11	7/16 x 1-7/16	
	12	7/16 x 2	
Threaded Stem	21	1/2 - 13 x 1-1/2	
	23	5/8 - 11 x 1" with hex nut base	
Round Plain Stem	31	1" x 2-1/4 with 2 holes 9/16 and 1-1/4 up from base	
	33	1-1/8 x 2-1/4 with 2 holes 9/16 and 1-1/4 up from base	

Replace -**- in part number with appropriate fastening code.



TP8700 Series