

# FASTENING

FASTENING

## IMPACT WRENCH COMPOSITE

**Bolt Capacity 16mm**

- Lightweight. ● Reverse lever.

### SP-7143

1/2" Retainer ring

4 Regulator dial



**Bolt Capacity 16mm**

- Lightweight. ● Reverse lever.

### SP-7143DX

1/2" Retainer ring

4 Regulator lever



**Bolt Capacity 14mm**

- Lightweight. ● Reverse lever.

### SP-7142S

3/8" Retainer ring

4 Regulator dial



**Bolt Capacity 16mm**

- Lightweight. ● Reverse lever.

### SP-7140

1/2" Retainer ring

4 Regulator dial



**Bolt Capacity 25mm**

- One hand reverse button (patented).

### SP-7150A-V8

3/4" Retainer ring

4 Regulator dial



**Bolt Capacity 25mm**

- One hand reverse button (patented).

### SP-7151AL-V8

3/4" Retainer ring

4 Regulator dial



Option

- #26061990 Support grip

**Bolt Capacity 32mm**

- Lightweight. ● One hand reverse button (patented).

### SP-7191A-V8

1" Retainer ring

4 Regulator dial



Option

- #26061990 Support grip

DRILLING

SANDING

GRINDING

CUTTING

HAMMERING

BEVELER

EDP	Model No.	Sq. Drive (inch)	Hammer	Torque Range (N·m)	Free Speed (min <sup>-1</sup> )	Overall Length (mm)	Air Consumption (ml/min)	Hose Coupling	Net Weight (kg)	JAN (4545695)
370021	SP-7143	1/2"	Dyna Jaw clutch	50~280	8000	180	0.6	1/4"NPT	1.36	000165
370028	SP-7143DX	1/2"	Dyna Jaw clutch	50~320	8000	173	0.6	1/4"NPT	1.36	001629
370187	SP-7142S	3/8"	Twin Dog clutch	50~270	7500	163	0.4	1/4"NPT	1.4	001049
370032	SP-7140	1/2"	Twin dog clutch	50~450	5800	185	0.6	1/4"NPT	2.1	000158
370029	SP-7150A-V8	3/4"	Twin Dog clutch	300~1000	4300	237	1.3	3/8"NPT	3.7	002572
370041	SP-7151AL-V8	3/4"	Pin clutch	270~900	4300	320	0.8	3/8"NPT	4.5	002503
370042	SP-7191A-V8	1"	Pin clutch	280~1100	4300	320	0.8	1/2"NPT	4.65	002602

Air pressure: 0.62 MPa Air hose inner dia.: 9.5 mm Rear exhaust Air connector included