


ユニオン

UNION (SFW Type)



UNIT : mm

型番	チューブ外径	最小穴径	差込深さ	組込長さ	本体長さ	六角対辺	
TYPE NO.	TUBE O.D.	MIN. BORE	DEPTH	APPROX	BODY	WIDTH ACROSS HEX	
	T	A	B	C	D	E	F

[ミリサイズチューブ用]

SFW- 2M- 0	2	1.5	9.5	28.7	19.7	8	8
SFW- 3M- 0	3	2.4	13	35.9	22.5	12	12
SFW- 4M- 0	4	3	13.7	37.9	24.5	12	12
SFW- 5M- 0	5	4	13.7	40.4	27	14	14
SFW- 6M- 0	6	4.5	15.6	44.2	29	14	14
SFW- 8M- 0	8	6	16.4	45.9	30.5	14	15.8
SFW-10M- 0	10	8	17.2	47.9	32.5	17.4	19
SFW-12M- 0	12	10	23.1	53.3	32.5	22	22
SFW-14M- 0	14	11	23.3	52.5	31.3	22	24
SFW-15M- 0	15	12	23.3	53.5	32.3	24	27
SFW-16M- 0	16	13	24.9	53.5	32.3	24	27
SFW-18M- 0	18	15	24.9	54.5	33.3	27	30
SFW-20M- 0	20	17	24.9	55	33.8	30	32
SFW-22M- 0	22	19	26.6	55	33.8	30	32
SFW-25M- 0	25	22	31.7	65.8	40.4	35	38

[インチサイズチューブ用] チューブ外径の () 内はインチ表示

SFW- 1C- 0	1.58(1/16")	1.4	8.3	25.3	17.7	8	8
SFW- 2C- 0	3.17(1/8")	2.4	13	35.9	22.5	12	12
SFW- 3C- 0	4.76(3/16")	3.2	13.7	37.9	24.5	12	14
SFW- 4C- 0	6.35(1/4")	4.8	15.6	44.2	29	14	14
SFW- 6C- 0	9.52(3/8")	7.5	17.2	47.9	32.5	15.8	17.4
SFW- 8C- 0	12.7(1/2")	10.4	23.1	53.3	32.5	22	22
SFW-10C- 0	15.88(5/8")	13	24.9	53.5	32.3	24	27
SFW-12C- 0	19.05(3/4")	16	24.9	54.5	33.3	27	30
SFW-14C- 0	22.23(7/8")	19.2	26.6	55	33.8	30	32
SFW-16C- 0	25.4(1")	22.3	31.7	65.8	40.4	35	38

[鋼管サイズパイプ用] チューブ外径の () 内は鋼管サイズ表示

SFW- 6A- 0	10.5(6A)	8	17.4	46.6	30.8	19	22
SFW- 8A- 0	13.8(8A)	10.6	23.3	52.5	31.3	22	24
SFW-10A- 0	17.3(10A)	14.5	24.9	54.5	33.3	27	30
SFW-15A- 0	21.7(15A)	18.5	26.6	55	33.8	30	32

◎製品改良のため、形状及び寸法は、予告無く変更することがありますので、あらかじめご了承下さい。

豆知識 ④ JISとANSI配管の外径比較表

呼び系		外径		
		JIS	ANSI	
B	A	mm	mm	インチ
1/8	6	10.5	10.3	0.405
1/4	8	13.8	13.7	0.540
3/8	10	17.3	17.1	0.675
1/2	15	21.7	21.3	0.840
3/4	20	27.2	26.7	1.050
1	25	34.0	33.4	1.315