

Stainless Steel Castors –Medium duty type–

RoHS compliant products.

POINT

- Brackets (including balls in swivel head) are made of **stainless steel. (SUS304)**
- **Stainless steel needle bearing** is used for wheels with stainless steel wheel center and POTH.
- Smooth swiveling thanks to **double bearing** in the swivel head with dust shield for balls.
- Antibacterial polyurethane wheel SWUW for sanitary facilities.
- Antistatic polyurethane wheel SEUW for clean room.
- SISIKU's unique point - **Box style wheel.**
(Available with SW, SUW, SWUW and SEUW wheels)



Stainless steel needle bearing



Swivel with stopper
SUNJB-150SW

USE EXAMPLE

- For fisheries, foods industry, kitchen equipment and food processing machines.
- For carriers in market and super market.
- For harbor facilities.
- For chemical industry.
- For carriers in hospital and restaurant.
- For carriers in clean room.

◎We'll accept your custom-order. Please feel free to contact us.
(Use "Specification Form for Custom-designed castor" at the end of this catalog.)

◎Please feel free to ask about the product weight for each item.

Options

Swivel with trailing pedal stopper

Double stopper provides locking on swivel head and wheel simultaneously.



SUNJWB-150SW

SUNJ Swivel castors



SUNJ-75 (available with SW, SUW and PO)

SUNJ-100

SUNJ-125

SUNJ-150

SUNJ-200 (available with POTH and PO)

SUNJB Swivel with stopper



SUNJB-100 (available with other than PO and MC)

SUNJB-125 (available with other than PO and MC)

SUNJB-150 (available with other than PO and MC)

SUNJ-SJ Threaded stem fitting



SUNJ-SJ-100

SUNJ-SJ-125

SUNJB-SJ Threaded stem fitting with stopper



SUNJB-SJ-100 (available with other than PO and MC)

SUNJB-SJ-125 (available with other than PO and MC)

SUNK Fixed castors



SUNK-75 (available with SW, SUW and PO)

SUNK-100

SUNK-125

SUNK-150

SUNK-200 (available with POTH and PO)

WHEELS NBS ...Stainless steel needle bearing OL ...Oilless bushing

See P.62 to P.71 for detailed description.



→P.69

SW (SBR)

NBS



→P.69

SUW (UR)

NBS



→P.69

SWUW
(Antibacterial UR/White)

NBS



→P.68

SEUW (Antistatic UR)

NBS



→P.67

POTH (UR)

NBS



→P.65

MC (Monomer cast nylon)

NBS

NB φ75: without bearing

Volume resistance 10⁸~10⁹Ω·cm

*For reference only, not guaranteed.

(Wheel center: Nylon 6)

<Made in Germany>

NB With stopper type: not available