


組ヤスリ DIE SINKER'S-ASSORTED FILES

目の粗さ識別 ● 荒目：赤 ● 中目：緑
 エンドキャップ付 ● 細目：黄 ● 油目：黒

■ Orange colored HANDLE (vinyl chloride) with "END-CAP."



規格表 STANDARD TABLE

TYPE	DIMENSION		セット SET	平 HAND	半丸 HALF ROUND	丸 ROUND	角 SQUARE	三角 TRIANGULAR	シノギ TRAPEZOID
	L	ℓ		W × T	W × T	φ W	W	W	W × T
105 5本組 5-PCS	215L	110 ℓ	—	11 × 3.5	12 × 3.8	φ 5.5	5.5	9.0	(12) × (3.5)
	kg-25pcs		1.38	1.48	1.43	1.13	1.30	1.44	1.50
	No./1set		5(each 1)	5	5	5	5	5	(5)
	ITEM No.		ST 005 **	HI 005 **	HA 005 **	MA 005 **	KA 005 **	SA 005 **	SI 005 **
108 8本組 8-PCS	200L	100 ℓ	—	9 × 3.0	9.5 × 3.0	φ 4.3	4.3	7.5	9.5 × 3.0
	kg-40pcs		1.51	1.54	1.62	1.06	1.24	1.62	1.64
	No./1set		8(each 1)	8	8	8	8	8	8
	ITEM No.		ST 008 **	HI 008 **	HA 008 **	MA 008 **	KA 008 **	SA 008 **	SI 008 **
110 10本組 10-PCS	185L	85 ℓ	—	7 × 2.5	7.3 × 2.5	φ 3.2	3.2	6.0	7.3 × 2.5
	kg-50pcs		1.22	1.37	1.27	0.73	0.79	1.37	1.30
	No./1set		10(each 1)	10	10	10	10	10	10
	ITEM No.		ST 010 **	HI 010 **	HA 010 **	MA 010 **	KA 010 **	SA 010 **	SI 010 **
112 12本組 12-PCS	170L	70 ℓ	—	4 × 2.0	4.2 × 2.0	φ 2.5	2.5	4.0	4.2 × 2.0
	kg-60pcs		0.72	0.78	0.75	0.59	0.60	0.70	0.78
	No./1set		12(each 1)	12	12	12	12	12	12
	ITEM No.		ST 012 **	HI 012 **	HA 012 **	MA 012 **	KA 012 **	SA 012 **	SI 012 **

ITEM No. ** assorted

	荒目 Bastard	中目 Second	細目 Smooth	油目 Dead Smooth
複目W-cut	01	02	03	04
単目S-cut	11	12	13	—

〈ITEM No.例〉

組ヤスリ5本組平中目：HI 00502

〈ITEM No.ex〉

5-PCS HAND Second：HI 00502

目の粗さ表 CUTTING No. TABLE

TYPE	No. 1cm ±10% allowance			
	荒目 Bastard	中目 Second	細目 Smooth	油目 Dead Smooth
5本組 5-PCS	13	17	27	40
8本組 8-PCS	15	20	30	42
10本組 10-PCS	17	23	32	44
12本組 12-PCS	20	26	35	50