





HIT SERIES

HIT dimensions

• CAD data is downloadable from our website.




HIT□-□-13



A cross-section

HIT□-□-18



A cross-section

Color Type

Color code	Top-Bottom cover	Front-Rear panel	Side plate
SS	Silver	Silver	Silver
BB	Black	Black	Black

Part no. / Dimensions

• Please suffix color code at the end of part number □□ when ordering HIT series.

Part no.	W	H	D	a	b	c	d	Weight (g)
HIT 9-2-13□□	89	20	130	8	3.6	81	118.6	183
HIT 9-4-13□□	89	40	130	8	3.6	81	118.6	255
HIT13-3-13□□	130	30	130	8	3.6	122	118.6	289
HIT13-5-13□□	130	50	130	8	3.6	122	118.6	370
HIT18-4-13□□	180	40	130	8	3.6	172	118.6	414
HIT18-6-13□□	180	60	130	8	3.6	172	118.6	503
HIT13-3-18□□	128	30	180	12	3.6	115.5	168	411
HIT13-5-18□□	128	50	180	12	3.6	115.5	168	535
HIT17-4-18□□	174	40	180	12	3.6	161.5	168	578
HIT17-6-18□□	174	60	180	12	3.6	161.5	168	719
HIT23-5-18□□	228	50	180	12	3.6	215.5	168	772
HIT23-7-18□□	228	70	180	12	3.6	215.5	168	928