

Components

• Please refer to P188 for detailed dimensions of rack mounting bracket (MSM · MZ series).

Ref. #	Part name	Pcs	Material	Color / Finish
1	Front panel	1	Aluminium t2.0	Silver · Black anodized / Hair line finish
-	Rear panel	1	Aluminium t2.0	Silver · Black anodized
3	Side frame	2	Aluminium extrusion	Gray · Black painted
4	Front frame	2	Aluminium extrusion	Gray · Black painted
-	Rear frame	2	Aluminium extrusion	Silver anodized
6	Top cover	1	Steel t1.0	Light gray · Black painted
7	Bottom cover	1	Steel t1.0	Light gray · Black painted
8	Corner block	2	Die-cast Aluminium	Gray · Black painted
9	Rear feet	2	ABS (UL94V-0)	Gray · Black
10	Rubber feet	4	Polyurethane	Black
11	Rack mounting bracket	2	Aluminium extrusion	Gray · Black painted
-	Screw	1 set	Steel M4, M5	Black · Normal trivalent chromate

Accessories (Optional parts)



Color Type

Color code	Panel	Frame	Cover
G	Silver	Gray	Light gray
B	Black	Black	Black
BS	Silver	Black	Black

Part no. / Dimensions

Part no.	H	W	D	Weight (kg)
MSR 88-43-23□	88	430	230	3.1
MSR 88-43-28□	88	430	280	3.5
MSR 88-43-35□	88	430	350	4.2
MSR 88-43-45□	88	430	450	5.1
MSR 133-43-23□	132.5	430	230	3.6
MSR 133-43-28□	132.5	430	280	4.1
MSR 133-43-35□	132.5	430	350	4.8
MSR 133-43-45□	132.5	430	450	5.8
MSR 177-43-23□	177	430	230	4.3
MSR 177-43-28□	177	430	280	4.9
MSR 177-43-35□	177	430	350	5.7
MSR 177-43-45□	177	430	450	6.9
MSR 222-43-23□	221.5	430	230	4.7
MSR 222-43-28□	221.5	430	280	5.3
MSR 222-43-35□	221.5	430	350	6.2
MSR 222-43-45□	221.5	430	450	7.5

• Please suffix color code at the end of part number □ when ordering MSR series.