

SPCP SERIES

SPCP IP67 POLYCARBONATE ENCLOSURE



■ Technical data ■

IP66/67

Operating temperature -20°C~+75°C

Maximum torque 1N·m ~ 1.5N·m
(10kgf·cm ~ 15kgf·cm)



FEATURE

- IP66/67 rated waterproof plastic enclosure.
- Body and cover are made of glass fiber filled polycarbonate in light gray, and have a excellent heat-resistance.
- Available in 28 sizes, and selectable from 2 type of appearance covers of light grays or transparence.
- Applicable in many field such as FA, network communication, and so on.
- Mountable on a wall by using the holes for fastening a cover.

Components

Ref. #	Part name	Pcs	Material	Color / Finish
1	Cover	1	Polycarbonate UL94V-2	White gray · Transparence
2	Body	1	Glass fiber filled polycarbonate UL94V-0	White gray
3	Gasket	1	Polyurethane	Black
4	Cover screw	4	Polyamide	White gray
5	Tapping screw	4	Steel	Zinc plated