

Slim Jaws or Wide Jaws?

Choose the 265, 270 or 275 for working in tight areas where a narrow jaw will fit.

The 293 and 296 offer a wider jaw for electrical and industrial applications.



	265	270	275	293	296
Basic DC Accuracy	0.50%	0.50%	0.50%	0.75%	0.50%
DC Voltage	600 V	600 V	600 V	600 V	600V
AC Voltage	600 V	600 V	600 V	600 V	600V
AC/DC Current (Jaw)	400 AC Only	400 AC Only	400 A AC & DC	700A AC Only	700A AC & DC
DC Microamps (Test Leads)		400uA	1100uA		
Resistance	40 M	40 M	110 M	40 K	40K
Frequency	400 MHz	400 MHz	110 MHz	10 KHz	10 KHz
Capacitance	4,000 uF	4,000 uF	4,000 uF		
Temperature		1,000 F	1,000 F		
Continuity	Y	Y	Y	Y	Y
True RMS			Y	Y	Y
Counts	4,000	4,000	11,000	4,000	4,000
Auto Ranging	Y	Y	Y	Y	Y
Manual Ranging	Y	Y	Y	Y	Y
In-Rush Current Capture		Y	Y		
Peak Hold		Y	Y	Y	Y
Min/Max/Record		Y	Y	Y	Y
Data Hold	Y	Y	y	Y	Y
Non-Contact Voltage Detection		Y	Y		
Auto Power Off	Y	Y	Y	Y	Y
cULus	61010-1	61010-1	61010-1	3111-1	3111-1
CAT II	1,000V	1,000 V	1,000 V	1,000V	1,000V
CAT III	600V	600 V	600 V	600V	600V



Pocket-Size, Safety Volt Testers

Determine the presence or absence of AC voltage without disconnecting the system in question.

- No switch required, always 'on' ready for use
- Uses 2 AAA batteries (included)
- UL listed, lifetime warranty

Model 40 (low voltage):

Red glow indicates presence of 24-90 V.

Model 50:

Audible buzzer and visual alarm, red glow indicates presence of 50-1,000 V.

183aC3 HVAC DMM and Clamp Meter Kit

Troubleshoot ECMs & VFDs. Test flame sensors, check capacitors, measure temperature rise.

Kit includes: 183a DMM, 265 Clamp-On, A106 adapter, GK13M general purpose probe, A085 test lead alligator clips, A040 test lead, A901CP case.

Optional A108 Data Logging Software & Interface Cable allow you to view what you see on your multimeter display on your computer screen.

