

Prices displayed include 8% tax.

TRUSCO **Stock 38,650 Items**

## Hexagon Sarae Nut Die Set for Pipe Tap (PT thread)



THDT-PTSET

- Features** • A set of taper pipe tap and hexagon sarae nut die (PT thread) that can be used with an adjustable wrench.
- Specs** • Tap Machining Thread: Taper Thread  
• Number of tap bit thread: 1.5 ridges  
• Die: For repairing PT (taper) ridge
- Materials** • Tap and Die: Low-Alloy Steel (SKS)  
• Case: Steel
- Origin** • Japan

**Warning**

• Cannot be used for stainless steel screw. Hexagon sarae nut die, unlike round die, does not have adjustment screw to adjust size. Therefore, hexagon sarae nut die may not fit depending on the screw precision.

Order Unit: 1 Set

(Price revision date: Jan, 2018) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per set)	MSRP (per set)	Q'ty Per Set (piece)	SPQ (set)	Weight (kg/set)
768-1704	THDT-PTSET	¥77,274	¥95,400	12	1	2

Contact us: 0120-509-849 <http://www.orange-book.com/>

Set Contents			
Item Name	Item No.	Item Name	Item No.
Tap (1/8 to 28)	T-KN-PT1/8	Sarae Nut Die (1/8 to 28)	TD6-1/8 PT28
Tap (1/4 to 19)	T-KN-PT1/4	Sarae Nut Die (1/4 to 19)	TD6-1/4 PT19
Tap (3/8 to 19)	T-KN-PT3/8	Sarae Nut Die (3/8 to 19)	TD6-3/8 PT19
Tap (1/2 to 14)	T-KN-PT1/2	Sarae Nut Die (1/2 to 14)	TD6-1/2 PT14
Tap (3/4 to 14)	T-KN-PT3/4	Sarae Nut Die (3/4 to 14)	TD6-3/4 PT14
Tap (1 to 11)	T-KN-PT1	Sarae Nut Die (1 to 11)	TD6-1 PT11

Spiral Fluted Taps

Point Taps

Roll Taps

Hand Taps

Hexagonal Shank Tapping Drills

TRUSCO **Stock 38,650 Items**

## Hexagon Sarae Nut Die Set for Pipe Tap (PS thread)



THDT-PSSET

- Features** • A set of taper pipe tap and hexagon sarae nut die (PS thread) that can be used with an adjustable wrench.
- Specs** • Tap Machining Thread: Parallel Thread  
• Number of tap bit thread: 4.5 ridges  
• Die: For repairing PS (straight) ridge
- Materials** • Tap and Die: Low-Alloy Steel (SKS)  
• Case: Steel
- Origin** • Japan

**Warning**

• Cannot be used for stainless steel screw. Hexagon sarae nut die, unlike round die, does not have adjustment screw to adjust size. Therefore, hexagon sarae nut die may not fit depending on the screw precision.

Order Unit: 1 Set

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per set)	MSRP (per set)	Q'ty Per Set (piece)	SPQ (set)	Weight (kg/set)
858-7619	THDT-PSSET	¥77,266	¥95,390	12	1	2

Contact us: 0120-509-849 <http://www.orange-book.com/>

Set Contents			
Item Name	Item No.	Item Name	Item No.
Tap (1/8 to 28)	T-KN-PS1/8	Sarae Nut Die (1/8 to 28)	TD6-1/8 PS28
Tap (1/4 to 19)	T-KN-PS1/4	Sarae Nut Die (1/4 to 19)	TD6-1/4 PS19
Tap (3/8 to 19)	T-KN-PS3/8	Sarae Nut Die (3/8 to 19)	TD6-3/8 PS19
Tap (1/2 to 14)	T-KN-PS1/2	Sarae Nut Die (1/2 to 14)	TD6-1/2 PS14
Tap (3/4 to 14)	T-KN-PS3/4	Sarae Nut Die (3/4 to 14)	TD6-3/4 PS14
Tap (1 to 11)	T-KN-PS1	Sarae Nut Die (1 to 11)	TD6-1 PS11

Tap Holders

Taps for Pipe

Thread Mills for Machining Center

Dies

Thread Repair Tools

Tap and Bolt Burr Removing Tools

Screw

TRUSCO **Stock 38,650 Items**

## Hexagon Sarae Nut Die Set for Pipe Tap (PF thread)



THDT-PFSET

- Features** • A set of parallel pipe tap and hexagon sarae nut die (PF thread) that can be used with an adjustable wrench.
- Specs** • Tap Machining Thread: Parallel Thread  
• Number of tap bit thread: 4.5 ridges  
• Die: For repairing PF (straight) ridge
- Materials** • Tap and Die: Low-Alloy Steel (SKS)  
• Case: Steel
- Origin** • Japan

**Warning**

• Cannot be used for stainless steel screw. Hexagon sarae nut die, unlike round die, does not have adjustment screw to adjust size. Therefore, hexagon sarae nut die may not fit depending on the screw precision.

Order Unit: 1 Set

(Price revision date: Jan, 2018) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per set)	MSRP (per set)	Q'ty Per Set (piece)	SPQ (set)	Weight (kg/set)
768-1691	THDT-PFSET	¥77,274	¥95,400	12	1	2

Contact us: 0120-509-849 <http://www.orange-book.com/>

Set Contents			
Item Name	Item No.	Item Name	Item No.
Tap (1/8 to 28)	T-KN-PF1/8	Sarae Nut Die (1/8 to 28)	TD6-1/8 PF28
Tap (1/4 to 19)	T-KN-PF1/4	Sarae Nut Die (1/4 to 19)	TD6-1/4 PF19
Tap (3/8 to 19)	T-KN-PF3/8	Sarae Nut Die (3/8 to 19)	TD6-3/8 PF19
Tap (1/2 to 14)	T-KN-PF1/2	Sarae Nut Die (1/2 to 14)	TD6-1/2 PF14
Tap (3/4 to 14)	T-KN-PF3/4	Sarae Nut Die (3/4 to 14)	TD6-3/4 PF14
Tap (1 to 11)	T-KN-PF1	Sarae Nut Die (1 to 11)	TD6-1 PF11

For other cutting tools, see p. 1-805 to 1006