

Prices displayed include 8% tax.

TRUSCO Stock 38,650 Items

Hexagon Sarae Nut Die (unified coarse thread)



2 side width dimension



TD6-1UNC8
THD-UNCSET (set item)



Warning
•Hexagon sarae nut die, unlike round die, does not have adjustment screw to adjust size. Therefore, hexagon sarae nut die may not fit depending on the screw precision.
•Cannot be used for stainless steel screw.

Features •Used to clean bolt and screw. •You can work with an adjustable wrench.
•Substitute for round die when repairing ridge. Use •For repairing UNC (unified coarse) ridge
Materials •Low-Alloy Steel (SKS) Origin •Japan

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nominal Dimension	Number of Ridges	Thickness (mm)	2 Side Width Dimension (mm)	SPQ (piece)	Weight (g)
432-9368	TD6-1/4UNC20	¥2,098	¥2,590	1/4	20	6.3	15.0	1	10
432-9376	TD6-5/16UNC18	¥2,098	¥2,590	5/16	18	8.0	17.5	1	10
432-9384	TD6-3/8UNC16	¥2,098	¥2,590	3/8	16	9.5	19.1	1	15
432-9392	TD6-7/16UNC14	¥2,284	¥2,820	7/16	14	11.1	22.2	1	30
432-9406	TD6-1/2UNC13	¥2,520	¥3,110	1/2	13	12.7	27.0	1	40
432-9414	TD6-9/16UNC12	¥3,564	¥4,400	9/16	12	12.7	27.0	1	40
432-9422	TD6-5/8UNC11	¥3,880	¥4,790	5/8	11	15.8	32.0	1	70
432-9431	TD6-3/4UNC10	¥4,617	¥5,700	3/4	10	19.0	36.5	1	100
432-9449	TD6-7/8UNC9	¥5,670	¥7,000	7/8	9	22.2	41.0	1	150
432-9457	TD6-1UNC8	¥7,873	¥9,720	1	8	25.4	46.0	1	200

Set Commodity

Order Unit: 1 Set

SPQ: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Set Contents	Qty Per Set (piece)	Weight (g/set)
768-1712	THD-UNCSET	¥41,294	¥50,980	TD6-1/4UNC20, TD6-5/16UNC18, TD6-3/8UNC16, TD6-7/16UNC14, TD6-1/2UNC13, TD6-5/8UNC11, TD6-3/4UNC10, TD6-7/8UNC9, TD6-1UNC8	9	1050

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items

Hexagon Sarae Nut Die (unified fine thread)



2 side width dimension



TD6-1UNF14
THD-UNFSET (set item)



Warning
•Hexagon sarae nut die, unlike round die, does not have adjustment screw to adjust size. Therefore, hexagon sarae nut die may not fit depending on the screw precision.
•Cannot be used for stainless steel screw.

Features •Used to clean bolt and screw. •You can work with an adjustable wrench.
•Substitute for round die when repairing ridge. Use •For repairing UNF (unified fine) ridge
Materials •Low-Alloy Steel (SKS) Origin •Japan

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nominal Dimension	Number of Ridges	Thickness (mm)	2 Side Width Dimension (mm)	SPQ (piece)	Weight (g)
432-9465	TD6-1/4UNF28	¥2,098	¥2,590	1/4	28	6.3	15.0	1	10
432-9473	TD6-5/16UNF24	¥2,098	¥2,590	5/16	24	8.0	17.5	1	10
432-9481	TD6-3/8UNF24	¥2,098	¥2,590	3/8	24	9.5	19.1	1	15
432-9490	TD6-7/16UNF20	¥2,284	¥2,820	7/16	20	11.1	22.2	1	30
432-9503	TD6-1/2UNF20	¥2,520	¥3,110	1/2	20	12.7	27.0	1	40
432-9511	TD6-9/16UNF18	¥3,564	¥4,400	9/16	18	12.7	27.0	1	40
432-9520	TD6-5/8UNF18	¥3,880	¥4,790	5/8	18	15.8	32.0	1	70
432-9538	TD6-3/4UNF16	¥4,617	¥5,700	3/4	16	19.0	36.5	1	100
433-6852	TD6-7/8UNF14	¥5,670	¥7,000	7/8	14	22.2	41.0	1	150
432-9554	TD6-1UNF14	¥7,873	¥9,720	1	14	25.4	46.0	1	200

Set Commodity

Order Unit: 1 Set

SPQ: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Set Contents	Qty Per Set (piece)	Weight (g/set)
768-1721	THD-UNFSET	¥41,294	¥50,980	TD6-1/4UNF28, TD6-5/16UNF24, TD6-3/8UNF24, TD6-7/16UNF20, TD6-1/2UNF20, TD6-5/8UNF18, TD6-3/4UNF16, TD6-7/8UNF14, TD6-1UNF14	9	1050

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items

Hexagon Sarae Nut Die (for whitworth thread)



2 side width dimension



TD6-3/4W10
THD-WSET (set item)



Warning
•Hexagon sarae nut die, unlike round die, does not have adjustment screw to adjust size. Therefore, hexagon sarae nut die may not fit depending on the screw precision.
•Cannot be used for stainless steel screw.

Features •Used to clean bolt and screw. •You can work with an adjustable wrench.
•Substitute for round die when repairing ridge. Use •For repairing BSW (whitworth) ridge
Materials •Low-Alloy Steel (SKS) Origin •Japan

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nominal Dimension	Number of Ridges	Thickness (mm)	2 Side Width Dimension (mm)	SPQ (piece)	Weight (g)
352-0803	TD6-1/8W40	¥1,863	¥2,300	1/8	40	6.3	15.0	1	7
432-9279	TD6-3/16W24	¥2,098	¥2,590	3/16	24	6.3	15.0	1	10
352-0773	TD6-1/4W20	¥1,863	¥2,300	1/4	20	6.3	15.0	1	7
432-9244	TD6-5/16W18	¥2,098	¥2,590	5/16	18	8.0	17.5	1	10
352-0889	TD6-3/8W16	¥1,863	¥2,300	3/8	16	9.5	19.1	1	15
432-9252	TD6-7/16W14	¥2,309	¥2,850	7/16	14	11.1	22.2	1	30
352-0757	TD6-1/2W12	¥2,236	¥2,760	1/2	12	12.7	27.0	1	39
432-9261	TD6-9/16W12	¥3,564	¥4,400	9/16	12	12.7	27.0	1	40
352-0749	TD6-5/8W11	¥3,451	¥4,260	5/8	11	15.8	32.0	1	66
352-0854	TD6-3/4W10	¥4,082	¥5,040	3/4	10	19.0	36.5	1	96
352-0838	TD6-7/8W9	¥5,079	¥6,270	7/8	9	22.2	41.0	1	143
352-0820	TD6-1W8	¥7,031	¥8,680	1	8	25.4	46.0	1	195

Set Commodity

Order Unit: 1 Set

SPQ: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Set Contents	Qty Per Set (piece)	Weight (g/set)
768-1739	THD-WSET	¥41,294	¥50,980	TD6-1/8W40, TD6-1/4W20, TD6-5/16W18, TD6-3/8W16, TD6-7/16W14, TD6-1/2W12, TD6-5/8W11, TD6-3/4W10, TD6-7/8W9, TD6-1W8	10	1050

Contact us:0120-509-849 <http://www.orange-book.com/>

Threading Tools

Spiral Fluted Taps

Point Taps

Roll Taps

Hand Taps

Hexagonal Shank Tapping Drills

Tap Holders

Taps for Pipe

Thread Mills for Machining Center

Dies

Thread Repair Tools

Tap and Bolt Burr Removing Tools

Screw

For other cutting tools, see p. 1-805 to 1006