

Prices displayed include 8% tax.

**TRUSCO** Stock 38,650 Items  
**"Measuring Tape with Memo Plate"** Calibration OK Approx. 2 Weeks

**Com** Drawing  
**Adjustable Hook** **Lock** **JIS 1Rank** **455 mmPitch**  
 Tape Width 16mm

- Features**
- With a memo plate to jot down.
  - With metal end-clip.
- Materials**
- Tape: Steel
- Origin**
- China



Please use a pencil.



TT13-20B

Double-sided



**TRUSCO** Stock 38,650 Items  
**"Double Sided Neo-Lock"** Calibration OK Approx. 2 Weeks **RoHS**

**Com** Drawing  
**Adjustable Hook** **Lock** **JIS 1Rank** **455 mmPitch**

- Features**
- Both front and back sides uses adapted common general scale gradation.
- Materials**
- Tape: Steel
- Origin**
- Malaysia



TRC-1635L

Double-sided



Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Tape Length (m)	Tape Width (mm)	Horizontal Retention (m)	SPQ (piece)	Weight (g)
353-9202	TT13-20B	¥ 535	¥ 660	2.0	13	1.2	10	73
353-9229	TT16-35B	¥1,013	¥1,250	3.5	16	1.5	10	132
353-9245	TT16-55B	¥1,377	¥1,700	5.5	16	1.5	10	195

Contact us:0120-509-849 <http://www.orange-book.com/>

Order Unit: 1 Piece (Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Tape Length (m)	Tape Width (mm)	Horizontal Retention (m)	SPQ (piece)	Weight (g)
276-0614	TRC-1635L	¥1,029	¥1,270	3.5	16	1.3	6	122

Contact us:0120-509-849 <http://www.orange-book.com/>

**TRUSCO** Stock 38,650 Items  
**Double Side Measuring Tape**

**Adjustable Hook** **Lock** **455 mmPitch**

- Features**
- Conducting a JIS standard compatible inspection, it realizes a low price while keeping its quality.
  - Matte type highly durable tape specification.
  - With the brake function.
- Materials**
- Tape: Steel
- Origin**
- China



TERC-1955B-BK



Back

Double-sided



Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Tape Length (m)	Tape Width (mm)	Horizontal Retention (m)	SPQ (piece)	Weight (g)
837-1256	TERC-1955B-BK	¥741	¥ 800	5.5	19	1.7	10	195
837-1257	TERC-2555B-BK	¥972	¥1,050	5.5	25	2.4	10	235

Contact us:0120-509-849 <http://www.orange-book.com/>

**TRUSCO** Stock 38,650 Items  
**Double Side Measuring Tape Magnet Hook**

**Adjustable Hook** **Lock** **455 mmPitch**

- Features**
- Conducting a JIS standard compatible inspection, it realizes a low price while keeping its quality.
  - Equipped with a magnet hook that is convenient for measuring.
  - Matte type highly durable tape specification.
  - With the brake function.
- Materials**
- Tape: Steel
- Origin**
- China



TERC-2555BMG-BK

Magnet part



Double-sided



Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Tape Length (m)	Tape Width (mm)	Horizontal Retention (m)	SPQ (piece)	Weight (g)
837-1258	TERC-2555BMG-BK	¥1,065	¥1,150	5.5	25	2.4	10	240

Contact us:0120-509-849 <http://www.orange-book.com/>

**MURATEC KDS** Stock 280 Items  
**"Neo-Lock"** Calibration OK Approx. 2 Weeks **RoHS**

**Adjustable Hook** **Lock** **JIS 1Rank** **455 mmPitch**

- Features**
- Perfectly fits the hand compact design.
- Materials**
- Tape: Steel
- Origin**
- Malaysia



S16-35N

Single-sided



Order Unit: 1 Piece (Price revision date: Jan, 2016) MURATEC-KDS CORP.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Tape Length (m)	Tape Width (mm)	Horizontal Retention (m)	SPQ (piece)	Weight (g)
003-2379	S13-20N	¥ 697	¥1,020	2.0	13	1.2	12	68
003-2387	S16-35N	¥1,317	¥1,950	3.5	16	1.5	12	128
003-2395	S16-55N	¥1,791	¥2,650	5.5	16	1.5	12	185

Contact us:0120-25-5548 <http://www.muratec-kds.jp/>

**MURATEC KDS** Stock 280 Items  
**"Double Sided Neo-Lock"** Calibration OK Approx. 2 Weeks **RoHS**

**Adjustable Hook** **Lock** **JIS 1Rank** **455 mmPitch**

- Features**
- The back side is a vertical scale that is easy to see for height measurement.
- Materials**
- Tape: Steel
- Origin**
- Malaysia



ZS19-55BP

Double-sided



Order Unit: 1 Piece (Price revision date: Jan, 2016) MURATEC-KDS CORP.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Tape Length (m)	Tape Width (mm)	Horizontal Retention (m)	SPQ (piece)	Weight (g)
209-8962	ZS19-35BP	¥1,544	¥2,290	3.5	19	1.8	6	164
109-7229	ZS19-55BP	¥1,814	¥2,690	5.5	19	1.8	6	222
209-8971	ZS19-75BP	¥2,499	¥3,700	7.5	19	1.8	6	305
109-7407	ZS22-55BP	¥2,106	¥3,120	5.5	22	2.1	6	252
209-9721	ZS22-75BP	¥2,532	¥3,750	7.5	22	2.1	6	344
109-7512	ZS25-55BP	¥1,959	¥2,900	5.5	25	2.4	4	278
109-7521	ZS25-75BP	¥2,397	¥3,550	7.5	25	2.4	4	390
221-7015	ZS25-10BP	¥3,240	¥4,800	10.0	25	2.4	4	510

Contact us:0120-25-5548 <http://www.muratec-kds.jp/>