

Prices displayed include 8% tax.

TRUSCO  
 Stock 38,650 Items

## "Steel Pocket Tape Measure"

Calibration OK  
Approx. 2 Weeks

Com Drawing  
 JIS 1 Rank  
 455 mm Pitch

- Features
- With its phosphorescent plate specification, easy to find even in a dark work site.
  - Tape is strong against bend, durable steel (SK85) is used as core material, and the surface is baking finish with white polyester.
  - Standard Tensile Strength: 20N
- Specs
- Materials
- Tape: Steel
- Origin
- China



PKM-20



TJM DESIGN  
 Stock 1,907 Items

## "Engineer Pocket"

Calibration OK  
Approx. 3 Weeks

JIS 1 Rank  
 455 mm Pitch

- Features
- Tape is strong against bend, durable steel (SK85) is used as core material, and the surface is baking finish with white polyester.
  - Standard Tensile Strength: 20N
- Specs
- Materials
- Tape: Steel
- Origin
- China



EPK-20BL



Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Tape Length (m)	Tape Width (mm)	Tape Thickness (mm)	SPQ (piece)	Weight (g)
342-9776	PKM-10	¥1,863	¥2,300	10	10	0.17	4	168
342-9784	PKM-20	¥2,835	¥3,500	20	10	0.17	4	298

Contact us: 0120-509-849 <http://www.orange-book.com/>

Order Unit: 1 Piece

TJM DESIGN CORP.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Tape Length (m)	Tape Width (mm)	Tape Thickness (mm)	SPQ (piece)	Weight (g)
292-0107	EPK-10BL	¥2,802	¥4,150	10	10	0.17	4	168
292-0115	EPK-20BL	¥4,199	¥6,220	20	10	0.17	4	298
292-0123	EPK-30BL	¥6,123	¥9,070	30	10	0.17	4	416

Contact us: 0120-125577 <http://www.tajimatool.co.jp/>

TJM DESIGN  
 Stock 1,907 Items

## "Symron-S"

Calibration OK  
Approx. 3 Weeks

JIS 1 Rank

- Features
- A compact tape measure that is easy to use.
  - Excellent in insulation and chemical resistance.
  - Washable with water.
  - It will not be bent even if a tire rolls over it.
- Specs
- Materials
- Tape: Glass Fiber
- Origin
- China



YNS-20BL



MURATEC KDS  
 Stock 280 Items

## "Uni Long"

Calibration OK  
Approx. 2 Weeks

JIS 1 Rank  
 455 mm Pitch

- Features
- A usable reel type.
  - With shock absorber for tip protection.
  - Standard tensile strength: 100N
- Specs
- Materials
- Tape: Steel
- Origin
- Malaysia



UL13-50



Order Unit: 1 Piece

TJM DESIGN CORP.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Tape Length (m)	Tape Width (mm)	Tape Thickness (mm)	SPQ (piece)	Weight (g)
377-3191	YNS-10BL	¥1,923	¥2,850	10	13	0.55	4	190
377-3205	YNS-20BL	¥2,883	¥4,270	20	13	0.55	4	335
377-3213	YNS-30BL	¥4,110	¥6,090	30	13	0.55	4	495
377-3221	YNS-50BL	¥6,210	¥9,200	50	13	0.55	1	745

Contact us: 0120-125577 <http://www.tajimatool.co.jp/>

Order Unit: 1 Piece

(Price revision date: Jan, 2016) MURATEC-KDS CORP.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Tape Length (m)	Tape Width (mm)	Tape Thickness (mm)	SPQ (piece)	Weight (kg)
109-1620	UL13-30	¥7,560	¥11,200	30	13	0.23	5	0.9
109-1638	UL13-50	¥10,800	¥16,000	50	13	0.23	5	1.4

Contact us: 0120-25-5548 <http://www.muratec-kds.jp/>

MURATEC KDS  
 Stock 280 Items

## "Speed Teclon"

Calibration OK  
Approx. 3 Weeks

JIS 1 Rank  
 455 mm Pitch

- Features
- A unique 4x speed mechanism with fast rolling.
  - Super power coating tape that is strong against break, rust and wear.
- Materials
- Tape: Steel
- Origin
- Malaysia



ST13-50



Item No.	Standard Tensile Strength
ST10-30	50N
ST10-50	50N
ST13-30	100N
ST13-50	100N

MURATEC KDS  
 Stock 280 Items

## "Speed Teclon"

Calibration OK  
Approx. 2 Weeks

JIS 1 Rank  
 455 mm Pitch

- Features
- A unique 4x speed mechanism with fast rolling.
  - Adopted an elastomeric grip that is non-slip and easy to grasp.
  - With shock absorber
  - A stainless steel tape resistant to breaking, rust and wear.
- Specs
- Materials
- Tape: Stainless Steel
- Origin
- Malaysia



SST10-50



Order Unit: 1 Piece

(Price revision date: Jan, 2016) MURATEC-KDS CORP.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Tape Length (m)	Tape Width (mm)	Tape Thickness (mm)	SPQ (piece)	Weight (kg)
376-2033	ST10-30	¥8,506	¥12,100	30	10	0.40	5	0.874
376-2041	ST10-50	¥11,602	¥16,500	50	10	0.40	5	1.230
165-7160	ST13-30	¥9,044	¥13,400	30	13	0.45	5	1.200
165-7178	ST13-50	¥12,891	¥19,100	50	13	0.45	5	1.700

Contact us: 0120-25-5548 <http://www.muratec-kds.jp/>

Order Unit: 1 Piece

(Price revision date: Jan, 2016) MURATEC-KDS CORP.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Tape Length (m)	Tape Width (mm)	Tape Thickness (mm)	SPQ (piece)	Weight (kg)
109-1654	SST10-30	¥10,393	¥15,400	30	10	0.45	5	0.85
109-1662	SST10-50	¥12,961	¥19,200	50	10	0.45	5	1.19

Contact us: 0120-25-5548 <http://www.muratec-kds.jp/>