

Vibration-proof Materials (underlay type)

Stock 329 Items

2-247

Prices displayed include 8% tax.

TRUSCO **Stock 38,650 Items**

Hexagonal Vibration-proof Rubber

RoHS

Com Drawing



TOH-D Type (double bolt type)



TOH-S Type (single bolt type)

- Features** • Because the hexagonal type is in millimeter size, work can be performed with commercially available tool.
 • It can also be attached to places deep down such as the bottom of a groove by using a deep socket.
Use • Various machine tool, centrifugal separator, crusher, motor, and other standard industrial machinery.
Specs • Rubber Hardness: 60°
Materials • Rubber: Natural Rubber (NR) • Metal Fitting: Rolling Steel Material for Standard Structure Origin • Japan

Double Bolt Type

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Mechanical Spring Constant (N/mm)	Allowable Weight (N)	Outer Dimensions (mm)	Rubber Height (mm)	Screw Dimension	Mounting Shaft Length (mm)	SPQ (piece)	Weight (g)
761-2303	TOH-1216D	¥463	¥500	41	24	12	16	M5 x 0.80	12	10	8.3
761-2320	TOH-1415D	¥463	¥500	67	30	14	15	M5 x 0.80	15	10	20.2
761-2346	TOH-2115D	¥490	¥530	115	62	21	15	M6 x 1.00	15	10	10.2
761-2362	TOH-2618D	¥602	¥650	165	82	26	18	M6 x 1.00	18	10	33.5
761-2389	TOH-2918D	¥723	¥780	310	220	29	18	M8 x 1.25	24	10	56.0

TRUSCO NAKAYAMA CORPORATION

Single Bolt Type

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Mechanical Spring Constant (N/mm)	Allowable Weight (N)	Outer Dimensions (mm)	Rubber Height (mm)	Screw Dimension	Mounting Shaft Length (mm)	SPQ (piece)	Weight (g)
761-2311	TOH-1216S	¥528	¥570	58	23	12	16	M5 x 0.80	12	10	7.6
761-2338	TOH-1415S	¥528	¥570	94	29	14	15	M5 x 0.80	15	10	9.0
761-2354	TOH-2115S	¥602	¥650	180	69	21	15	M6 x 1.00	15	10	19.5
761-2371	TOH-2618S	¥685	¥740	215	95	26	18	M6 x 1.00	18	10	40.0
761-2397	TOH-2918S	¥833	¥900	600	245	29	18	M8 x 1.25	24	10	53.8

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

Vibration Absorbing Rubber for Light Load

RoHS

Com Drawing



TK215

- Features** • A vibration absorbing rubber of low mechanical spring with a large degree of flexibility on the rubber, it demonstrates its effect on vibration prevention against a wide frequency range.
Specs • Rubber Hardness: 47°
Materials • Rubber: Natural Rubber (NR) • Metal Fitting: Rolling Steel Material for Standard Structure Origin • Japan

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Mechanical Spring Constant (N/mm)	Allowable Weight (N)	Outer Dimensions (mm)	Rubber Height (mm)	Mounting Hole Diameter (mm)	Mounting Pitch (mm)	Weight (g)
233-8157	TK215	¥1,111	¥1,200	34.5	69	60	15	6	48	35
233-8165	TK202	¥2,991	¥3,230	98.0	295	90	20	8	70	100
233-8173	TK203	¥3,610	¥3,900	125.0	635	130	30	10	110	280

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

Round Type Stopper

RoHS

Com Drawing



TS103

- Features** • The feeling of impact at the time of a collision is small and the noise generation is minimized, so it is possible to reduce the impact of the collision and the surrounding area.
Specs • Rubber Hardness: 57°
Materials • Rubber: Natural Rubber (NR) • Metal Fitting: Rolling Steel Material for Standard Structure Origin • Japan

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Allowable Weight (N)	Outer Dimensions (mm)	Rubber Height (mm)	Mounting Hole Diameter (mm)	Mounting Pitch (mm)	Weight (kg)
233-8181	TS101	¥ 2,926	¥ 3,160	7850	50	35	5.5	40	0.1
233-8190	TS102	¥ 6,110	¥ 6,600	24490	80	56	6.5	63	0.5
233-8203	TS103	¥ 7,730	¥ 8,350	38984	100	69	13.0	80	0.9
233-8211	TS104	¥11,830	¥12,780	61475	125	88	13.0	100	1.8
233-8220	TS105	¥13,747	¥14,850	97961	160	108	17.0	125	2.9
233-8238	TS106	¥21,708	¥23,450	154938	200	135	17.0	160	6.2
233-8246	TS107	¥43,147	¥46,610	244902	250	170	21.0	200	11.0
233-8254	TS108	¥62,495	¥67,510	389844	315	212	21.0	250	20.5

Contact us: 0120-509-849 <http://www.orange-book.com/>

OHNO RUBBER **Stock 55 Items**

Vibration Absorbing Rubber for Low Load

RoHS



OAT-12140

- Features** • Effective for vibration reduction in the low frequency range. • The vibration absorbing effect and the natural rubber material with outstanding adhesion strength for metal fittings have achieved the low hardness. • A hardness of approximately 1/3 of the standard hardness of 65±5 (JIS-A).
Use • Vibration prevention of various industrial equipment.
Specs • Rubber Hardness: 20°
Materials • Screw: Steel (SWCH/SPCC) • Rubber Part: Natural Rubber Type Origin • Japan

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Mechanical Spring Constant (N/mm)	Allowable Weight (N)	Outer Dimensions (mm)	Rubber Height (mm)	Screw Dimension	Mounting Shaft Length (mm)	SPQ (piece)	Weight (g)
441-5850	OAT-12140	¥529	¥490	8.8	17	12	14	M4 x 0.7	14	1	6
441-5876	OAT-15151	¥529	¥490	10.5	23	15	15	M4 x 0.7	15	1	9
441-5868	OAT-15150	¥562	¥520	10.5	23	15	15	M5 x 0.8	15	1	10
441-5884	OAT-20150	¥691	¥640	19.0	41	20	15	M6 x 1.0	15	1	17
441-5892	OAT-25180	¥821	¥760	36.0	96	25	18	M6 x 1.0	18	1	30
441-5906	OAT-30180	¥896	¥830	68.2	180	30	18	M6 x 1.0	18	1	41
441-5914	OAT-35180	¥961	¥890	96.5	255	35	18	M6 x 1.0	18	1	54

Contact us: 0287-48-4100 <http://www.ohno5825.co.jp/>