



Stock 38,650 Items

Ball Plunger (steel ball)



T3PJ

Tighten with flathead screwdriver

Features •The main unit ball is a steel ball plunger with a negative groove.
Use •The pressing force of the ball can be adjusted by rotating the screw portion of the main unit. For positioning and fixing.
Specs •Heat Resistant Temperature: 250°C
Materials •Body: Steel •Ball: Steel, Hardened
Origin •Germany

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Load (N)	Screw Dimension	Stroke (mm)	Total Length (mm)	Ball Diameter (mm)	SPQ (piece)	Weight (g)
791-5446	T3PJ	¥211	¥260	3.0 to 4.5	M3 x 0.50	0.4	7	1.5	10	0.2
791-5497	T4PJ	¥162	¥200	8.5 to 14.0	M4 x 0.70	0.8	9	2.5	10	0.4
791-5551	T5PJ	¥162	¥200	8.0 to 14.0	M5 x 0.80	0.9	12	3.0	10	1.0
791-5616	T6PJ	¥162	¥200	11.0 to 18.0	M6 x 1.00	1.0	14	3.5	10	1.7
791-5675	T8PJ	¥252	¥310	18.0 to 31.0	M8 x 1.25	1.5	16	4.5	10	3.5
791-5250	T10PJ	¥252	¥310	24.0 to 45.0	M10 x 1.50	2.0	19	6.0	10	6.6
791-5306	T12PJ	¥381	¥470	26.0 to 49.0	M12 x 1.75	2.5	22	8.0	10	11.0
791-5357	T16PJ	¥535	¥660	41.0 to 86.0	M16 x 2.00	3.5	24	10.0	10	23.0
791-5403	T20PJ	¥721	¥890	56.0 to 111.0	M20 x 2.50	4.5	30	12.0	10	45.0

Contact us:0120-509-849 <http://www.orange-book.com/>



Stock 110 Items

Ball Plunger (steel ball)



BST

Tighten with flathead screwdriver

Features •With the spring built-in the screw body, strokes the center pin by pressing pressure and positions.
Use •Locating parts such as indexing and stopper.
Specs •Heat resistant temperature: 100°C
Materials •Body: Steel •Ball: Steel
Origin •Germany

Order Unit: 1 Piece

IMAO CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Load (N)	Screw Dimension	Stroke (mm)	Total Length (mm)	Ball Diameter (mm)	SPQ (piece)	Weight (g)
105-7600	BST3	¥281	¥260	1.5 to 3.0	M3 x 0.50	0.5	7	1.5	100	0.2
105-7618	BST4	¥216	¥200	4.0 to 10.0	M4 x 0.70	0.8	9	2.5	100	0.6
105-7626	BST5	¥216	¥200	6.0 to 11.0	M5 x 0.80	0.9	12	3.0	100	0.9
105-7685	BST6	¥216	¥200	9.0 to 13.0	M6 x 1.00	1.0	14	3.5	100	1.5
105-7693	BST8	¥335	¥310	15.0 to 30.0	M8 x 1.25	1.5	16	5.0	100	3.5
105-7707	BST10	¥335	¥310	20.0 to 35.0	M10 x 1.50	2.0	19	6.0	100	7.0
105-7715	BST12	¥508	¥470	30.0 to 55.0	M12 x 1.75	2.5	22	8.0	50	10.0
105-7723	BST16	¥691	¥640	65.0 to 125.0	M16 x 2.00	3.5	24	10.0	50	24.0
105-7731	BST20	¥950	¥880	80.0 to 160.0	M20 x 2.50	4.5	30	12.0	50	45.0

Contact us:0575-32-2239 <http://www.imao.co.jp/>



Stock 38,650 Items

Ball Plunger (stainless steel ball)



T3PJ-SUS

Tighten with flathead screwdriver

Features •The main unit ball is a stainless steel ball plunger with a negative groove.
Use •The pressing force of the ball can be adjusted by rotating the screw portion of the main unit. For positioning and fixing.
Specs •Heat Resistant Temperature: 250°C
Materials •Main Body: Stainless Steel •Ball: Stainless Steel, Hardened
Origin •Germany

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Load (N)	Screw Dimension	Stroke (mm)	Total Length (mm)	Ball Diameter (mm)	SPQ (piece)	Weight (g)
791-5454	T3PJ-SUS	¥592	¥730	3.0 to 4.5	M3 x 0.50	0.4	7	1.5	10	0.2
791-5501	T4PJ-SUS	¥511	¥630	8.5 to 14.0	M4 x 0.70	0.8	9	2.5	10	0.4
791-5560	T5PJ-SUS	¥511	¥630	8.0 to 14.0	M5 x 0.80	0.9	12	3.0	10	1.0
791-5624	T6PJ-SUS	¥511	¥630	11.0 to 18.0	M6 x 1.00	1.0	14	3.5	10	1.7
791-5683	T8PJ-SUS	¥721	¥890	18.0 to 31.0	M8 x 1.25	1.5	16	4.5	10	3.7
791-5268	T10PJ-SUS	¥883	¥1,090	24.0 to 45.0	M10 x 1.50	2.0	19	6.0	10	6.8
791-5314	T12PJ-SUS	¥1,045	¥1,290	26.0 to 49.0	M12 x 1.75	2.5	22	8.0	10	11.0
791-5365	T16PJ-SUS	¥1,207	¥1,490	41.0 to 86.0	M16 x 2.00	3.5	24	10.0	10	23.0
791-5411	T20PJ-SUS	¥1,507	¥1,860	56.0 to 111.0	M20 x 2.50	4.5	30	12.0	10	45.0

Contact us:0120-509-849 <http://www.orange-book.com/>



Stock 110 Items

Ball Plunger (stainless steel ball)



BSU

Tighten with flathead screwdriver

Features •With the spring built-in the screw body, strokes the center pin by pressing pressure and positions.
Use •Locating parts such as indexing and stopper.
Specs •Heat resistant temperature: 180°C
Materials •Body: Stainless Steel (SUS303) •Ball: Stainless Steel (SUS420)
Origin •Germany

Order Unit: 1 Piece

IMAO CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Load (N)	Screw Dimension	Stroke (mm)	Total Length (mm)	Ball Diameter (mm)	SPQ (piece)	Weight (g)
105-7740	BSU3	¥767	¥710	1.5 to 3.0	M3 x 0.50	0.5	7	1.5	100	0.2
105-7758	BSU4	¥691	¥640	4.0 to 10.0	M4 x 0.70	0.8	9	2.5	100	0.6
105-7766	BSU5	¥691	¥640	6.0 to 11.0	M5 x 0.80	0.9	12	3.0	100	0.9
105-7774	BSU6	¥691	¥640	9.0 to 13.0	M6 x 1.00	1.0	14	3.5	100	1.5
105-7782	BSU8	¥950	¥880	15.0 to 30.0	M8 x 1.25	1.5	16	5.0	100	3.5
105-7791	BSU10	¥1,188	¥1,100	20.0 to 35.0	M10 x 1.50	2.0	19	6.0	100	7.0
105-7804	BSU12	¥1,404	¥1,300	30.0 to 55.0	M12 x 1.75	2.5	22	8.0	50	10.0
105-7812	BSU16	¥1,620	¥1,500	65.0 to 125.0	M16 x 2.00	3.5	24	10.0	50	24.0
105-7821	BSU20	¥1,944	¥1,800	80.0 to 160.0	M20 x 2.50	4.5	30	12.0	50	45.0

Contact us:0575-32-2239 <http://www.imao.co.jp/>