

Prices displayed include 8% tax.

TRUSCO
 Stock 38,650 Items

Plunger (insertion type)



Features • Insertion type plunger.
 Use • Used by fitting the main unit case into the mounting hole. For positioning and fixing.
 Materials • Ball: Stainless Steel, Hardened Origin • Germany

Plastic Case Type Specs • Heat Resistant Temperature: 50°C
 Materials • Body: Resin (POM)

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Load (N)	Outer Diameter (mm)	Stroke (mm)	Total Length (mm)	Ball Diameter (mm)	SPQ (piece)	Weight (g)
791-5471	T4E-R	¥ 81	¥ 100	3.0 to 6.5	4	0.8	5	3.0	10	0.2
791-5535	T5E-R	¥ 90	¥ 110	6.0 to 9.4	5	1.0	6	4.0	10	0.4
791-5594	T6E-R	¥ 97	¥ 120	6.2 to 12.6	6	1.6	7	5.0	10	0.7
791-5659	T8E-R	¥ 113	¥ 140	10.0 to 20.4	8	1.9	9	6.5	10	1.5

Stainless Steel Case Type Specs • Heat Resistant Temperature: 250°C
 Materials • Body: Stainless Steel (SUS305)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Load (N)	Outer Diameter (mm)	Stroke (mm)	Total Length (mm)	Ball Diameter (mm)	SPQ (piece)	Weight (g)
791-5489	T4E-SUS	¥ 187	¥ 230	2.5 to 6.0	4	1.0	5	3.0	10	0.3
791-5543	T5E-SUS	¥ 194	¥ 240	3.0 to 6.5	5	1.4	6	4.0	10	0.6
791-5608	T6E-SUS	¥ 203	¥ 250	5.5 to 11.5	6	1.8	7	5.0	10	1.0
791-5667	T8E-SUS	¥ 243	¥ 300	7.0 to 12.5	8	2.4	9	6.5	10	2.1

Contact us: 0120-509-849 <http://www.orange-book.com/>



kipp
 Stock 110 Items

Plunger (insertion type)



Features • Insertion type plunger.
 Use • Locating parts such as indexing and stopper.
 Origin • Germany

Plastic Case Type Specs • Heat resistant temperature: 90°C
 Materials • Body: Polyacetal (POM) • Ball: Stainless Steel (SUS420)

Order Unit: 1 Piece

IMAO CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Load (N)	Outer Diameter (mm)	Stroke (mm)	Total Length (mm)	Ball Diameter (mm)	SPQ (piece)	Weight (g)
169-0477	EBP4	¥ 97	¥ 90	3 to 7	4	0.7	5	3.0	100	0.2
169-0485	EBP5	¥ 108	¥ 100	4 to 7	5	1.0	6	4.0	100	0.4
169-0493	EBP6	¥ 119	¥ 110	6 to 12	6	1.5	7	5.0	100	0.7
169-0507	EBP8	¥ 140	¥ 130	6 to 12	8	1.8	9	6.5	100	1.5

Stainless Steel Case Type Specs • Heat resistant temperature: 180°C
 Materials • Body: Stainless Steel (SUS303) • Ball: Stainless Steel (SUS420)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Load (N)	Outer Diameter (mm)	Stroke (mm)	Total Length (mm)	Ball Diameter (mm)	SPQ (piece)	Weight (g)
169-0515	SBP4	¥ 259	¥ 240	3 to 7	4	0.8	5	3.0	100	0.3
169-0523	SBP5	¥ 259	¥ 240	4 to 7	5	1.0	6	4.0	100	0.6
169-0531	SBP6	¥ 270	¥ 250	6 to 12	6	1.5	7	5.0	100	1.0
169-0540	SBP8	¥ 324	¥ 300	6 to 12	8	1.8	9	6.5	100	2.0

Contact us: 0575-32-2239 <http://www.imao.co.jp/>



TRUSCO
Orange Jr. Book

A pro-tool compact catalog that lists a wide variety of products all in one, including nearly every category on Orange-Book!

Published once every 2 years

Number of Products Listed: approx. **56,000** items

Number of Off-the-shelf Products: approx. **53,200**,

off-the-shelf ratio **95%**

Number of Listed Manufacturers: approx. **1,419** companies

Number of Catalog Pages: approx. **2,700** pages

Order Code	Item No.	Price (tax not included)
858-5867	OBJM2018E	¥ 5,500

