

Resin Couplings

The number next to the logo mark indicates items in stock for each brand.

Fluid Couplings • Tubes

Tube Fittings

Couplings

Pipe Joints

Ball Valves

Needle Valves

Air Tubes, Hoses

Tools for Tube

Tube Cutters

Air Reels



Resin Socket (for hose mounting)



TRS-N5NR

- Specs**
- Working Fluid: Air
 - Working temperature: 0 to 50°C
 - Max working pressure: 1.0MPa
- Materials**
- Main Body: Polyphenylene Ether (PPE) + Nylon (PA)
 - Seal Rubber: Nitrile Rubber (NBR)
- Origin**
- Japan

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Other Side Hose Size (mm)	SPQ (piece)	Weight (g)
819-5072	TRS-N5NR	¥731	¥790	5.0 x 8.0	100	28
819-5073	TRS-N6.5NR	¥731	¥790	6.5 x 10.0	100	28
819-5074	TRS-N8NR	¥768	¥830	8.0 x 12.0	100	30
819-5075	TRS-N8.5NR	¥768	¥830	8.5 x 12.5	100	30
819-5076	TRS-N9NR	¥824	¥890	9.0 x 15.0	100	32

Contact us: 0120-509-849 <http://www.orange-book.com/>



Resin Plug (for hose mounting)



TRP-N5N

- Specs**
- Working Fluid: Air
 - Working temperature: 0 to 50°C
 - Max working pressure: 1.0MPa
 - For hose mounting
- Materials**
- Main Body: Polyacetate (POM)
- Origin**
- Japan

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Other Side Hose Size (mm)	SPQ (piece)	Weight (g)
819-5054	TRP-N5N	¥222	¥240	5.0 x 8.0	100	12
819-5055	TRP-N6.5N	¥222	¥240	6.5 x 10.0	100	12
819-5057	TRP-N8N	¥241	¥260	8.0 x 12.0	100	14
819-5056	TRP-N8.5N	¥241	¥260	8.5 x 12.5	100	14
819-5058	TRP-N9N	¥269	¥290	9.0 x 15.0	100	16

Contact us: 0120-509-849 <http://www.orange-book.com/>



Resin Socket (for hose mounting)



TRS-T2NR

- Warning**
- Only for TRS-T2NR, reinforcement insert (made of brass) is included in the barb part.

- Specs**
- Working Fluid: Air
 - Working temperature: 0 to 50°C
 - Max working pressure: 1.0MPa
 - One-way opening/closing type
 - For hose mounting
- Materials**
- Main Body: Polyphenylene Ether (PPE) + Nylon (PA)
 - Seal Rubber: Nitrile Rubber (NBR)
- Origin**
- Japan

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Other Side Hose Size Inner Diameter (mm)	SPQ (piece)	Weight (g)
819-5065	TRS-T2NR	¥658	¥710	7	100	25
819-5066	TRS-T3NR	¥658	¥710	10	100	23
819-5067	TRS-T4NR	¥658	¥710	13	100	24

Contact us: 0120-509-849 <http://www.orange-book.com/>



Resin Plug (for hose mounting)



TRP-T02

- Specs**
- Working Fluid: Air
 - Working temperature: 0 to 50°C
 - Max working pressure: 1.0MPa
 - For hose mounting
- Materials**
- Main Body: Nylon (PA)
- Origin**
- Japan

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Other Side Hose Size Inner Diameter (mm)	SPQ (piece)	Weight (g)
819-5050	TRP-T02	¥116	¥125	7	100	5
819-5051	TRP-T03	¥116	¥125	10	100	6
819-5052	TRP-T04	¥116	¥125	13	100	7

Contact us: 0120-509-849 <http://www.orange-book.com/>



Stock 38,650 Items

Resin Socket (for internal thread mounting)



TRS-S2NR

- Warning**
- Only for TRS-S2NR, reinforcement insert (made of brass) is included in the screw part.

- Specs**
- Working Fluid: Air
 - Working temperature: 0 to 50°C
 - One-way opening/closing type
 - Max working pressure: 1.0MPa
- Materials**
- Main Body: Polyphenylene Ether (PPE) + Nylon (PA)
 - Seal Rubber: Nitrile Rubber (NBR)
- Origin**
- Japan

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Other Side Mounting Size	SPQ (piece)	Weight (g)
819-5068	TRS-S2NR	¥658	¥710	Rc1/4	100	24
819-5069	TRS-S3NR	¥658	¥710	Rc3/8	100	26
819-5070	TRS-S4NR	¥658	¥710	Rc1/2	100	25

Contact us: 0120-509-849 <http://www.orange-book.com/>



Resin Plug (for internal thread mounting)



Nylon TRP-S02

- Specs**
- Working Fluid: Air
 - Working temperature: 0 to 50°C
 - Max working pressure: 1.0MPa
 - For Internal Thread Mounting
- Origin**
- Japan

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Other Side Mounting Size	SPQ (piece)	Weight (g)
819-5059	TRP-S02	¥116	¥125	Rc1/4	100	5
819-5060	TRP-S03	¥116	¥125	Rc3/8	100	6

Contact us: 0120-509-849 <http://www.orange-book.com/>



Resin Socket (for 2 branch piping)



TRS-L1NR

- Specs**
- Working Fluid: Air, Water
 - Working temperature: 0 to 50°C
 - Max working pressure: 1.0MPa
- Materials**
- Main Body: Polyacetate (POM)
 - Seal Rubber: Nitrile Rubber (NBR)
- Origin**
- Japan

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Number of Divisions	SPQ (piece)	Weight (g)
819-5077	TRS-L1NR	¥2,888	¥3,120	2	50	80

Contact us: 0120-509-849 <http://www.orange-book.com/>



Stock 38,650 Items

Resin Elbow Plug



TRP-SL02

- Specs**
- Working Fluid: Air, Water
 - Working temperature: 0 to 50°C
 - Max working pressure: 1.0MPa
- Materials**
- Main Body: Polyacetate (POM)
- Origin**
- Japan

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Other Side Mounting Size	SPQ (piece)	Weight (g)
819-5062	TRP-SL02	¥241	¥260	Rc1/4	100	11
819-5063	TRP-SL03	¥241	¥260	Rc3/8	100	8
819-5064	TRP-SL04	¥241	¥260	Rc1/2	100	10

Contact us: 0120-509-849 <http://www.orange-book.com/>

Description of the coupling in the pressurized state leads to serious accident.