

Description of the coupling in the pressurized state leads to serious accident.

TRUSCO Stock 38,650 Items

## "α Urethane Braided Hose"

Com Drawing



- Features**
- The resin spring guard is used on the socket side, making it hard to break.
  - Excellent in oil resistance and pressure resistance.
  - Compatible with general coupling.
- Specs**
- Working Fluid: Air •Fluid Temperature: -5 to 60° C (to be freeze free)
  - Working Pressure: 1.5MPa (when used at room temperature)
  - With coupling plug
- Materials**
- Polyurethane
- Origin**
- Japan

Order Unit: 1 Roll

Order Code	Item No.	Price (per roll)	MSRP (per roll)	Color	Outer Diameter x Inner Diameter (mm)	Total Length (m)	Thickness (mm)	SPQ (roll)	Weight (kg)
759-6871	TUH-5	¥ 2,407	¥ 2,600	Orange	10 x 7	5	1.5	10	0.30
298-5888	TUH-10	¥ 3,258	¥ 3,520	Orange	10 x 7	10	1.5	1	0.57
298-5896	TUH-20	¥ 5,259	¥ 5,680	Orange	10 x 7	20	1.5	1	1.14
298-5900	TUH-30	¥ 7,128	¥ 7,700	Orange	10 x 7	30	1.5	1	1.71

TRUSCO NAKAYAMA CORPORATION

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items

## "Soft Urethane Braided Hose" (with resin coupling)

Com Drawing



- Features**
- Highly flexible and with less peculiar windings.
  - Resin Joint: One-touch Lock Type
  - With high pressure resistance and less bouncing.
  - Compatible with general coupling.
- Specs**
- Working Fluid: Air •Fluid Temperature: -20 to 60° C (without freezing)
  - Working Pressure: 1.4MPa •Allowable Bending Radius: 40mm
  - Connecting Joint: JN-6.5N/TN-6.5NR
- Materials**
- Hose: Polyurethane Resin
  - Socket: Polyphenylene Ether (PPE) + Nylon (PA)
  - Plug: Polyacetal (POM)
- Origin**
- Japan

Order Unit: 1 Roll

Order Code	Item No.	Price (per roll)	MSRP (per roll)	Color	Outer Diameter x Inner Diameter (mm)	Total Length (m)	Thickness (mm)	SPQ (roll)	Weight (kg)
228-0094	SUB-6.5-5	¥ 3,055	¥ 3,300	Orange	10 x 6.5	5	1.75	10	0.30
228-0108	SUB-6.5-10	¥ 5,212	¥ 5,630	Orange	10 x 6.5	10	1.75	10	0.57
228-0116	SUB-6.5-20	¥ 9,220	¥ 9,960	Orange	10 x 6.5	20	1.75	5	1.11
228-0124	SUB-6.5-30	¥ 13,423	¥ 14,500	Orange	10 x 6.5	30	1.75	3	1.65

TRUSCO NAKAYAMA CORPORATION

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items

## "Lightweight Soft Hose"

Com Drawing



- Features**
- Since the lightweight aluminum coupling is used, the air tool can be smoothly mounted with good usability.
  - By using special resin, surprising flexibility of the hose is realized.
  - Compatible with general coupling.
  - The resin spring guard is used on the socket side, making it hard to break.
  - With small bending radius and excellent usability. (min bending radius 40mm)
- Specs**
- Working Fluid: Air
  - Fluid Temperature: -5 to 60° C (to be freeze free)
  - Working Pressure: 1MPa (when used at room temperature)
  - With coupling plug
- Materials**
- Hose: Special Elastomer •Socket: Aluminum (with resin spring guard) •Plug: Iron
- Origin**
- Japan

Order Unit: 1 Roll

Order Code	Item No.	Price (per roll)	MSRP (per roll)	Color	Outer Diameter x Inner Diameter (mm)	Total Length (m)	Thickness (mm)	SPQ (roll)	Weight (kg)
298-5918	TKYH-10	¥ 6,314	¥ 6,820	Green (purple line)	10 x 6.5	10	1.75	1	0.68
298-5926	TKYH-20	¥ 8,859	¥ 9,570	Green (purple line)	10 x 6.5	20	1.75	1	1.25

TRUSCO NAKAYAMA CORPORATION

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items

## "Anti-spatter Polyurethane Braided Hose"

Com Drawing



- Features**
- Because it uses flame retardant urethane plastic, it prevents melting and spreading due to sparks such as spattering.
  - Has characteristics like lightweight, flexibility, wear resistance similar to polyurethane hose and excellent operability.
  - The hull is water resistance polyurethane raw materials with excellent weather resistance and safe for outdoor works.
- Specs**
- Working Fluid: Air •Fluid Temperature: -5 to 60° C (to be freeze free)
  - Working Pressure: 1.5MPa
  - Allowable Bending Radius: 6.5mm (room temperature) 50mm 8.5mm (room temperature) 60mm 11.0mm (room temperature) 80mm
- Materials**
- Flame Retardant Polyurethane Resin
- Origin**
- Japan

Order Unit: 1 Roll

Order Code	Item No.	Price (per roll)	MSRP (per roll)	Color	Connecting Joint	Outer Diameter x Inner Diameter (mm)	Total Length (m)	Thickness (mm)	SPQ (roll)	Weight (kg)
152-6758	SPB-6.5-10	¥ 5,739	¥ 6,200	Green	CHS-6.5H-MP/C4P-6.5H	10.0 x 6.5	10	1.75	10	0.76
152-6766	SPB-8.5-10	¥ 7,359	¥ 7,950	Green	CHS-8.5H-MP/C4P-8.5H	12.5 x 8.5	10	2.00	10	0.96
152-6774	SPB-11-10	¥ 12,590	¥ 13,600	Green	CHS-11.0H-MP/C4P-11.0H	16.0 x 11.0	10	2.50	10	1.73

TRUSCO NAKAYAMA CORPORATION

Contact us:0120-509-849 <http://www.orange-book.com/>

