



Description of the coupling in the pressurized state leads to serious accident.



Stock 38,650 Items

## "α Urethane Braided Hose"



TUB-6510




TUB-8510

TUB-6550

- Features**
- A low price version of urethane blade hose.
  - Excellent in oil resistance and pressure resistance.
  - Because it is flexibility, hard to have windings.
- Specs**
- Working Fluid: Air
  - Fluid Temperature: -5 to 60°C (to be freeze free)
  - Working Pressure: 1.5MPa (when used at room temperature)

**Materials** • Polyurethane  
**Origin** • Japan



**Warning**  
• Please use exclusive couplings for braided hose. Using other couplings may damage the hose.

Order Unit: 1 Roll

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per roll)	MSRP (per roll)	Color	Outer Diameter x Inner Diameter (mm)	Total Length (m)	Thickness (mm)	SPQ (roll)	Weight (kg)
759-9251	TUB-6505	¥ 1,342	¥ 1,450	Orange	10.0 x 6.5	5	1.75	5	0.29
759-9269	TUB-6510	¥ 2,222	¥ 2,400	Orange	10.0 x 6.5	10	1.75	5	0.57
759-9277	TUB-6520	¥ 4,443	¥ 4,800	Orange	10.0 x 6.5	20	1.75	5	1.14
759-9285	TUB-6530	¥ 6,665	¥ 7,200	Orange	10.0 x 6.5	30	1.75	5	1.71
298-5845	TUB-6550	¥ 9,368	¥ 10,120	Orange	10.0 x 6.5	50	1.75	1	2.85
298-5853	TUB-65100	¥ 18,737	¥ 20,240	Orange	10.0 x 6.5	100	1.75	1	5.70
759-9293	TUB-8505	¥ 2,278	¥ 2,460	Orange	12.5 x 8.5	5	2.00	5	0.42
759-9307	TUB-8510	¥ 3,703	¥ 4,000	Orange	12.5 x 8.5	10	2.00	5	0.83
759-9315	TUB-8520	¥ 7,406	¥ 8,000	Orange	12.5 x 8.5	20	2.00	5	1.68
759-9323	TUB-8530	¥ 11,109	¥ 12,000	Orange	12.5 x 8.5	30	2.00	5	2.49
298-5861	TUB-8550	¥ 15,783	¥ 17,050	Orange	12.5 x 8.5	50	2.00	1	4.15
298-5870	TUB-85100	¥ 31,567	¥ 34,100	Orange	12.5 x 8.5	100	2.00	1	8.30
759-9218	TUB-1105	¥ 3,795	¥ 4,100	Orange	16.0 x 11.0	5	2.50	5	0.65
759-9226	TUB-1110	¥ 6,295	¥ 6,800	Orange	16.0 x 11.0	10	2.50	5	1.30
759-9234	TUB-1120	¥ 12,497	¥ 13,500	Orange	16.0 x 11.0	20	2.50	5	2.60
759-9242	TUB-1130	¥ 18,514	¥ 20,000	Orange	16.0 x 11.0	30	2.50	5	3.90
352-1427	TUB-1150	¥ 27,309	¥ 29,500	Orange	16.0 x 11.0	50	2.50	1	6.50

Contact us: 0120-509-849 <http://www.orange-book.com/>



Stock 38,650 Items

## "Soft Urethane Braided Hose"



SUB-6.5-100

- Features**
- Highly flexible and with less peculiar windings.
  - With high pressure resistance and less bouncing.
- Specs**
- Working Fluid: Air
  - Fluid Temperature: -20 to 60°C (without freezing)
  - Working Pressure: 1.4MPa
  - Allowable Bending Radius: 40mm

**Materials** • Hose: Polyurethane Resin  
**Origin** • Japan



**Warning**  
• Please use exclusive couplings for braided hose. Using other couplings may damage the hose.

Order Unit: 1 Roll

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per roll)	MSRP (per roll)	Color	Outer Diameter x Inner Diameter (mm)	Total Length (m)	Thickness (mm)	SPQ (roll)	Weight (kg)
228-0132	SUB-6.5-100	¥ 39,806	¥ 43,000	Orange	10 x 6.5	100	1.75	4	5.5

Contact us: 0120-509-849 <http://www.orange-book.com/>



Stock 38,650 Items

## Urethane Braided Tube



TOP-6.5-100NG (neo gray)



TOP-6.5-100 (red)

- Features**
- Compared with rubber hose, it is approx. 1/3 to 1/5 lighter.
  - Excellent in oil resistance and pressure resistance and flexibility at low temperature (-5°C).
- Specs**
- Working Fluid: Air
  - Fluid Temperature: -5 to 60°C (to be freeze free)
  - Working Pressure: 1.5MPa
  - Allowable Bending Radius: (room temperature) 60mm

**Materials** • Polyurethane  
**Origin** • Japan



**Warning**  
• Please use exclusive couplings for braided hose. Using other couplings may damage the hose.



**Color: Neo Gray**

Order Unit: 1 Roll

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per roll)	MSRP (per roll)	Color	Outer Diameter x Inner Diameter (mm)	Total Length (m)	Thickness (mm)	SPQ (roll)	Weight (kg)
214-7467	TOP-6.5-100NG	¥ 20,829	¥ 22,500	Neo Gray	10.0 x 6.5	100	1.75	5	5.5

**Color: Red**

Order Unit: 1 Roll

Order Code	Item No.	Price (per roll)	MSRP (per roll)	Color	Outer Diameter x Inner Diameter (mm)	Total Length (m)	Thickness (mm)	SPQ (roll)	Weight (kg)
104-3170	TOP-6.5-100	¥ 20,829	¥ 22,500	Red	10.0 x 6.5	100	1.75	5	5.5
104-3188	TOP-8.5-100	¥ 36,103	¥ 39,000	Red	12.5 x 8.5	100	2.00	5	7.0

Contact us: 0120-509-849 <http://www.orange-book.com/>