


Prices displayed include 8% tax.

TRUSCO **Silent and Large Flow Volume Nozzle for Air Dusters**



25mm
TD-RCFN

- Features**
- Blows air with large flow rate power from the cut round section with special processing cut. (TD-RCFN)
 - Special processing cut is performed, air is spread from the cut part sideways, synchronized with the air that goes forward, and wide pattern air is blown remarkably. (TD-HCFN)
- Origin**
- Japan



Item No.	Nozzle Length (mm)
TD-RCFN	25
TD-HCFN	25

SPQ: 10 Pieces

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nozzle Opening Diameter (mm)	Nozzle Mounting Port	Weight (g)
488-0145	TD-RCFN	¥1,389	¥1,500	1 (flat cut wide angle 30°)	G1/8	36
488-0137	TD-HCFN	¥1,389	¥1,500	1 (flat cut ball surface)	G1/8	36

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO **Connection Nipple for Air Duster**

Stock 38,650 Items



TD-HWN TD-HWP



TD-KN TD-KP

- Features**
- Replacement joint for air duster.
 - Equipped with O-ring that air leakage is unlikely to occur.
- Specs**
- Max working pressure: 1.0MPa
 - Distance between parallel sides of hexagon (mm): 14
- Materials**
- Brass (nickel plating)
- Accessories**
- O-ring
- Origin**
- Japan

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nozzle Mounting Port	SPQ (piece)	Weight (g)
784-8072	TD-HWN	¥213	¥230	G1/4	10	18
784-8081	TD-HWP	¥278	¥300	G1/4	10	28
784-8099	TD-KN	¥213	¥230	M12 x 1.0	10	15
784-8102	TD-KP	¥278	¥300	M12 x 1.0	10	25

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO **Air Duster Rate-increase Nozzle**

Stock 38,650 Items



75mm
TD-18-BNL (silver)



TD-18BNL-B (blue)



TD-18BNL-Y (yellow)



TD-18BNL-R (red)

- Features**
- Colors can be managed by the color of the nozzle for each place of use such as the working place of the factory.
 - Inhalation of air in the atmosphere, approximately 4 times the air volume can be obtained. (The amount of air that can be amplified varies depending on the usage environment.)
 - Because of alumite finish, it is strong against rust.
- Origin**
- Taiwan



Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Color	Nozzle Length (mm)	Nozzle Opening Diameter (mm)	Nozzle Mounting Port	SPQ (piece)	Weight (g)
284-3803	TD-18-BNL	¥3,147	¥3,400	Silver	75	16	G1/8	20	54
768-5033	TD18BNL-B	¥3,147	¥3,400	Blue	75	16	G1/8	20	54
768-5050	TD18BNL-Y	¥3,147	¥3,400	Yellow	75	16	G1/8	20	54
768-5041	TD18BNL-R	¥3,147	¥3,400	Red	75	16	G1/8	20	54

Contact us: 0120-509-849 <http://www.orange-book.com/>

KINKI **Air Duster Rate-increase Nozzle**

Stock 102 Items



75mm
K-601-DXN

- Features**
- Replacement is free according to applications.
- Origin**
- Japan

TRUSCO **Air Duster Rate-increase Nozzle** RoHS

Stock 38,650 Items



47mm
TD-18-BN

- Features**
- About 2.7 times the air comes out from the normal air amount.
- Origin**
- Japan

Order Unit: 1 Piece (Price revision date: Apr, 2015) KINKI SEISAKUSYO

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nozzle Length (mm)	Nozzle Opening Diameter (mm)	Nozzle Mounting Port	SPQ (piece)	Weight (g)
103-5550	K-601-DXN	¥3,055	¥3,300	75	16	G1/8	10	54

Contact us: 06-6700-2601 <http://www.kinki-seisakusho.co.jp/>

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nozzle Length (mm)	Nozzle Opening Diameter (mm)	Nozzle Mounting Port	SPQ (piece)	Weight (g)
228-0671	TD-18-BN	¥2,462	¥2,660	47	15	G1/8	10	24

Contact us: 0120-509-849 <http://www.orange-book.com/>