

The number next to the logo mark indicates items in stock for each brand.

Please wear protective equipment to use safely.



Stock 38,650 Items

Cutting Whetstone "TOKUMARU Cut" Economical Type



TMC-105

- Features**
- A thin type whetstone of 1mm.
 - Wonderful biting and sharpness.
 - Burr are minimal.
- Use**
- For cutting thin sheets, thin bars, and ALC, etc. of metals in general such as iron and stainless steel.
- Specs**
- Working Tool: Disk Grinder, Grindstone Cutting Machine
- Origin**
- China



Order Unit: 10 Sheets

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Q'ty Per Pack (sheet)	Abrasive	Grain Size (#)	Hardness	Outer Diameter x Blade Thickness x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Weight (g)
365-5857	TMC-105	¥138*	¥170*	10	AX	46	S	105 x 1.0 x 15.0	14400	24

Contact us:0120-509-849 <http://www.orange-book.com/>



Stock 38,650 Items

Cutting Whetstone "Eco Sharp Cut R"



ES-105R

- Features**
- Tough and sharp. It enhances safety with a double-sided cross reinforcement and demonstrates excellent sharpness.
- Use**
- For cutting iron and stainless steel, etc.
- Specs**
- Working Tool: Disk Grinder (ES-105R, ES-180R), Whetstone Cutting Machine

Item No.	Origin
ES-105R	Japan
ES-180R	Japan
ES-305R	China
ES-355R	China
ES-405R	China

Order by package Q'ty

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Q'ty Per Pack (sheet)	Abrasive	Grain Size (#)	Hardness	Outer Diameter x Blade Thickness x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Weight (g)
859-0639	ES-105R	¥194*	¥240*	10	5A	60	S	105 x 0.8 x 15.0	14400	25
859-0640	ES-180R	¥365*	¥450*	10	A	46	R	180 x 2.0 x 22.0	7600	117
859-0641	ES-305R	¥446*	¥550*	25	A	36	R	305 x 2.8 x 25.4	4490	470
859-0642	ES-355R	¥648*	¥800*	25	A	36	R	355 x 3.0 x 25.4	3850	670
859-0643	ES-405R	¥729*	¥900*	25	A	30	R	405 x 3.0 x 25.4	2980	910

Contact us:0120-509-849 <http://www.orange-book.com/>



Stock 755 Items

Cutting Whetstone "Theta Cut"



SCT1071NX60S

- Features**
- A straight type double-sided reinforcement cutting whetstone.
 - Realizes sharp cuts where the difference can be felt with the first cut that is made.
- Use**
- For cutting of metal in general, small diameter round bars, pipes, steel members, angular members, and galvanized iron, etc.
- Specs**
- Working Tool: Disk Grinder
- Origin**
- Japan



Warning

- Outer diameters of 180mm and 205mm are not compatible for use with castings.

Order Unit: 10 Sheets

NEWREGISTON Co.Ltd.

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Q'ty Per Pack (sheet)	Abrasive	Grain Size (#)	Hardness	Outer Diameter x Blade Thickness x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Weight (g)
353-3981	SCT1071NX60S	¥168*	-	10	NX	60	S	107 x 1.0 x 15.0	14200	25
835-5013	SCT12513NX60S	¥378*	-	10	NX	60	S	125 x 1.3 x 22.0	12000	37
835-5014	SCT15014NX46S	¥513*	-	10	NX	46	S	150 x 1.4 x 22.0	10000	62
835-5015	SCT18015NX46S	¥581*	-	10	NX	46	S	180 x 1.5 x 22.0	8400	94
835-5016	SCT20516NX46S	¥696*	-	10	NX	46	S	205 x 1.6 x 22.0	7400	127

Contact us:0120-466-300 <http://www.newregiston.co.jp/>



Stock 755 Items

Cutting Whetstone "Theta Mini"



SM581NX60S (theta mini 58)

- Features**
- An exclusive whetstone for the NEWREGISTON "RAIJIN" and "KUUJIN."
 - A small diameter size suitable for narrow spots and small areas.
- Origin**
- Japan

Theta Mini 58

Order Unit: 10 Sheets

NEWREGISTON Co.Ltd.

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Q'ty Per Pack (sheet)	Abrasive	Grain Size (#)	Hardness	Outer Diameter x Blade Thickness x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Weight (g)
835-5017	SM581NX60S	¥303*	-	10	NX	60	S	58 x 1 x 9.53	23700	6

Theta Mini 75

Order Unit: 10 Sheets

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Q'ty Per Pack (sheet)	Abrasive	Grain Size (#)	Hardness	Outer Diameter x Blade Thickness x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Weight (g)
835-5018	SM751NX60S	¥349*	-	10	NX	60	S	75 x 1 x 9.53	18300	10

Contact us:0120-466-300 <http://www.newregiston.co.jp/>