

For Disc Grinders, see p. 5-209 to 226

The number next to the logo mark indicates items in stock for each brand.

TRUSCO



Stock 38,650 Items

Bevel Disc



Features

- Since it is processed into an umbrella type special shape, the tip of the disc always hits the work and it can make a beautiful finish.
- Low clogging and there is no welding of nylon.

Specs

- Max Working Peripheral Velocity: 59.7m/s (3580m/min)

Materials

- Nylon non woven fabric

Origin

- Japan

Grinding Wheels

Disk Papers

Papers for Double Action Sander

Nylon Discs

Urethane Discs

Felt Discs

Diamond Wheels

Grinding Wheels

Dressers

Flap Wheels

Nylon Wheel with Shaft

Shank Mounted Felt Wheels with Shaft

Bands

Shank Mounted Stones

Carbide Bars

Diamond Bars

CBN Bars

Files

Diamond Files

Grinding Stones

Abrasives

Sheet Sanding Papers

Abrasive Belts

Cup Brushes

Wheel Brushes with Shank

Hand Brushes



TBD-100BK (screw-in type)



TBD-100BR (screw-in type)



TBD-100R (screw-in type)



TBD-100GN (screw-in type)



TBD-100BL (screw-in type)



TBD-100PI (screw-in type)



TBD-100YE (screw-in type)



TBD-10015BK (hole type)



TBD-10015BR (hole type)



TBD-10015R (hole type)



TBD-10015GN (hole type)



Item No.	Use
TBD-100BK, TBD-10015BK	Such as hard rust removal, black-dyed removal, and rust removal works.
TBD-100BR, TBD-10015BR	Burning, removal of oxide film, coat stripping, etc.
TBD-100R, TBD-10015R	For rust removal, peel off coating.
TBD-100GN, TBD-10015GN	Stainless steel finish, roughening (foot attaching) before painting/bonding.
TBD-100BL, TBD-100PI, TBD-100YE	To ground polishing before mirror surface finishing.

Screw-in type, containing 1 piece

Features

- M10 screw, can be removed in the grinder with one touch.

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Grain Size (#)	Color	Outer Diameter x Thickness x Thread Diameter (mm)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
829-1361	TBD-100BK-1P	¥1,539	¥1,900	Equivalent to 120	Black	95 x 12 x M10 (P1.5)	12000	10	70
829-1362	TBD-100BR-1P	¥1,134	¥1,400	Equivalent to 180	Brown	95 x 12 x M10 (P1.5)	12000	10	64
829-1363	TBD-100R-1P	¥1,134	¥1,400	Equivalent to 320	Red	95 x 11 x M10 (P1.5)	12000	10	48
829-1364	TBD-100GN-1P	¥1,134	¥1,400	Equivalent to 400	Green	95 x 11 x M10 (P1.5)	12000	10	42
829-1365	TBD-100BL-1P	¥1,134	¥1,400	Equivalent to 600	Blue	95 x 11 x M10 (P1.5)	12000	10	42
829-1366	TBD-100PI-1P	¥1,134	¥1,400	Equivalent to 800	Pink	95 x 11 x M10 (P1.5)	12000	10	42
829-1367	TBD-100YE-1P	¥1,134	¥1,400	Equivalent to 1000	Yellow	95 x 11 x M10 (P1.5)	12000	10	42

Screw-in type, containing 5 pieces

Features

- M10 screw, can be removed in the grinder with one touch.

Order Unit: 1 Box

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Color	Outer Diameter x Thickness x Thread Diameter (mm)	Max Working Rotation Speed (rpm)	Q'ty Per Box (piece)	SPQ (box)	Weight (g/box)
445-8214	TBD-100BK	¥6,480	¥8,000	Equivalent to 120	Black	95 x 12 x M10 (P1.5)	12000	5	20	350
445-8222	TBD-100BR	¥5,184	¥6,400	Equivalent to 180	Brown	95 x 12 x M10 (P1.5)	12000	5	20	320
445-8231	TBD-100R	¥5,184	¥6,400	Equivalent to 320	Red	95 x 11 x M10 (P1.5)	12000	5	20	240
445-8249	TBD-100GN	¥5,184	¥6,400	Equivalent to 400	Green	95 x 11 x M10 (P1.5)	12000	5	20	210
770-1292	TBD-100BL	¥5,184	¥6,400	Equivalent to 600	Blue	95 x 11 x M10 (P1.5)	12000	5	20	270
769-2901	TBD-100PI	¥5,184	¥6,400	Equivalent to 800	Pink	95 x 11 x M10 (P1.5)	12000	5	20	270
769-2919	TBD-100YE	¥5,184	¥6,400	Equivalent to 1000	Yellow	95 x 11 x M10 (P1.5)	12000	5	20	270

Hole type, containing 5 pieces

Features

- High flexibility, familiar well on uneven surfaces, does not over cut the work.
- Can be safely used without worry of wire scattering like wire brush.
- Since the mounting sole diameter is 15mm, it can be used with both electric and pneumatic grinders.

Order Unit: 1 Box

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Color	Outer Diameter x Thickness x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Q'ty Per Box (piece)	SPQ (box)	Weight (g/box)
471-9662	TBD-10015BK	¥7,128	¥8,800	Equivalent to 120	Black	95 x 12 x 15	12000	5	20	350
471-9671	TBD-10015BR	¥5,184	¥6,400	Equivalent to 180	Brown	95 x 12 x 15	12000	5	20	320
471-9689	TBD-10015R	¥5,184	¥6,400	Equivalent to 320	Red	95 x 11 x 15	12000	5	20	240
471-9697	TBD-10015GN	¥5,184	¥6,400	Equivalent to 400	Green	95 x 11 x 15	12000	5	20	210

Estimated Unit Price per Piece
¥1,037 to ¥1,426

Contact us: 0120-509-849 <http://www.orange-book.com/>