

For Disc Grinders, see p. 5-209 to 226/For Oil Polishing Abrasives, see p. 5-1023 to 1025

TRUSCO Stock 38,650 Items

"Beveled Disc Felt" (direct screw-in type)



- Features**
- Since it is processed into an umbrella type special shape, the tip of the disc always hits the work and it can make a beautiful finish.
 - It has high flexibility and fits nicely on the work.
 - M10 screw, can be removed in the grinder with one touch.
- Use**
- For glossing and creating mirror finishes on iron and stainless steel by applying an oil polishing agent (blue bar, etc.).
- Specs**
- Max Working Peripheral Velocity: 59.7m/s (3580m/min)
 - Max Working Rotation Speed: 12000rpm
- Origin**
- Japan

Contains 1 disc

Order Unit: 1 Sheet

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Outer Diameter x Thickness x Thread Diameter (mm)	SPQ (sheet)	Weight (g)
835-6132	TBD-100F-1P	¥1,377	¥1,700	95 x 10 x M10 (P1.5)	10	58

Contains 5 discs

Order Unit: 1 Box

Order Code	Item No.	Price (per box)	MSRP (per box)	Outer Diameter x Thickness x Thread Diameter (mm)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
470-2654	TBD-100F	¥6,334	¥7,820	95 x 10 x M10 (P1.5)	5	20	290

Contact us:0120-509-849 <http://www.orange-book.com/>



Package containing 1 disc

Including 5 sheets

Estimated Unit Price per Sheet
¥1,267

TRUSCO Stock 38,650 Items

"Felt Disc" (directly threaded type)



- Features**
- Use oil-and-fat composition (green rouge, white bar, Tripoli) according to the application, and make a mirror surface finish.
- Use**
- Mirror surface finish polishing, glazing, wiping work.
- Specs**
- Max Working Peripheral Velocity: 41.9m/s (2512m/min)
- Origin**
- Japan

Hard Type

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per box)	MSRP (per box)	Outer Diameter x Thickness x Thread Diameter (mm)	Max Working Rotation Speed (rpm)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
216-2032	FD100AL-H	¥7,938	¥9,800	100 x 10 x M10 (P1.5)	8000	5	20	330

Soft Type

Order Unit: 1 Box

Order Code	Item No.	Price (per box)	MSRP (per box)	Outer Diameter x Thickness x Thread Diameter (mm)	Max Working Rotation Speed (rpm)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
216-2041	FD100AL-S	¥5,184	¥6,400	100 x 10 x M10 (P1.5)	8000	5	1	290

Contact us:0120-509-849 <http://www.orange-book.com/>

Estimated Unit Price per Sheet
¥1,037 to ¥1,588

TRUSCO Stock 38,650 Items

"GP Sander Felt." (directly threaded type/for wiping)



- Features**
- Use oil-and-fat composition according to the application, and make a mirror surface finish.
 - 6 mm shaft adapter and it can be used also for straight grinder.
- Use**
- Optimum for surface polishing and mirror surface finishing.
- Specs**
- Max Working Peripheral Velocity: 36.6m/s (2198m/min)
- Accessories**
- 6mm Shaft Adapters 1 piece per box (sold separately item no.: GPS-J6-1P)
- Origin**
- Japan



6mm Shaft Adapters (Item No.: GPS-J6-1P)

Hard Type

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per box)	MSRP (per box)	Outer Diameter x Thickness x Thread Diameter (mm)	Max Working Rotation Speed (rpm)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
114-6530	GPSF10025H	¥21,238	¥26,220	100 x 25 x M10 (P1.5)	7000	5	20	520

Soft Type

Order Unit: 1 Box

Order Code	Item No.	Price (per box)	MSRP (per box)	Outer Diameter x Thickness x Thread Diameter (mm)	Max Working Rotation Speed (rpm)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
114-6548	GPSF10025S	¥15,172	¥18,730	100 x 25 x M10 (P1.5)	7000	5	20	400

Contact us:0120-509-849 <http://www.orange-book.com/>

Estimated Unit Price per Sheet
¥3,035 to ¥4,248