

# Diamond Bars (shank diameter 6mm)

Stock 954 Items

5-1195

Prices displayed include 8% tax.

For Micro Grinders, see p. 5-242 to 268

TRUSCO Stock 38,650 Items

## Diamond Bar



Specs •Cutting Diameter x Blade Length x Total Length: 15.0 x 10.0 x 80.0mm  
•Grain Size: #100 •Shaft diameter: 6mm Origin •Japan




T6-210C

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
128-5068	T6-210C	¥4,075	¥5,030	45000	1	28.4

Specs •Cutting Diameter x Blade Length x Total Length: 6.5 x 15.0 x 60.0mm  
•Grain Size: #100 •Shaft diameter: 6mm Origin •Japan




T6-202C

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
128-4894	T6-202C	¥1,863	¥2,300	50000	1	13.1

Specs •Cutting Diameter x Blade Length x Total Length: 8.0 x 15.0 x 60.0mm  
•Grain Size: #100 •Shaft diameter: 6mm Origin •Japan



T6-302C

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
299-7070	T6-302C	¥2,925	¥3,610	50000	1	14.8

Specs •Cutting Diameter x Blade Length x Total Length: 10.0 x 15.0 x 60.0mm  
•Grain Size: #100 •Shaft diameter: 6mm Origin •Japan



T6-402C

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
299-7088	T6-402C	¥3,240	¥4,000	50000	1	17.7

Specs •Cutting Diameter x Blade Length x Total Length: 6.5 x 22.0 x 60.0mm  
•Grain Size: #100 •Shaft diameter: 6mm Origin •Japan



T6-203C

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
128-4908	T6-203C	¥2,066	¥2,550	50000	1	12.4

Specs •Cutting Diameter x Blade Length x Total Length: 8.0 x 22.0 x 60.0mm  
•Grain Size: #100 •Shaft diameter: 6mm Origin •Japan



T6-303C

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
299-7096	T6-303C	¥2,106	¥2,600	50000	1	15.4

Specs •Cutting Diameter x Blade Length x Total Length: 10.0 x 22.0 x 60.0mm  
•Grain Size: #100 •Shaft diameter: 6mm Origin •Japan



T6-403C

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
299-7100	T6-403C	¥2,268	¥2,800	50000	1	20.3

Specs •Cutting Diameter x Total Length: 6.0 x 60.0mm  
•Grain Size: #100 •Shaft diameter: 6mm Origin •Japan




T6-301C

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
299-7053	T6-301C	¥1,863	¥2,300	100000	1	11.3

Specs •Cutting Diameter x Total Length: 8.0 x 60.0mm  
•Grain Size: #100 •Shaft diameter: 6mm Origin •Japan



T6-201C

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
128-4886	T6-201C	¥1,863	¥2,300	100000	1	12.5

Specs •Cutting Diameter x Total Length: 10.0 x 60.0mm  
•Grain Size: #100 •Shaft diameter: 6mm Origin •Japan



T6-401C

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
299-7061	T6-401C	¥2,025	¥2,500	100000	1	15.6

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items

## 5 Pieces Diamond Bar Set



T6-S5 (in a plastic case)

Features •For carbide alloys and non-metals such as glass and ceramics.  
•Realizes great shortening of processing time.  
•Uses selected natural diamonds of good shape. By our proprietary electro deposition technology, diamond particles are firmly adhered and proud of an outstanding long life.

Set Contents •T6-201C x 1 Piece •T6-202C x 1 Piece •T6-203C x 1 Piece •T6-204C x 1 Piece •T6-205F x 1 Piece  
Origin •Japan

Order Unit: 1 Set TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per set)	MSRP (per set)	Q'ty Per Set (piece)	SPQ (set)	Weight (g/set)
128-4835	T6-S5	¥10,044	¥12,400	5	1	98.1

Contact us: 0120-509-849 <http://www.orange-book.com/>

Abrasives

Grinding Wheels

Disk Papers

Papers for Double Action Sander

Nylon Discs

Urethane Discs

Felt Discs

Diamond Wheels

Grinding Wheels

Dressers

Flap Wheels

Nylon Wheel with Shaft

Shank Mounted Felt Wheels with Shaft

Bands

Shank Mounted Stones

Carbide Bars

Diamond Bars

CBN Bars

Files

Diamond Files

Grinding Stones

Abrasives

Sheet Sanding Papers

Abrasive Belts

Cup Brushes

Wheel Brushes with Shank

Hand Brushes