

The number next to the logo mark indicates items in stock for each brand.

- Desks
- PC Desks
- Meeting Tables
- Cafeteria Tables
- Office Chairs
- Meeting Chairs
- Working Chairs
- Anti-Static Stools
- Benches
- Umbrella Stands
- Reception Room Furnitures
- Hanger Racks
- Partitions
- Book Cabinets
- Counters
- Filing Cabinets
- Catalog Cases
- Map Cases/Letter Cases
- Pamphlet Stands
- File Wagons
- Lockers
- Shoes Boxes
- Safes
- Mailboxes
- Key Boxes
- Window Films
- Interior Blinds
- OA Floors
- System Kitchens



Stock 38,650 Items

Low Partition



- Features**
- Available in a rich variety of sizes for both width and height.
 - Flexible layout is possible by using self-supporting/connecting parts.
 - Simplified connection enables easy construction.
- Specs**
- Panel thickness: 30mm
- Materials**
- Panel fram: Vinyl chloride molded item
- Origin**
- Japan



Translucent type with transparency (polycarbonate)

Warning

- Stabilizer feet, connecting members, etc. are not included in the panel main body.



TLP-1209U-B (upper part translucent and height 1200mm type/blue)



TLP-1509U-GN (rupper part translucent and height 1500mm type/green)



TLP-1809U-GY (upper part translucent and height 1800mm type/gray)



TLP-1509F (full translucent type/translucent)



TLP-1509H-OR (vertical half translucent type/orange)

Upper part translucent and height 1200mm type

Order Unit: 1 Sheet | Factory direct | No freight charge | Excluding remote islands | TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Color	W x D x H (mm)	Type	SPQ (sheet)	Weight (kg)
★764-9207	TLP-1209U-B	¥37,179	¥45,900	Blue	900 x 30 x 1165	Connected Type	1	4.5
★764-9215	TLP-1209U-GN	¥37,179	¥45,900	Green	900 x 30 x 1165	Connected Type	1	4.5
★764-9223	TLP-1209U-GY	¥37,179	¥45,900	Gray	900 x 30 x 1165	Connected Type	1	4.5
★764-9231	TLP-1209U-OR	¥37,179	¥45,900	Orange	900 x 30 x 1165	Connected Type	1	4.5
★764-9291	TLP-1212U-B	¥43,416	¥53,600	Blue	1200 x 30 x 1165	Connected Type	1	6.5
★764-9304	TLP-1212U-GN	¥43,416	¥53,600	Green	1200 x 30 x 1165	Connected Type	1	6.5
★764-9312	TLP-1212U-GY	¥43,416	¥53,600	Gray	1200 x 30 x 1165	Connected Type	1	6.5
★764-9321	TLP-1212U-OR	¥43,416	¥53,600	Orange	1200 x 30 x 1165	Connected Type	1	6.5

Upper part translucent and height 1500mm type

Order Unit: 1 Sheet | Factory direct | No freight charge | Excluding remote islands | TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Color	W x D x H (mm)	Type	SPQ (sheet)	Weight (kg)
★764-9541	TLP-1509U-B	¥44,793	¥55,300	Blue	900 x 30 x 1465	Connected Type	1	6
★764-9550	TLP-1509U-GN	¥44,793	¥55,300	Green	900 x 30 x 1465	Connected Type	1	6
★764-9568	TLP-1509U-GY	¥44,793	¥55,300	Gray	900 x 30 x 1465	Connected Type	1	6
★764-9576	TLP-1509U-OR	¥44,793	¥55,300	Orange	900 x 30 x 1465	Connected Type	1	6
★764-9631	TLP-1512U-B	¥50,139	¥61,900	Blue	1200 x 30 x 1465	Connected Type	1	9
★764-9649	TLP-1512U-GN	¥50,139	¥61,900	Green	1200 x 30 x 1465	Connected Type	1	9
★764-9657	TLP-1512U-GY	¥50,139	¥61,900	Gray	1200 x 30 x 1465	Connected Type	1	9
★764-9665	TLP-1512U-OR	¥50,139	¥61,900	Orange	1200 x 30 x 1465	Connected Type	1	9

Upper part translucent and height 1800mm type

Order Unit: 1 Sheet | Factory direct | No freight charge | Excluding remote islands | TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Color	W x D x H (mm)	Type	SPQ (sheet)	Weight (kg)
★764-9801	TLP-1809U-B	¥50,382	¥62,200	Blue	900 x 30 x 1765	Connected Type	1	7
★764-9819	TLP-1809U-GN	¥50,382	¥62,200	Green	900 x 30 x 1765	Connected Type	1	7
★764-9827	TLP-1809U-GY	¥50,382	¥62,200	Gray	900 x 30 x 1765	Connected Type	1	7
★764-9835	TLP-1809U-OR	¥50,382	¥62,200	Orange	900 x 30 x 1765	Connected Type	1	7
★764-9894	TLP-1812U-B	¥60,426	¥74,600	Blue	1200 x 30 x 1765	Connected Type	1	10
★764-9908	TLP-1812U-GN	¥60,426	¥74,600	Green	1200 x 30 x 1765	Connected Type	1	10
★764-9916	TLP-1812U-GY	¥60,426	¥74,600	Gray	1200 x 30 x 1765	Connected Type	1	10
★764-9924	TLP-1812U-OR	¥60,426	¥74,600	Orange	1200 x 30 x 1765	Connected Type	1	10

Full translucent type

Order Unit: 1 Sheet | Factory direct | No freight charge | Excluding remote islands | TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Color	W x D x H (mm)	Type	SPQ (sheet)	Weight (kg)
★764-9193	TLP-1209F	¥41,229	¥50,900	Translucent	900 x 30 x 1165	Connected Type	1	4.0
★764-9282	TLP-1212F	¥47,466	¥58,600	Translucent	1200 x 30 x 1165	Connected Type	1	6.0
★764-9495	TLP-1509F	¥44,307	¥54,700	Translucent	900 x 30 x 1465	Connected Type	1	5.5
★764-9622	TLP-1512F	¥53,946	¥66,600	Translucent	1200 x 30 x 1465	Connected Type	1	7.0
★764-9754	TLP-1809F	¥49,734	¥61,400	Translucent	900 x 30 x 1765	Connected Type	1	6.0
★764-9886	TLP-1812F	¥60,426	¥74,600	Translucent	1200 x 30 x 1765	Connected Type	1	10.0

Vertical half translucent type

Order Unit: 1 Sheet | Factory direct | No freight charge | Excluding remote islands | TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Color	W x D x H (mm)	Type	SPQ (sheet)	Weight (kg)
★764-9509	TLP-1509H-B	¥49,005	¥60,500	Blue	900 x 30 x 1465	Connected Type	1	6
★764-9517	TLP-1509H-GN	¥49,005	¥60,500	Green	900 x 30 x 1465	Connected Type	1	6
★764-9525	TLP-1509H-GY	¥49,005	¥60,500	Gray	900 x 30 x 1465	Connected Type	1	6
★764-9533	TLP-1509H-OR	¥49,005	¥60,500	Orange	900 x 30 x 1465	Connected Type	1	6
★764-9762	TLP-1809H-B	¥50,382	¥62,200	Blue	900 x 30 x 1765	Connected Type	1	7
★764-9771	TLP-1809H-GN	¥50,382	¥62,200	Green	900 x 30 x 1765	Connected Type	1	7
★764-9789	TLP-1809H-GY	¥50,382	¥62,200	Gray	900 x 30 x 1765	Connected Type	1	7
★764-9797	TLP-1809H-OR	¥50,382	¥62,200	Orange	900 x 30 x 1765	Connected Type	1	7

Contact us: 0120-509-849 <http://www.orange-book.com/>