

# Wall Surface Bookshelves (depth 450mm type)

For Bases, see p. 10-142

The number next to the logo mark indicates items in stock for each brand.

**TRUSCO** Stock 38,650 Items **U-shaped Wall Surface Bookshelf (steel double sliding door)** **Finished Goods** **Heavy Caution**



- Specs**
- Color: White
  - With Screw for Connection
- Materials**
- Steel
- Origin**
- Japan

**Warning**

- When using both the top and bottom placing type as a bottom placing type, please use the base (UBW-06). (However, since the USW-18 has an adjuster, the base can not be used.)

Order Unit: 1 Piece | Factory direct | Freight: ¥2,000 | Excluding remote islands | **TRUSCO NAKAYAMA CORPORATION**

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Load Capacity (kg/piece)	Equal Load Capacity (kg/stage)	W x D x H (mm)	Installation Type	Accessories	Shelf Board Pitch (mm)	Additional Shelf Board	Weight (kg)
★765-8320	USW-4	¥33,141	¥35,800	60	60	900 x 450 x 380	Designated for top placing	-	-	-	17
★765-8338	USW-7	¥36,658	¥39,600	120	60	900 x 450 x 720	For both top/bottom placing	Cylinder Lock, Shelf Board x 1	16.75	UW-01TS	33
★765-8290	USW-11	¥44,712	¥48,300	180	60	900 x 450 x 1050	For both top/bottom placing	Cylinder Lock, Shelf Board x 2	16.75	UW-01TS	40
★765-8303	USW-18	¥78,963	¥85,300	200	60	900 x 450 x 1830	Designated for bottom placing	Cylinder Lock, Shelf Board x 4, Adjuster	16.75	UW-01TS	70
★765-8311	USW-21	¥79,519	¥85,900	200	60	900 x 450 x 2100	Designated for bottom placing	Cylinder lock, 5 shelf boards	16.75	UW-01TS	74

Contact us: 0120-509-849 <http://www.orange-book.com/>

**TRUSCO** Stock 38,650 Items **U-shaped Wall Surface Bookshelf (steel sliding door, 3-door type)** **Finished Goods**



- Features**
- The opening is larger as compared to the USW type and you can smoothly put in and take out stored objects at the center part.
- Specs**
- Color: White
  - With Screw for Connection
- Materials**
- Steel
- Origin**
- Japan

**Warning**

- When using the dual purpose type for top and bottom placing as a bottom placing type, please use the base (UBW-06).

Order Unit: 1 Piece | Factory direct | Freight: ¥2,000 | Excluding remote islands | **TRUSCO NAKAYAMA CORPORATION**

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Load Capacity (kg/piece)	Equal Load Capacity (kg/stage)	W x D x H (mm)	Installation Type	Accessories	Shelf Board Pitch (mm)	Additional Shelf Board	Weight (kg)
★765-8281	USSW-7	¥50,914	¥55,000	120	60	900 x 450 x 720	For both top/bottom placing	Cylinder lock, 1 shelf board	16.75	UW-01TS	29
★765-8273	USSW-11	¥58,783	¥63,500	180	60	900 x 450 x 1050	For both top/bottom placing	Cylinder lock, 2 shelf boards	16.75	UW-01TS	39

Contact us: 0120-509-849 <http://www.orange-book.com/>

**TRUSCO** Stock 38,650 Items **U-shaped Wall Surface Bookshelf (personal locker)** **Finished Goods**



- Specs**
- Color: White
  - With Screw for Connection
- Materials**
- Steel
- Origin**
- Japan

**Warning**

- The base (UBW-06) will be required.
- For the IC lock type, an IC registration/deletion card is attached to each compartment.
- Please use the IC card you have.

Order Unit: 1 Piece | Factory direct | Freight: ¥2,000 | Excluding remote islands | **TRUSCO NAKAYAMA CORPORATION**

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Load Capacity (kg/piece)	W x D x H (mm)	Installation Type	Key type	Inlet	Weight (kg)
★765-8125	ULW-11	¥70,354	¥76,000	180	900 x 450 x 1050	Designated for bottom placing	Cylinder Lock	None	38.8
★765-8117	ULPW-11	¥76,834	¥83,000	180	900 x 450 x 1050	Designated for bottom placing	Cylinder Lock	Yes	38.8
★769-3478	ULW-11-IC	¥222,171	¥240,000	180	900 x 450 x 1050	Designated for bottom placing	IC lock	None	39.3
★769-3460	ULPW-11-IC	¥224,949	¥243,000	180	900 x 450 x 1050	Designated for bottom placing	IC lock	Yes	39.3

Contact us: 0120-509-849 <http://www.orange-book.com/>