

# Standard Bookshelves (depth 400mm type)

10-151

Office Furniture

Prices displayed include 8% tax. For Bases, see p. 10-152/For Shelf Boards and Fall Prevention Metal Fittings, see p. 10-164 to 165

TRUSCO **Stock** 38,650 Items

## Double Door Bookshelf (A4 type)

Finished Goods **Heavy Caution**

Com Green Purchasing Chemical Content Inspection

Com Drawing

Specs •Color: Neon Gray •Compatible Type Fall Prevention Metal Fittings: TK/NTK Type  
Materials •Steel  
Origin •Japan

Warning

•When using the dual purpose type for top and bottom placing as a bottom placing type, please use the base (FB40-G06).



FH40-G4



FH40-G7



FH40-G11



FH40-G19

Order Unit: 1 Piece | Factory direct | Freight: ¥2,000 | Excluding remote islands

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Load Capacity (kg/piece)	Equal Load Capacity (kg/stage)	W x D x H (mm)	Installation Type	Accessories	Shelf Board Pitch (mm)	Additional Shelf Board	Weight (kg)
★520-6596	FH40-G4	¥23,791	¥25,700	60	-	880 x 400 x 390	Designated for top placing	Cylinder Lock	-	-	10.5
★520-6626	FH40-G7	¥35,918	¥38,800	120	60	880 x 400 x 750	For both top/bottom placing	Cylinder Lock, Shelf Board x 1	30	N-33	19.0
★520-6685	FH40-G11	¥40,176	¥43,400	180	60	880 x 400 x 1110	For both top/bottom placing	Cylinder Lock, Shelf Board x 2	30	N-33	28.0
★520-6804	FH40-G19	¥56,191	¥60,700	200	60	880 x 400 x 1860	Designated for bottom placing	Cylinder Lock, Shelf Board x 4	30	N-33	47.0

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock** 38,650 Items

## Glass Sliding Door Bookshelf (A4 type)

Finished Goods **Heavy Caution**

Com Green Purchasing Chemical Content Inspection

Com Drawing

Specs •Color: Neon Gray •Compatible Type Fall Prevention Metal Fittings: TK/NTK Type  
Materials •Steel  
Origin •Japan

Warning

•When using as a bottom placing type, please use the bases (FB40-G06, FB40-G06W).



FJG40-G7



FJG40-G7W (files sold separately)



FJG40-G11



FJG40-G11W (files sold separately)

Order Unit: 1 Piece | Factory direct | Freight: ¥2,000 | Excluding remote islands

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Load Capacity (kg/piece)	Equal Load Capacity (kg/stage)	W x D x H (mm)	Installation Type	Accessories	Shelf Board Pitch (mm)	Additional Shelf Board	Weight (kg)
★520-6669	FJG40-G7	¥36,566	¥39,500	120	60	880 x 400 x 750	For both top/bottom placing	Cylinder lock, 1 shelf board	30	N-33	21
★520-6677	FJG40-G7W	¥56,006	¥60,500	200	60	1760 x 400 x 750	For both top/bottom placing	Cylinder lock, 2 shelf boards	30	N-33	43
★520-6731	FJG40-G11	¥45,175	¥48,800	180	60	880 x 400 x 1110	For both top/bottom placing	Cylinder lock, 2 shelf boards	30	N-33	29
★520-6740	FJG40-G11W	¥75,261	¥81,300	200	60	1760 x 400 x 1110	For both top/bottom placing	Cylinder lock, 4 shelf boards	30	N-33	60

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock** 38,650 Items

## Steel Sliding Door Bookshelf (A4 type)

Finished Goods

Com Green Purchasing Chemical Content Inspection

Com Drawing

Specs •Color: Neon Gray •Compatible Type Fall Prevention Metal Fittings: TK/NTK Type  
Materials •Steel  
Origin •Japan

Warning

•When using the dual purpose type for top and bottom placing as a bottom placing type, please use the base (FB40-G06).



N103D



N106D



FS40-G7

Order Unit: 1 Piece | Factory direct | Freight: ¥2,000 | Excluding remote islands

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Load Capacity (kg/piece)	Equal Load Capacity (kg/stage)	W x D x H (mm)	Installation Type	Accessories	Shelf Board Pitch (mm)	Additional Shelf Board	Weight (kg)
★520-6600	N103D	¥17,774	¥19,200	60	-	880 x 400 x 390	Designated for top placing	-	-	-	12.5
★520-6618	N106D	¥31,289	¥33,800	60	-	1760 x 400 x 390	Designated for top placing	-	-	-	24.6
★520-6634	FS40-G7	¥32,122	¥34,700	120	60	880 x 400 x 750	For both top/bottom placing	Cylinder lock, 1 shelf board	30	N-33	21.0

Contact us: 0120-509-849 <http://www.orange-book.com/>