

10-156 Standard Bookshelves (depth 400mm type)

For Shelf Boards and Fall Prevention Metal Fittings, see p. 10-164 to 165 The number next to the logo mark indicates items in stock for each brand.

Office Furniture

- Desks
- PC Desks
- Meeting Tables
- Cafeteria Tables
- Office Chairs
- Meeting Chairs
- Working Chairs
- Anti-Static Stools
- Benches
- Umbrella Stands
- Reception Room Furnitures
- Hanger Racks
- Partitions
- Book Cabinets
- Counters
- Filing Cabinets
- Catalog Cases
- Map Cases·Letter Cases
- Pamphlet Stands
- File Wagons
- Lockers
- Shoes Boxes
- Safes
- Mailboxes
- Key Boxes
- Window Films
- Interior Blinds
- OA Floors
- System Kitchens

Stock
38,650 Items

Bookshelf



Specs • Compatible Type Fall Prevention Metal Fittings: TK/NTK Type
Materials • Steel
Origin • Japan

N603G (glass sliding door bookshelf: neo gray) (files sold separately)
N603D (steel sliding door bookshelf: neo gray) (files sold separately)

Order Unit: 1 Piece | Factory direct | Freight: ¥2,000 | Excluding remote islands | TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Load Capacity (kg/piece)	Equal Load Capacity (kg/stage)	W x D x H (mm)	Installation Type	Accessories	Shelf Board Pitch (mm)	Additional Shelf Board	Weight (kg)
★511-8981	N603G	¥47,304	¥51,100	200	60	880 x 400 x 1790	Designated for bottom placing	Cylinder Lock, Shelf Board x 4	30	N-33	54.3
★520-7754	N603D	¥43,323	¥46,800	200	60	880 x 400 x 1790	Designated for bottom placing	Cylinder Lock, Shelf Board x 4	30	N-33	51.9

Contact us: 0120-509-849 <http://www.orange-book.com/>

Stock
38,650 Items

Bookshelf Base



Specs • Compatible Type Fall Prevention Metal Fittings: TK/NTK Type
Materials • Steel
Origin • Japan

Base item No.	Compatible Body
303B	N303D, N303G, NP303, W303D, W303G, WT2C35, WT2C45, WT2C65, WTCB333, WTCB343, WTCB363, WP303, FO40-G7, FO40-G11, FH40-G7, FH40-G11, FJG40-G7, FJG40-G11, F540-G7, F540-G11, FR40-G326AP, FR40-G313AP
304B	N304D, N304G, W304D, W304G
305B	N305D, N305G, W305D, W305G
306B	N306D, N306G, W306D, W306G, FJG40-G7W, FJG40-G11W, F540-G7W, F540-G11W
FB40-W06	W303D, W303G, WT2C35, WT2C45, WT2C65, WTCB333, WTCB343, WTCB363, WP303
FB40-W06W	W306D, W306G
FB40-G06	N303D, N303G, NP303, FO40-G7, FO40-G11, FH40-G7, FH40-G11, FJG40-G7, FJG40-G11, F540-G7, F540-G11, FR40-G326AP, FR40-G313AP
FB40-G06W	N306D, N306G, F540-G7W, F540-G7W, FJG40-G7W, FJG40-G7W



Black Specs • Color: Black
 Order Unit: 1 Piece | Factory direct | Freight: ¥1,500 | Excluding remote islands | TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	W x D x H (mm)	Applicable Bookshelf Dimension (mm) W x D	Weight (kg)
★511-9103	303B	¥2,962	¥3,200	874 x 390 x 88	880 x 400	2.0
★507-0287	304B	¥3,703	¥4,000	1194 x 390 x 88	1200 x 400	2.5
★520-7746	305B	¥4,814	¥5,200	1494 x 390 x 88	1500 x 400	3.2
★511-9278	306B	¥5,184	¥5,600	1754 x 390 x 88	1760 x 400	3.7



White Specs • Color: White
 Order Unit: 1 Piece | Factory direct | Freight: ¥1,500 | Excluding remote islands | TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	W x D x H (mm)	Applicable Bookshelf Dimension (mm) W x D	Weight (kg)
★462-6788	FB40-W06	¥6,110	¥6,600	880 x 380 x 60	880 x 400	3
★462-6796	FB40-W06W	¥9,072	¥9,800	1760 x 380 x 60	1760 x 400	5



Neo Gray Specs • Color: Neon Gray
 Order Unit: 1 Piece | Factory direct | Freight: ¥1,500 | Excluding remote islands | TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	W x D x H (mm)	Applicable Bookshelf Dimension (mm) W x D	Weight (kg)
★520-6774	FB40-G06	¥6,110	¥6,600	880 x 380 x 60	880 x 400	3
★520-6782	FB40-G06W	¥9,072	¥9,800	1760 x 380 x 60	1760 x 400	5

Contact us: 0120-509-849 <http://www.orange-book.com/>