

10-160 Standard Bookshelves (depth 380mm type)

For Shelf Boards and Fall Prevention Metal Fittings, see p. 10-164 to 165 The number next to the logo mark indicates items in stock for each brand.

Office Furniture

- Desks
- PC Desks
- Meeting Tables
- Cafeteria Tables
- Office Chairs
- Meeting Chairs
- Working Chairs
- Anti-Static Stools
- Benches
- Umbrella Stands
- Reception Room Furnitures
- Hanger Racks
- Partitions
- Book Cabinets
- Counters
- Filing Cabinets
- Catalog Cases
- Map Cases/Letter Cases
- Pamphlet Stands
- File Wagons
- Lockers
- Shoes Boxes
- Safes
- Mailboxes
- Key Boxes
- Window Films
- Interior Blinds
- OA Floors
- System Kitchens

TRUSCO **Stock 38,650 Items** **Bookshelf** **Finished Goods** **Heavy Caution**

Com eco Green Purchasing Chemical Content Inspection **Com Drawing** Specs •Compatible Type Fall Prevention Metal Fittings: TK/NTK Type
Materials •Steel
Origin •Japan



White Specs •Color: White

Order Unit: 1 Piece | Factory direct | Freight: ¥2,000 | Excluding remote islands | TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Load Capacity (kg/piece)	Equal Load Capacity (kg/stage)	W x D x H (mm)	Installation Type	Accessories	Shelf Board Pitch (mm)	Additional Shelf Board	Weight (kg)
★462-7440	W301	¥18,792	¥20,300	120	40	515 x 380 x 880	Designated for bottom placing	Cylinder Lock, Shelf Board x 2	30	W-23	15.0
★462-7458	W303	¥26,938	¥29,100	180	60	880 x 380 x 880	Designated for bottom placing	Cylinder Lock, Shelf Board x 2	30	W-33	23.8
★462-7571	W603	¥36,288	¥39,200	200	60	880 x 380 x 1790	Designated for bottom placing	Cylinder Lock, Shelf Board x 4	30	W-33	45.0



Neo Gray Specs •Color: Neo Gray

Order Unit: 1 Piece | Factory direct | Freight: ¥2,000 | Excluding remote islands |

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Load Capacity (kg/piece)	Equal Load Capacity (kg/stage)	W x D x H (mm)	Installation Type	Accessories	Shelf Board Pitch (mm)	Additional Shelf Board	Weight (kg)
★511-9146	N301	¥18,792	¥20,300	120	40	515 x 380 x 880	Designated for bottom placing	Cylinder Lock, Shelf Board x 2	30	N-23	15.0
★511-9162	N303	¥26,938	¥29,100	180	60	880 x 380 x 880	Designated for bottom placing	Cylinder Lock, Shelf Board x 2	30	N-33	23.8
★511-9189	N603	¥36,288	¥39,200	200	60	880 x 380 x 1790	Designated for bottom placing	Cylinder Lock, Shelf Board x 4	30	N-33	45.0

Contact us: 0120-509-849 <http://www.orange-book.com/>

NAIKI **Bookshelf** **New** **Finished Goods** **Heavy Caution**

Com eco Green Purchasing Specs •Color: Warm White
Origin •Japan



Order Unit: 1 Piece | Factory direct | Shipping not included |

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Load Capacity (kg/piece)	Equal Load Capacity (kg/stage)	W x D x H (mm)	Installation Type	Accessories	Shelf Board Pitch (mm)	Additional Shelf Board	SPQ (piece)	Weight (kg)
★836-9175	K736N-AW	¥23,513	¥25,400	120	40	515 x 380 x 880	Designated for bottom placing	Cylinder Lock, Shelf Board x 2	30	SS-K73-AW	1	15.0
★836-9176	K336J-AW	¥35,177	¥38,000	120	40	880 x 380 x 880	Designated for bottom placing	Cylinder Lock, Shelf Board x 2	30	SS-D320-AW	1	29.0
★836-9177	K366J-AW	¥48,415	¥52,300	200	40	880 x 380 x 1790	Designated for bottom placing	Cylinder Lock, Shelf Board x 4	30	SS-D320-AW	1	45.6

Contact us: 0120-711-021 <http://www.naiki.co.jp/>