

TRUSCO **Stock 38,650 Items**

"Inside Wagon"



- Features** • Can be stored under desk and easily taken out.
Origin • Japan



TNKK5036W



TNKK9036W



TNKS5036W (with door)



(inside wagon)



(inside wagon with door)

Inside wagon

- Features** • Can be used from both sides seeking to maximize usability.

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Load Capacity (kg/piece)	W x D x H (mm)	Caster Diameter (mm)	Shelf Board Pitch (mm)	SPQ (piece)	Weight (kg)
384-1596	TNKK5036W	¥30,919	¥33,400	40	500 x 360 x 615	20	20	1	10.3
384-1600	TNKK9036W	¥39,806	¥43,000	40	900 x 360 x 615	20	20	1	14.1

Inside wagon with doors

- Features** • Inside wagon with doors (with key).
Specs • With shelf board x 1

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Load Capacity (kg/piece)	W x D x H (mm)	Caster Diameter (mm)	Shelf Board Pitch (mm)	SPQ (piece)	Weight (kg)
384-1588	TNKS036W	¥36,103	¥39,000	40	500 x 360 x 600	50	20	1	15.3

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO NAKAYAMA CORPORATION

KOYO **KOYO**

"Free Box"



- Features** • Easy-to-move storage cabinet with casters, equipped with handles on both sides.
• With large name card holders that can display stored items clearly.
• Being spacious with a depth of 350mm, is useful for multiple purposes ranging from organizing files, managing equipment to storing luggage.
Specs • Equal Load Capacity: 20kg/Stage
Materials • Main Body: Steel
• Caster: Resin
Origin • Japan



IC-42 (files sold separately)




IC-40 (fee shelf x 2)




When the door is open (stored items sold separately) IC-43 (files sold separately)




IC-41 (fee shelf x 3) When the door is open (stored items sold separately)




1 box Inside Dimension



1 box Inside Dimension



1 box Inside Dimension



1 box Inside Dimension

Order Unit: 1 Piece | Factory direct | No freight charge | Excluding remote islands

KOYO STEEL Co.Ltd.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Load Capacity (kg/piece)	W x D x H (mm)	Caster Diameter (mm)	SPQ (piece)	Weight (kg)
★458-7375	IC-42	¥29,376	¥27,200	80	400 x 350 x 830	50	1	12.0
★458-7359	IC-40	¥33,264	¥30,800	80	400 x 350 x 830	50	1	15.0
★458-7383	IC-43	¥40,176	¥37,200	80	450 x 350 x 1188	50	1	18.5
★458-7367	IC-41	¥41,256	¥38,200	80	450 x 350 x 1188	50	1	22.0

Contact us: 026-274-0808 <http://www.koyo-steel.co.jp/>