

The number next to the logo mark indicates items in stock for each brand.



Stock 38,650 Items

Parts Box



- Features**
- Made of all steel. There is no worry of leakage of liquid such as water, oil etc. due to seamless single-sheet drawing.
 - Surface galvanized steel sheet is excellent in anti-rust effect.
- Materials**
- Steel (surface treatment: galvanized finishing)
- Origin**
- Japan



K-2

Order Unit: 1 Piece

(Price revision date: Jan, 2015) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Capacity (L)	Outer Dimension (mm) W x D x H	Effective Inner Dimension (mm) W x D x H	SPQ (piece)	Weight (kg)
507-2000	KA-4	¥1,102	¥1,190	5.0	510 x 320 x 45	417 x 266 x 43	10	1.3
507-1992	KA-2	¥1,990	¥2,150	6.0	595 x 360 x 45	488 x 304 x 43	10	1.8
507-1984	K-10	¥787	¥850	3.5	301 x 220 x 92	210 x 161 x 90	20	0.6
507-1976	K-9	¥879	¥950	5.2	352 x 240 x 96	257 x 176 x 94	20	0.8
507-1968	K-8	¥990	¥1,070	6.9	405 x 263 x 96	307 x 201 x 94	20	1.1
507-1950	K-7	¥1,138	¥1,230	7.7	465 x 265 x 96	370 x 201 x 94	20	1.5
507-1941	K-5	¥1,342	¥1,450	12.0	470 x 320 x 120	360 x 245 x 118	10	1.6
507-1933	K-4	¥1,379	¥1,490	14.0	510 x 320 x 120	395 x 242 x 118	10	2.0
507-1925	K-2	¥2,582	¥2,790	17.5	595 x 360 x 115	470 x 280 x 113	10	2.7

Contact us: 0120-509-849 <http://www.orange-book.com/>

Example of Stacking Storage



When not in use, keep it in piles



Stock 38,650 Items

Parts Box



- Features**
- Made of all steel. There is no worry of leakage of liquid such as water, oil etc. due to seamless single-sheet drawing.
 - We added a color to make parts management easy.
- Materials**
- Steel (surface treatment: baked coating)
- Origin**
- Japan




K-5:B

Order Unit: 1 Piece

(Price revision date: Jan, 2015) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Options (Color)	Price (per piece)	MSRP (per piece)	Capacity (L)	Outer Dimension (mm) W x D x H	Effective Inner Dimension (mm) W x D x H	SPQ (piece)	Weight (kg)
507-2182	KA-4	B	¥1,454	¥1,570	5.0	510 x 320 x 45	417 x 266 x 43	10	1.3
507-2174	KA-4	R	¥1,454	¥1,570	5.0	510 x 320 x 45	417 x 266 x 43	10	1.3
507-2166	KA-2	B	¥2,453	¥2,650	6.0	595 x 360 x 45	488 x 304 x 43	10	1.8
507-2158	KA-2	R	¥2,453	¥2,650	6.0	595 x 360 x 45	488 x 304 x 43	10	1.8
507-2140	K-10	B	¥1,203	¥1,300	3.5	301 x 220 x 92	210 x 161 x 90	20	0.6
507-2131	K-10	R	¥1,203	¥1,300	3.5	301 x 220 x 92	210 x 161 x 90	20	0.6
507-2123	K-9	B	¥1,296	¥1,400	5.2	352 x 240 x 96	257 x 176 x 94	20	0.8
507-2115	K-9	R	¥1,296	¥1,400	5.2	352 x 240 x 96	257 x 176 x 94	20	0.8
507-2107	K-8	B	¥1,416	¥1,530	6.9	405 x 263 x 96	307 x 201 x 94	20	1.1
507-2093	K-8	R	¥1,416	¥1,530	6.9	405 x 263 x 96	307 x 201 x 94	20	1.1
507-2085	K-7	B	¥1,620	¥1,750	7.7	465 x 265 x 96	370 x 201 x 94	20	1.5
507-2077	K-7	R	¥1,620	¥1,750	7.7	465 x 265 x 96	370 x 201 x 94	20	1.5
507-2069	K-5	B	¥1,833	¥1,980	12.0	470 x 320 x 120	360 x 245 x 118	10	1.6
507-2051	K-5	R	¥1,833	¥1,980	12.0	470 x 320 x 120	360 x 245 x 118	10	1.6
507-2042	K-4	B	¥1,833	¥1,980	14.0	510 x 320 x 120	395 x 242 x 118	10	2.0
507-2034	K-4	R	¥1,833	¥1,980	14.0	510 x 320 x 120	395 x 242 x 118	10	2.0
507-2026	K-2	B	¥3,444	¥3,720	17.5	595 x 360 x 115	470 x 280 x 113	10	2.7
507-2018	K-2	R	¥3,444	¥3,720	17.5	595 x 360 x 115	470 x 280 x 113	10	2.7

Contact us: 0120-509-849 <http://www.orange-book.com/>



Stock 38,650 Items

Parts Box



- Features**
- Surface galvanized steel sheet is excellent in anti-rust effect.
 - When putting parts, tilt the handle inward. Even when stacked, the parts will not be damaged. When it is empty, it is not bulky since taper is attached to the main body when the handle is tilted to the outside.
- Materials**
- Steel (surface treatment: galvanized finishing)
- Origin**
- Japan



M-4

Order Unit: 1 Piece

(Price revision date: Jan, 2015) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Capacity (L)	Outer Dimension (mm) W x D x H	Effective Inner Dimension (mm) W x D x H	SPQ (piece)	Weight (kg)
507-2221	M-8	¥1,537	¥1,660	6.9	367 x 277 x 96	307 x 201 x 94	20	1.4
507-2212	M-7	¥1,638	¥1,770	7.7	433 x 277 x 96	370 x 201 x 94	20	2.0
507-2204	M-5	¥1,861	¥2,010	12.0	430 x 337 x 120	360 x 245 x 118	10	2.1
507-2191	M-4	¥2,102	¥2,270	14.0	467 x 337 x 120	395 x 242 x 118	10	2.3

Contact us: 0120-509-849 <http://www.orange-book.com/>