

Total 78 models

Unit (mm)

Model Number	Radius of Ball Nose R	Length of Cut ℓ	Shank Taper Angle β	Overall Length L	Shank Diameter ϕd	Suggested Retail Price ¥
CSEB 1001-0020-6	R0.05	0.2	11°	50	6	13,320
CSEB 2001-0010	R0.05	0.1	11°	50	4	12,120
CSEB 2002-0020-6	R0.1	0.2	11°	50	6	9,840
CSEB 2002-0030		0.3		50	4	8,520
CSEB 2003-0030	R0.15	0.3	11°	50	4	6,960
CSEB 2003-0030-6		0.3		50	6	8,400
CSEB 2003-0045		0.45		50	4	6,960
CSEB 2004-0040	R0.2	0.4	11°	50	4	4,680
CSEB 2004-0040-6		0.4		50	6	6,120
CSEB 2004-0060		0.6		50	4	4,680
CSEB 2005-0050	R0.25	0.5	11°	50	4	4,320
CSEB 2005-0050-6		0.5		50	6	5,760
CSEB 2005-0075		0.75		50	4	4,320
CSEB 2006-0060	R0.3	0.6	11°	50	4	4,200
CSEB 2006-0060-6		0.6		50	6	5,520
CSEB 2006-0090		0.9		50	4	4,200
CSEB 2007-0100	R0.35	1	11°	50	4	8,000
CSEB 2008-0080	R0.4	0.8	11°	50	4	4,200
CSEB 2008-0080-6		0.8		50	6	5,520
CSEB 2008-0120		1.2		50	4	4,200
CSEB 2009-0130	R0.45	1.3	11°	50	4	8,000
CSEB 2010-0100	R0.5	1	11°	50	4	3,840
CSEB 2010-0100-6		1		50	6	5,160
CSEB 2010-0150		1.5		50	4	3,840
CSEB 2010-0250		2.5		50	4	3,840
CSEB 2011-0160	R0.55	1.6	11°	50	4	9,280
CSEB 2012-0180	R0.6	1.8	11°	50	4	5,400
CSEB 2013-0190	R0.65	1.9	11°	50	4	9,280
CSEB 2014-0210	R0.7	2.1	11°	50	4	5,400
CSEB 2015-0150	R0.75	1.5	11°	50	4	4,680
CSEB 2015-0150-6		1.5		50	6	6,000
CSEB 2015-0200		2		50	4	4,680
CSEB 2015-0225		2.25		50	4	4,680
CSEB 2015-0400		4		50	4	4,680
CSEB 2016-0240	R0.8	2.4	11°	50	4	5,400
CSEB 2017-0250	R0.85	2.5	11°	50	4	9,280
CSEB 2018-0270	R0.9	2.7	11°	50	4	8,000
CSEB 2019-0280	R0.95	2.8	11°	50	4	9,280
CSEB 2020-0200	R1	2	11°	50	4	3,480
CSEB 2020-0200-6		2		60	6	4,680
CSEB 2020-0300		3		60	4	3,480
CSEB 2020-0600		6		60	4	3,480
CSEB 2025-0250	R1.25	2.5	11°	50	4	5,950
CSEB 2025-0250-6		2.5		60	6	7,200
CSEB 2025-0375		3.75		50	4	5,950
CSEB 2025-0600	R1.5	6	11°	60	4	5,950
CSEB 2030-0300		3		50	6	4,200
CSEB 2030-0450		4.5		70	6	4,200
CSEB 2030-0800	R1.75	8	11°	70	6	4,200
CSEB 2035-0520		5.2		70	6	7,800
CSEB 2040-0400	R2	4	11°	50	6	4,800
CSEB 2040-0600-4		6	—	70	4	4,300
CSEB 2040-0600		6	11°	70	6	4,800
CSEB 2040-0800		8	11°	70	6	4,800

φ3mm Shank
V SeriesUDC-PCD
SeriesCBN
Series

Square

Square
Long Neck
Square

Radius

Radius
Long Neck
Radius
Taper Neck
Radius

Ball

Ball / Long
Shank Ball
Long Neck
Ball
Taper Neck
Ball

Taper

Taper

Barrel

Barrel

Spiral

Spiral
V Cutter

Drill

Drill

Technical Data

Technical Data

Next Page →