

3GTプーリ寸法表

下表は、標準在庫プーリ・受注生産プーリをご検討いただく際の参考寸法です。表以外の歯数・寸法のプーリも製作いたします。当社までお問い合わせください。

単位 mm

歯数	PD	OD	C(FID)	FOD	B	H	フランジ呼称
10	9.55	8.79	6.0	13	3	-	FA(S)10013006
11	10.50	9.74	7.0	14	3	-	FA(S)10014007
12	11.46	10.70	7.0	15	3	-	FA(S)10015007
13	12.41	11.65	8.0	16	4	-	FA(S)10016008
14	13.37	12.61	9.0	17	4	-	FA(S)10017009
15	14.32	13.56	10.0	18	4	-	FA(S)10018010
16	15.28	14.52	11.0	19	4	9	FA(S)10019011
17	16.23	15.47	12.0	20	5	10	FA(S)10020012
18	17.19	16.43	12.0	21	5	10	FA(S)10021012
19	18.14	17.38	13.0	22	5	10	FA(S)10022013
20	19.10	18.34	14.0	23	5	10	FA(S)10023014
21	20.05	19.29	15.0	24	5	11	FA(S)10024015
22	21.01	20.25	16.0	24	6	12	FA(S)10024016
23	21.96	21.20	17.0	25	6	13	FA(S)10025017
24	22.92	22.16	18.0	26	6	14	FA(S)10026018
25	23.87	23.11	18.0	27	6	14	FA(S)10027018
26	24.83	24.07	19.0	28	6	15	FA(S)10028019
27	25.78	25.02	20.0	29	6	16	FA(S)10029020
28	26.74	25.98	21.0	30	6	17	FA(S)10030021
29	27.69	26.93	22.0	31	6	18	FA(S)10031022
30	28.65	27.89	23.0	32	6	19	FA(S)10032023
31	29.60	28.84	24.0	33	6	20	FA(S)10033024
32	30.56	29.80	25.0	34	6	20	FA(S)10034025
33	31.51	30.75	26.0	35	8	22	FA(S)10035026
34	32.47	31.71	27.0	36	8	22	FA(S)10036027
35	33.42	32.66	28.0	37	8	24	FA(S)10037028
36	34.38	33.62	29.0	38	8	24	FA(S)10038029
37	35.33	34.57	30.0	39	8	26	FA(S)10039030
38	36.29	35.53	31.0	40	8	26	FA(S)10040031
39	37.24	36.48	32.0	41	8	28	FA(S)10041032
40	38.20	37.44	33.0	42	8	28	FA(S)10042033
41	39.15	38.39	34.0	43	8	30	FA(S)12043034
42	40.11	39.35	34.0	44	8	30	FA(S)10044034
43	41.06	40.30	35.0	45	10	30	FA(S)12045035
44	42.02	41.25	36.0	46	10	30	FA(S)10046036
45	42.97	42.21	37.0	47	10	32	FA(S)10047037
46	43.93	43.16	38.0	48	10	32	FA(S)10048038
47	44.88	44.12	39.0	49	10	32	FA(S)12049039
48	45.84	45.07	40.0	49	10	32	FA(S)10049040
49	46.79	46.03	41.0	50	10	32	FA(S)12050041
50	47.75	46.98	42.0	51	10	34	FA(S)10051042
51	48.70	47.94	43.0	52	10	34	-
52	49.66	48.89	44.0	53	10	34	FA(S)10053044
53	50.61	49.85	45.0	54	10	34	-
54	51.57	50.80	46.0	55	12	34	FA(S)10055046
55	52.52	51.76	47.0	56	12	34	FA(S)10056047
56	53.48	52.71	48.0	57	12	36	FA(S)10057048
57	54.43	53.67	49.0	58	12	36	-
58	55.39	54.62	50.0	59	12	36	FA(S)12059050
59	56.34	55.58	51.0	60	12	36	-
60	57.30	56.53	52.0	61	12	36	FA(S)10061052
61	58.25	57.49	53.0	62	12	36	-
62	59.21	58.44	54.0	63	12	36	FA(S)12063054
63	60.16	59.40	55.0	64	12	38	-
64	61.12	60.35	56.0	65	12	38	-
65	62.07	61.31	56.0	66	12	38	-
66	63.03	62.26	57.0	67	12	38	FA(S)12067057
67	63.98	63.22	58.0	68	12	38	-
68	64.94	64.17	59.0	69	12	38	FA(S)12069059
69	65.89	65.13	60.0	70	12	38	-
70	66.85	66.08	61.0	70	12	38	-
71	67.80	67.04	62.0	71	12	40	-
72	68.75	67.99	63.0	72	12	40	FA(S)10072063
73	69.71	68.95	64.0	73	12	40	-
74	70.66	69.90	65.0	74	12	40	-
75	71.62	70.86	66.0	75	12	40	-
76	72.57	71.81	67.0	76	12	40	-
77	73.53	72.77	68.0	77	12	40	-
78	74.48	73.72	69.0	78	12	40	-
79	75.44	74.68	70.0	79	12	42	-
80	76.39	75.63	71.0	80	12	42	-

歯数	PD	OD	C(FID)	FOD	B	H	フランジ呼称
81	77.35	76.59	72.0	81	12	42	-
82	78.30	77.54	73.0	82	12	42	-
83	79.26	78.50	74.0	83	12	42	-
84	80.21	79.45	75.0	84	12	42	FA(S)12084075
85	81.17	80.41	76.0	85	12	42	-
86	82.12	81.36	76.0	86	12	42	-
87	83.08	82.32	77.0	87	12	42	-
88	84.03	83.27	78.0	88	12	42	-
89	84.99	84.23	79.0	89	12	44	-
90	85.94	85.18	80.0	90	12	44	-
91	86.90	86.14	81.0	91	12	44	-
92	87.85	87.09	82.0	91	12	44	-
93	88.81	88.05	83.0	92	12	44	-
94	89.76	89.00	84.0	93	12	44	-
95	90.72	89.96	85.0	94	12	44	-
96	91.67	90.91	86.0	95	12	44	FA(S)12095086
97	92.63	91.87	87.0	96	12	44	-
98	93.58	92.82	88.0	97	12	44	-
99	94.54	93.78	89.0	98	12	44	-
100	95.49	94.73	90.0	99	12	44	-
101	96.45	95.69	90.0	100	12	46	-
102	97.40	96.64	91.0	101	12	46	-
103	98.36	97.60	92.0	102	12	46	-
104	99.31	98.55	93.0	103	12	46	-
105	100.27	99.51	94.0	104	12	46	-
106	101.22	100.46	95.0	105	16	46	-
107	102.18	101.42	96.0	106	16	46	-
108	103.13	102.37	97.0	107	16	46	-
109	104.09	103.33	98.0	108	16	46	-
110	105.04	104.28	99.0	109	16	46	-
111	106.00	105.24	100.0	110	16	46	-
112	106.95	106.19	101.0	111	16	48	-
113	107.91	107.15	102.0	112	16	48	-
114	108.86	108.10	103.0	113	16	48	-
115	109.82	109.05	104.0	113	16	48	-
116	110.77	110.01	105.0	114	16	48	-
117	111.73	110.96	106.0	115	16	48	-
118	112.68	111.92	107.0	116	16	48	-
119	113.64	112.87	108.0	117	16	48	-
120	114.59	113.83	109.0	118	16	48	-
121	115.55	114.78	110.0	119	16	48	-
122	116.50	115.74	111.0	120	16	48	-
123	117.46	116.69	112.0	121	16	48	-
124	118.41	117.65	113.0	122	16	48	-
125	119.37	118.60	114.0	123	16	48	-
126	120.32	119.56	115.0	124	16	50	-
127	121.28	120.51	116.0	125	16	50	-
128	122.23	121.47	117.0	126	16	50	-
129	123.19	122.42	118.0	127	16	50	-
130	124.14	123.38	118.0	128	16	50	-
131	125.10	124.33	119.0	129	16	50	-
132	126.05	125.29	120.0	130	16	50	-
133	127.01	126.24	121.0	131	16	50	-
134	127.96	127.20	122.0	132	16	50	-
135	128.92	128.15	123.0	133	16	50	-
136	129.87	129.11	124.0	134	16	50	-
137	130.83	130.06	125.0	134	16	50	-
138	131.78	131.02	126.0	135	16	50	-
139	132.74	131.97	127.0	136	16	50	-
140	133.69	132.93	128.0	137	16	50	-
141	134.65	133.88	129.0	138	16	52	-
142	135.60	134.84	130.0	139	16	52	-
143	136.55	135.79	131.0	140	16	52	-
144	137.51	136.75	132.0	141	16	52	-
145	138.46	137.70	133.0	142	16	52	-
146	139.42	138.66	134.0	143	16	52	-
147	140.37	139.61	135.0	144	16	52	-
148	141.33	140.57	136.0	145	16	52	-
149	142.28	141.52	137.0	146	16	52	-
150	143.24	142.48	138.0	147	16	52	-

□ は標準在庫プーリもご用意しております。形状については、118ページをご参照ください。
標準在庫プーリのB寸法は、下穴寸法を記載しております。