

3Mプーリー寸法表

下表は、標準在庫プーリー・受注生産プーリーをご検討いただく際の参考寸法です。表以外の歯数・寸法のプーリーも製作いたします。当社までお問い合わせください。

単位 mm

歯数	PD	OD	C(FID)	B	H	M	FOD	フランジ呼称
10	9.55	8.79	6.0	3	-	-	13	FS(A)10013006
11	10.50	9.74	7.0	3	-	-	14	FS(A)10014007
12	11.46	10.70	7.0	3	-	-	15	FS(A)10015007
13	12.41	11.65	8.0	4	-	-	16	FS(A)10016008
14	13.37	12.61	9.0	4	-	-	17	FS(A)10017009
15	14.32	13.56	10.0	4	-	-	18	FS(A)10018010
16	15.28	14.52	11.0	4	9	-	19	FS(A)10019011
17	16.23	15.47	12.0	5	10	-	20	FS(A)10020012
18	17.19	16.43	12.0	5	10	-	21	FS(A)10021012
19	18.14	17.38	13.0	5	10	-	22	FS(A)10022013
20	19.10	18.34	14.0	5	10	-	23	FS(A)10023014
21	20.05	19.29	15.0	5	11	-	24	FS(A)10024015
22	21.01	20.25	16.0	6	12	-	24	FS(A)10024016
23	21.96	21.20	17.0	6	13	-	25	FS(A)10025017
24	22.92	22.16	18.0	6	14	-	26	FS(A)10026018
25	23.87	23.11	18.0	6	14	-	27	FS(A)10027018
26	24.83	24.07	19.0	6	15	-	28	FS(A)10028019
27	25.78	25.02	20.0	6	16	-	29	FS(A)10029020
28	26.74	25.98	21.0	6	17	-	30	FS(A)10030021
29	27.69	26.93	22.0	6	18	-	31	FS(A)10031022
30	28.65	27.89	23.0	6	19	-	32	FS(A)10032023
31	29.60	28.84	24.0	6	20	-	33	FS(A)10033024
32	30.56	29.80	25.0	6	20	-	34	FS(A)10034025
33	31.51	30.75	26.0	8	22	-	35	FS(A)10035026
34	32.47	31.71	27.0	8	22	-	36	FS(A)10036027
35	33.42	32.66	28.0	8	24	-	37	FS(A)10037028
36	34.38	33.62	29.0	8	24	-	38	FS(A)10038029
37	35.33	34.57	30.0	8	26	-	39	FS(A)10039030
38	36.29	35.53	31.0	8	26	-	40	FS(A)10040031
39	37.24	36.48	32.0	8	28	-	41	FS(A)10041032
40	38.20	37.44	33.0	8	28	-	42	FS(A)10042033
41	39.15	38.39	34.0	8	30	-	43	FS(A)12043034
42	40.11	39.35	34.0	8	30	-	44	FS(A)10044034
43	41.06	40.30	35.0	10	30	-	45	FS(A)12045035
44	42.02	41.25	36.0	10	30	-	46	FS(A)10046036
45	42.97	42.21	37.0	10	32	-	47	FS(A)10047037
46	43.93	43.16	38.0	10	32	-	48	FS(A)10048038
47	44.88	44.12	39.0	10	32	-	49	FS(A)12049039
48	45.84	45.07	40.0	10	32	-	49	FS(A)10049040
49	46.79	46.03	41.0	10	32	-	50	FS(A)12050041
50	47.75	46.98	42.0	10	34	-	51	FS(A)10051042
51	48.70	47.94	43.0	10	34	-	52	-
52	49.66	48.89	44.0	10	34	-	53	FS(A)10053044
53	50.61	49.85	45.0	10	34	-	54	-
54	51.57	50.80	46.0	12	34	-	55	FS(A)10055046
55	52.52	51.76	47.0	12	34	-	56	FS(A)10056047
56	53.48	52.71	48.0	12	36	-	57	FS(A)10057048
57	54.43	53.67	49.0	12	36	-	58	-
58	55.39	54.62	50.0	12	36	-	59	FS(A)12059050
59	56.34	55.58	51.0	12	36	-	60	-
60	57.30	56.53	52.0	12	36	-	61	FS(A)10061052
61	58.25	57.49	53.0	12	36	-	62	-
62	59.21	58.44	54.0	12	36	-	63	FS(A)12063054
63	60.16	59.40	55.0	12	38	-	64	-
64	61.12	60.35	56.0	12	38	-	65	-
65	62.07	61.31	56.0	12	38	-	66	-
66	63.03	62.26	57.0	12	38	-	67	FS(A)12067057
67	63.98	63.22	58.0	12	38	-	68	-
68	64.94	64.17	59.0	12	38	-	69	FS(A)12069059
69	65.89	65.13	60.0	12	38	-	70	-
70	66.85	66.08	61.0	12	38	-	70	-
71	67.80	67.04	62.0	12	40	-	71	-
72	68.75	67.99	63.0	12	40	-	72	FS(A)10072063
73	69.71	68.95	64.0	12	40	-	73	-
74	70.66	69.90	65.0	12	40	-	74	-
75	71.62	70.86	66.0	12	40	-	75	-
76	72.57	71.81	67.0	12	40	-	76	-
77	73.53	72.77	68.0	12	40	-	77	-
78	74.48	73.72	69.0	12	40	-	78	-
79	75.44	74.68	70.0	12	42	-	79	-
80	76.39	75.63	71.0	12	42	-	80	-

歯数	PD	OD	C(FID)	B	H	M	FOD	フランジ呼称
81	77.35	76.59	72.0	12	42	-	81	-
82	78.30	77.54	73.0	12	42	-	82	-
83	79.26	78.50	74.0	12	42	-	83	-
84	80.21	79.45	75.0	12	42	-	84	FS(A)12084075
85	81.17	80.41	76.0	12	42	-	85	-
86	82.12	81.36	76.0	12	42	-	86	-
87	83.08	82.32	77.0	12	42	-	87	-
88	84.03	83.27	78.0	12	42	-	88	-
89	84.99	84.23	79.0	12	44	-	89	-
90	85.94	85.18	80.0	12	44	-	90	-
91	86.90	86.14	81.0	12	44	-	91	-
92	87.85	87.09	82.0	12	44	-	91	-
93	88.81	88.05	83.0	12	44	-	92	-
94	89.76	89.00	84.0	12	44	-	93	-
95	90.72	89.96	85.0	12	44	-	94	-
96	91.67	90.91	86.0	12	44	-	95	FS(A)12095086
97	92.63	91.87	87.0	12	44	-	96	-
98	93.58	92.82	88.0	12	44	-	97	-
99	94.54	93.78	89.0	12	44	-	98	-
100	95.49	94.73	90.0	12	44	80	99	-
101	96.45	95.69	90.0	12	46	80	100	-
102	97.40	96.64	91.0	12	46	81	101	-
103	98.36	97.60	92.0	12	46	82	102	-
104	99.31	98.55	93.0	12	46	83	103	-
105	100.27	99.51	94.0	12	46	84	104	-
106	101.22	100.46	95.0	16	46	85	105	-
107	102.18	101.42	96.0	16	46	86	106	-
108	103.13	102.37	97.0	16	46	87	107	-
109	104.09	103.33	98.0	16	46	88	108	-
110	105.04	104.28	99.0	16	46	89	109	-
111	106.00	105.24	100.0	16	46	90	110	-
112	106.95	106.19	101.0	16	48	91	111	-
113	107.91	107.15	102.0	16	48	92	112	-
114	108.86	108.10	103.0	16	48	93	113	-
115	109.82	109.05	104.0	16	48	94	113	-
116	110.77	110.01	105.0	16	48	95	114	-
117	111.73	110.96	106.0	16	48	96	115	-
118	112.68	111.92	107.0	16	48	97	116	-
119	113.64	112.87	108.0	16	48	98	117	-
120	114.59	113.83	109.0	16	48	99	118	-
121	115.55	114.78	110.0	16	48	100	119	-
122	116.50	115.74	111.0	16	48	101	120	-
123	117.46	116.69	112.0	16	48	102	121	-
124	118.41	117.65	113.0	16	48	103	122	-
125	119.37	118.60	114.0	16	48	104	123	-
126	120.32	119.56	115.0	16	50	105	124	-
127	121.28	120.51	116.0	16	50	106	125	-
128	122.23	121.47	117.0	16	50	107	126	-
129	123.19	122.42	118.0	16	50	108	127	-
130	124.14	123.38	118.0	16	50	108	128	-
131	125.10	124.33	119.0	16	50	109	129	-
132	126.05	125.29	120.0	16	50	110	130	-
133	127.01	126.24	121.0	16	50	111	131	-
134	127.96	127.20	122.0	16	50	112	132	-
135	128.92	128.15	123.0	16	50	113	133	-
136	129.87	129.11	124.0	16	50	114	134	-
137	130.83	130.06	125.0	16	50	115	134	-
138	131.78	131.02	126.0	16	50	116	135	-
139	132.74	131.97	127.0	16	50	117	136	-
140	133.69	132.93	128.0	16	50	118	137	-
141	134.65	133.88	129.0	16	52	119	138	-
142	135.60	134.84	130.0	16	52	120	139	-
143	136.55	135.79	131.0	16	52	121	140	-
144	137.51	136.75	132.0	16	52	122	141	-
145	138.46	137.70	133.0	16	52	123	142	-
146	139.42	138.66	134.0	16	52	124	143	-
147	140.37	139.61	135.0	16	52	125	144	-
148	141.33	140.57	136.0	16	52	126	145	-
149	142.28	141.52	137.0	16	52	127	146	-
150	143.24	142.48	138.0	16	52	128	147	-

は標準在庫プーリーもご用意しております。形状については、124ページをご参照ください。