

## 5Mプーリ寸法表

下表は、標準在庫プーリ・受注生産プーリをご検討いただく際の参考寸法です。表以外の歯数・寸法のプーリも製作いたします。当社までお問い合わせください。

単位 mm

歯数	PD	OD	C(FID)	B	H	M	FOD	フランジ呼称
14	22.28	21.14	16.0	6	12	-	26	FS(A)10026016
15	23.87	22.73	17.0	6	13	-	27	FS(A)10027017
16	25.46	24.32	19.0	6	15	-	29	FS(A)10029019
17	27.06	25.91	20.0	6	16	-	31	FS(A)10031020
18	28.65	27.50	22.0	6	18	-	32	FS(A)10032022
19	30.24	29.10	23.0	6	19	-	34	FS(A)10034023
20	31.83	30.69	24.0	8	20	-	35	FS(A)10035024
21	33.42	32.28	26.0	8	22	-	37	FS(A)10037026
22	35.01	33.87	27.0	8	22	-	39	FS(A)10039027
23	36.61	35.46	29.0	8	24	-	40	FS(A)10040029
24	38.20	37.05	30.0	8	26	-	42	FS(A)10042030
25	39.79	38.65	32.0	8	28	-	43	FS(A)10043032
26	41.38	40.24	33.0	10	28	-	45	FS(A)10045033
27	42.97	41.83	34.0	10	30	-	47	FS(A)10047034
28	44.56	43.42	36.0	10	30	-	48	FS(A)10048036
29	46.15	45.01	38.0	10	32	-	50	FS(A)10050038
30	47.75	46.60	39.0	10	32	-	51	FS(A)10051039
31	49.34	48.20	41.0	10	34	-	53	FS(A)10053041
32	50.93	49.79	42.0	10	34	-	55	FS(A)10055042
33	52.52	51.38	44.0	12	36	-	56	FS(A)10056044
34	54.11	52.97	46.0	12	36	-	58	FS(A)10058046
35	55.70	54.56	47.0	12	36	-	59	FS(A)10059047
36	57.30	56.15	49.0	12	38	-	61	FS(A)10061049
37	58.89	57.74	50.0	12	38	-	63	FS(A)10063050
38	60.48	59.34	52.0	12	38	-	64	FS(A)10064052
39	62.07	60.93	54.0	12	40	-	66	FS(A)10066054
40	63.66	62.52	55.0	12	40	-	67	FS(A)10067055
41	65.25	64.11	57.0	12	40	-	69	FS(A)12069057
42	66.85	65.70	58.0	12	42	-	71	FS(A)10071058
43	68.44	67.29	60.0	12	42	-	72	FS(A)12072060
44	70.03	68.89	62.0	12	42	-	74	FS(A)10074062
45	71.62	70.48	63.0	12	44	-	75	FS(A)10075063
46	73.21	72.07	65.0	12	44	-	77	FS(A)10077065
47	74.80	73.66	66.0	12	44	-	79	FS(A)12079066
48	76.39	75.25	68.0	12	46	-	80	FS(A)10080068
49	77.99	76.84	69.0	12	46	-	82	FS(A)12082069
50	79.58	78.43	71.0	12	46	-	83	FS(A)10083071
51	81.17	80.03	73.0	12	46	-	85	-
52	82.76	81.62	74.0	12	48	-	86	FS(A)10086074
53	84.35	83.21	76.0	12	48	-	88	-
54	85.94	84.80	77.0	12	48	-	90	FS(A)10090077
55	87.54	86.39	79.0	12	48	-	91	-
56	89.13	87.98	81.0	12	50	-	93	FS(A)10093081
57	90.72	89.58	82.0	12	50	-	94	-
58	92.31	91.17	84.0	12	50	-	96	FS(A)12096084
59	93.90	92.76	85.0	12	50	-	98	-
60	95.49	94.35	87.0	12	52	-	99	FS(A)12099087
61	97.08	95.94	89.0	12	52	-	101	-
62	98.68	97.53	90.0	12	52	-	102	FS(A)12102090
63	100.27	99.12	92.0	12	52	-	104	-
64	101.86	100.72	93.0	16	54	-	106	FS(A)12106093
65	103.45	102.31	95.0	16	54	-	107	-
66	105.04	103.90	96.0	16	54	-	109	FS(A)12109096
67	106.63	105.49	98.0	16	54	-	110	-
68	108.23	107.08	100.0	16	56	-	112	FS(A)12112100
69	109.82	108.67	101.0	16	56	-	114	-
70	111.41	110.27	103.0	16	56	90	115	-
71	113.00	111.86	104.0	16	56	91	117	-
72	114.59	113.45	106.0	16	56	93	118	FS(A)12118106
73	116.18	115.04	108.0	16	58	95	120	-
74	117.77	116.63	109.0	16	58	96	122	-
75	119.37	118.22	111.0	16	58	98	123	-
76	120.96	119.81	112.0	16	58	99	125	-
77	122.55	121.41	114.0	16	58	101	126	-
78	124.14	123.00	116.0	16	60	103	128	-
79	125.73	124.59	117.0	16	60	104	129	-
80	127.32	126.18	119.0	16	60	106	131	-
81	128.92	127.77	120.0	16	60	107	133	-
82	130.51	129.36	122.0	16	60	109	134	-

歯数	PD	OD	C(FID)	B	H	M	FOD	フランジ呼称
83	132.10	130.96	124.0	16	62	111	136	-
84	133.69	132.55	125.0	16	62	112	137	FS(A)12137125
85	135.28	134.14	127.0	16	62	114	139	-
86	136.87	135.73	128.0	16	62	115	141	-
87	138.46	137.32	130.0	16	62	117	142	-
88	140.06	138.91	132.0	16	64	119	144	-
89	141.65	140.50	133.0	16	64	120	145	-
90	143.24	142.10	135.0	16	64	122	147	-
91	144.83	143.69	136.0	16	64	123	149	-
92	146.42	145.28	138.0	16	64	125	150	-
93	148.01	146.87	139.0	16	64	126	152	-
94	149.61	148.46	141.0	16	66	128	153	-
95	151.20	150.05	143.0	16	66	130	155	-
96	152.79	151.65	144.0	16	66	131	157	FS(A)12157144
97	154.38	153.24	146.0	16	66	133	158	-
98	155.97	154.83	147.0	16	66	134	160	-
99	157.56	156.42	149.0	16	66	136	161	-
100	159.15	158.01	151.0	16	68	138	163	-
101	160.75	159.60	152.0	16	68	139	165	-
102	162.34	161.20	154.0	16	68	141	166	-
103	163.93	162.79	155.0	16	68	142	168	-
104	165.52	164.38	157.0	16	68	144	169	-
105	167.11	165.97	158.0	16	68	145	171	-
106	168.70	167.56	160.0	16	70	147	172	-
107	170.30	169.15	162.0	16	70	149	174	-
108	171.89	170.74	163.0	16	70	150	176	-
109	173.48	172.34	165.0	16	70	152	177	-
110	175.07	173.93	166.0	16	70	153	179	-
111	176.66	175.52	168.0	16	70	155	180	-
112	178.25	177.11	170.0	16	70	157	182	-
113	179.85	178.70	171.0	16	72	158	184	-
114	181.44	180.29	173.0	16	72	160	185	-
115	183.03	181.89	174.0	16	72	161	187	-
116	184.62	183.48	176.0	16	72	163	188	-
117	186.21	185.07	178.0	16	72	165	190	-
118	187.80	186.66	179.0	16	72	166	192	-
119	189.39	188.25	181.0	16	72	168	193	-
120	190.99	189.84	182.0	16	74	169	195	-
121	192.58	191.43	184.0	16	74	171	196	-
122	194.17	193.03	186.0	16	74	173	198	-
123	195.76	194.62	187.0	16	74	174	200	-
124	197.35	196.21	189.0	16	74	176	201	-
125	198.94	197.80	190.0	16	74	177	203	-
126	200.54	199.39	192.0	16	74	179	204	-
127	202.13	200.98	193.0	20	76	180	206	-
128	203.72	202.58	195.0	20	76	182	207	-
129	205.31	204.17	197.0	20	76	184	209	-
130	206.90	205.76	198.0	20	76	185	211	-
131	208.49	207.35	200.0	20	76	187	212	-
132	210.08	208.94	201.0	20	76	188	214	-
133	211.68	210.53	203.0	20	76	190	215	-
134	213.27	212.12	205.0	20	76	192	217	-
135	214.86	213.72	206.0	20	78	193	219	-
136	216.45	215.31	208.0	20	78	195	220	-
137	218.04	216.90	209.0	20	78	196	222	-
138	219.63	218.49	211.0	20	78	198	223	-
139	221.23	220.08	213.0	20	78	200	225	-
140	222.82	221.67	214.0	20	78	201	227	-
141	224.41	223.27	216.0	20	78	203	228	-
142	226.00	224.86	217.0	20	78	204	230	-
143	227.59	226.45	219.0	20	80	206	231	-
144	229.18	228.04	221.0	20	80	208	233	-
145	230.77	229.63	222.0	20	80	209	235	-
146	232.37	231.22	224.0	20	80	211	236	-
147	233.96	232.81	225.0	20	80	212	238	-
148	235.55	234.41	227.0	20	80	214	239	-
149	237.14	236.00	229.0	20	80	216	241	-
150	238.73	237.59	230.0	20	80	217	242	-

は標準在庫プーリもご用意しております。形状については、126ページをご参照ください。