

## 8Mプーリ寸法表

下表は、標準在庫プーリ・受注生産プーリをご検討いただく際の参考寸法です。表以外の歯数・寸法のプーリも製作いたします。当社までお問い合わせください。

単位 mm

歯数	PD	OD	C(FID)	B	H	M	FOD	フランジ呼称
22	56.02	54.65	45.0	16	40	-	64	FS20064045
23	58.57	57.20	47.0	16	42	-	67	FS20067047
24	61.12	59.74	50.0	16	44	-	70	FS20070050
25	63.66	62.29	52.0	16	46	-	72	FS20072052
26	66.21	64.84	54.0	16	48	-	75	FS20075054
27	68.75	67.38	57.0	16	50	-	77	FS20077057
28	71.30	69.93	59.0	16	52	-	80	FS20080059
29	73.85	72.48	62.0	16	54	-	82	FS20082062
30	76.39	75.02	64.0	16	56	-	85	FS20085064
31	78.94	77.57	67.0	16	58	-	88	FS25088067
32	81.49	80.12	69.0	20	60	-	90	FS20090069
33	84.03	82.66	71.0	20	62	-	93	FS20093071
34	86.58	85.21	74.0	20	64	-	95	FS20095074
35	89.13	87.75	76.0	20	66	-	98	FS20098076
36	91.67	90.30	79.0	20	68	-	100	FS20100079
37	94.22	92.85	81.0	20	70	-	103	FS20103081
38	96.77	95.39	84.0	20	72	-	105	FS20105084
39	99.31	97.94	86.0	20	74	-	108	FS25108086
40	101.86	100.49	89.0	20	74	-	110	FS20110089
41	104.41	103.03	92.0	20	76	-	113	FS25113092
42	106.95	105.58	94.0	20	76	-	116	FS25116094
43	109.50	108.13	97.0	20	78	-	118	FS25118097
44	112.05	110.67	99.0	20	78	-	121	FS20121099
45	114.59	113.22	102.0	20	78	-	123	FS25123102
46	117.14	115.77	104.0	20	80	-	126	FS20126104
47	119.68	118.31	107.0	20	80	-	128	FS25128107
48	122.23	120.86	109.0	20	80	-	131	FS20131109
49	124.78	123.41	112.0	20	82	-	133	FS25133112
50	127.32	125.95	114.0	20	82	-	136	FS20136114
51	129.87	128.50	117.0	20	82	-	139	FS25139117
52	132.42	131.04	119.0	20	84	-	141	FS25141119
53	134.96	133.59	122.0	20	84	-	143	FS25143122
54	137.51	136.14	125.0	20	84	-	146	FS25146125
55	140.06	138.68	127.0	20	86	-	149	FS25149127
56	142.60	141.23	130.0	20	86	-	151	FS20151130
57	145.15	143.78	132.0	20	86	112	154	FS25154132
58	147.70	146.32	135.0	20	88	115	156	FS25156135
59	150.24	148.87	137.0	20	88	117	159	FS25159137
60	152.79	151.42	140.0	30	88	120	161	FS20161140
61	155.34	153.96	142.0	30	90	122	164	FS25164142
62	157.88	156.51	145.0	30	90	125	166	FS25166145
63	160.43	159.06	147.0	30	90	127	169	FS25169147
64	162.97	161.60	150.0	30	92	130	172	FS20172150
65	165.52	164.15	153.0	30	92	133	174	FS25174153
66	168.07	166.70	155.0	30	92	135	177	FS25177155
67	170.61	169.24	158.0	30	94	138	179	FS25179158
68	173.16	171.79	160.0	30	94	140	182	FS25182160
69	175.71	174.34	163.0	30	94	143	184	FS25184163
70	178.25	176.88	165.0	30	94	145	187	FS25187165
71	180.80	179.43	168.0	30	94	148	190	FS25190168

歯数	PD	OD	C(FID)	B	H	M	FOD	フランジ呼称
72	183.35	181.97	171.0	30	94	151	192	FS20192171
73	185.89	184.52	173.0	30	96	153	195	FS25195173
74	188.44	187.07	175.0	30	96	155	197	FS25197175
75	190.99	189.61	178.0	30	96	158	200	FS25200178
76	193.53	192.16	180.0	30	96	160	202	FS25202180
77	196.08	194.71	183.0	30	96	163	205	FS25205183
78	198.63	197.25	186.0	30	96	166	207	FS25207186
79	201.17	199.80	188.0	30	98	168	210	FS25210188
80	203.72	202.35	191.0	30	98	171	212	FS25212191
81	206.26	204.89	193.0	30	98	173	215	FS25215193
82	208.81	207.44	196.0	30	98	176	218	FS25218196
83	211.36	209.99	198.0	30	98	178	220	FS25220198
84	213.90	212.53	201.0	30	98	181	223	FS25223201
85	216.45	215.08	203.0	30	100	183	225	FS25225203
86	219.00	217.63	206.0	30	100	186	228	FS25228206
87	221.54	220.17	208.0	30	100	188	230	FS25230208
88	224.09	222.72	211.0	30	100	191	233	FS25233211
89	226.64	225.26	214.0	30	100	194	235	FS25235214
90	229.18	227.81	216.0	30	100	196	238	FS25238216
91	231.73	230.36	219.0	30	102	199	240	-
92	234.28	232.90	221.0	30	102	201	243	-
93	236.82	235.45	224.0	30	102	204	246	-
94	239.37	238.00	226.0	30	102	206	248	-
95	241.92	240.54	229.0	30	102	209	251	-
96	244.46	243.09	231.0	30	102	211	253	FS25253231
97	247.01	245.64	234.0	30	104	214	256	-
98	249.55	248.18	236.0	30	104	216	258	-
99	252.10	250.73	239.0	40	104	219	261	-
100	254.65	253.28	242.0	40	104	222	263	-
101	257.19	255.82	244.0	40	104	224	266	-
102	259.74	258.37	247.0	40	104	227	268	-
103	262.29	260.92	249.0	40	106	229	271	-
104	264.83	263.46	252.0	40	106	232	274	-
105	267.38	266.01	254.0	40	106	234	276	-
106	269.93	268.55	257.0	40	106	237	279	-
107	272.47	271.10	259.0	40	106	239	281	-
108	275.02	273.65	262.0	40	106	242	284	-
109	277.57	276.19	264.0	40	108	244	286	-
110	280.11	278.74	267.0	40	108	247	289	-
111	282.66	281.29	270.0	40	108	250	291	-
112	285.21	283.83	272.0	40	108	252	294	FS25294272
113	287.75	286.38	275.0	40	108	255	296	-
114	290.30	288.93	277.0	40	108	257	299	-
115	292.85	291.47	280.0	40	110	260	302	-
116	295.39	294.02	282.0	40	110	262	304	-
117	297.94	296.57	285.0	40	110	265	307	-
118	300.48	299.11	287.0	40	110	267	309	-
119	303.03	301.66	290.0	50	110	270	312	-
120	305.58	304.21	292.0	50	110	272	314	-

□ は標準在庫プーリもご用意しております。形状については、128ページをご参照ください。  
標準在庫プーリのB寸法は、下穴寸法を記載しております。