

## XLプーリ寸法表

下表は、標準在庫プーリ・受注生産プーリをご検討いただく際の参考寸法です。表以外の歯数・寸法のプーリも製作いたします。当社までお問い合わせください。

単位 mm

歯数	PD	OD	C(FID)	B	H	FOD	フランジ呼称
10	16.17	15.66	12.5	5	10.5	24	FS10024013
11	17.79	17.28	12.5	5	10.5	24	FS10024013
12	19.40	18.90	15.0	5	13	25	FS10025015
13	21.02	20.51	17.5	6	14	28	FS10028018
14	22.64	22.13	17.5	6	15	28	FS10028018
15	24.26	23.75	20.0	6	16	30	FS10030020
16	25.87	25.36	20.0	6	17	32	FS10032020
17	27.49	26.98	22.5	7	18	33	FS10033023
18	29.11	28.60	25.0	7	20	35	FS10035025
19	30.72	30.22	25.0	8	22	35	FS10035025
20	32.34	31.83	27.5	8	24	40	FS10040028
21	33.96	33.45	27.5	8	24	40	FS10040028
22	35.57	35.07	31.0	8	26	45	FS10045031
23	37.19	36.68	31.0	8	26	45	FS10045031
24	38.81	38.30	31.0	8	26	45	FS10045031
25	40.43	39.92	36.0	8	26	48	FS10048036
26	42.04	41.53	36.0	10	28	48	FS10048036
27	43.66	43.15	36.0	10	28	52	FS10052036
28	45.28	44.77	41.0	10	28	55	FS10055041
29	46.89	46.39	41.0	10	28	55	FS10055041
30	48.51	48.00	41.0	10	30	55	FS10055041
31	50.13	49.62	46.0	10	30	58	FS10058046
32	51.74	51.24	46.0	10	30	58	FS10058046
33	53.36	52.85	46.0	10	30	61	FS10061046
34	54.98	54.47	46.0	10	30	61	FS10061046
35	56.60	56.09	51.0	10	30	67	FS10067051
36	58.21	57.70	51.0	10	30	67	FS10067051
37	59.83	59.32	51.0	10	30	67	FS10067051
38	61.45	60.94	56.0	10	32	70	FS10070056
39	63.06	62.56	56.0	10	32	70	FS10070056
40	64.68	64.17	56.0	10	32	70	FS10070056
41	66.30	65.79	61.0	10	32	76	FS10076061
42	67.91	67.41	61.0	10	32	76	FS10076061
43	69.53	69.02	61.0	10	32	76	FS10076061
44	71.15	70.64	61.0	10	32	76	FS10076061
45	72.77	72.26	66.0	10	32	83	FS10083066
46	74.38	73.87	66.0	10	32	83	FS10083066
47	76.00	75.49	66.0	10	32	83	FS10083066
48	77.62	77.11	71.0	12	34	83	FS10083071
49	79.23	78.73	71.0	12	34	88	-
50	80.85	80.34	71.0	12	34	88	-
51	82.47	81.96	75.0	12	34	95	-
52	84.08	83.58	75.0	12	34	95	-
53	85.70	85.19	75.0	12	34	95	-
54	87.32	86.81	80.0	12	34	99	-
55	88.94	88.43	80.0	12	34	99	-
56	90.55	90.04	80.0	12	36	99	-
57	92.17	91.66	80.0	12	36	99	-
58	93.79	93.28	85.0	12	36	103	-
59	95.40	94.90	85.0	12	36	103	-
60	97.02	96.51	90.0	12	36	111	-
61	98.64	98.13	90.0	12	36	111	-
62	100.25	99.75	90.0	12	36	111	-
63	101.87	101.36	90.0	12	38	111	-
64	103.49	102.98	95.0	12	38	115	-
65	105.11	104.60	95.0	12	38	115	-

歯数	PD	OD	C(FID)	B	H	FOD	フランジ呼称
66	106.72	106.21	95.0	12	38	115	-
67	108.34	107.83	100.0	12	38	119	-
68	109.96	109.45	100.0	12	38	119	-
69	111.57	111.07	100.0	12	38	119	-
70	113.19	112.68	100.0	12	38	119	-
71	114.81	114.30	105.0	12	38	123	-
72	116.43	115.92	105.0	12	38	123	-
73	118.04	117.53	105.0	12	38	127	-
74	119.66	119.15	110.0	12	40	131	-
75	121.28	120.77	110.0	16	40	131	-
76	122.89	122.39	110.0	16	40	131	-
77	124.51	124.00	115.0	16	40	135	-
78	126.13	125.62	115.0	16	40	135	-
79	127.74	127.24	115.0	16	40	135	-
80	129.36	128.85	120.0	16	44	140	-
81	130.98	130.47	120.0	16	44	140	-
82	132.60	132.09	120.0	16	44	140	-
83	134.21	133.70	125.0	16	44	144	-
84	135.83	135.32	125.0	16	44	144	-
85	137.45	136.94	125.0	16	44	144	-
86	139.06	138.56	125.0	16	44	148	-
87	140.68	140.17	125.0	16	44	148	-
88	142.30	141.79	125.0	16	44	148	-
89	143.91	143.41	130.0	16	48	152	-
90	145.53	145.02	130.0	16	48	152	-
91	147.15	146.64	135.0	16	48	156	-
92	148.77	148.26	135.0	16	48	156	-
93	150.38	149.87	135.0	16	48	156	-
94	152.00	151.49	140.0	16	52	160	-
95	153.62	153.11	140.0	16	52	160	-
96	155.23	154.73	140.0	16	52	160	-
97	156.85	156.34	140.0	16	52	164	-
98	158.47	157.96	140.0	16	52	164	-
99	160.08	159.58	140.0	16	52	164	-
100	161.70	161.19	145.0	16	52	168	-
101	163.32	162.81	145.0	16	52	168	-
102	164.94	164.43	150.0	16	58	172	-
103	166.55	166.04	150.0	16	58	172	-
104	168.17	167.66	155.0	16	58	176	-
105	169.79	169.28	155.0	16	58	176	-
106	171.40	170.90	155.0	16	58	180	-
107	173.02	172.51	155.0	16	58	180	-
108	174.64	174.13	155.0	16	58	180	-
109	176.25	175.75	160.0	16	62	184	-
110	177.87	177.36	160.0	16	62	184	-
111	179.49	178.98	160.0	16	62	184	-
112	181.11	180.60	160.0	16	62	184	-
113	182.72	182.21	160.0	16	62	184	-
114	184.34	183.83	170.0	16	66	192	-
115	185.96	185.45	170.0	16	66	192	-
116	187.57	187.07	170.0	16	66	196	-
117	189.19	188.68	170.0	16	66	196	-
118	190.81	190.30	170.0	16	66	196	-
119	192.42	191.92	175.0	16	72	200	-
120	194.04	193.53	175.0	16	72	200	-

□ は標準在庫プーリもご用意しております。形状については、134ページをご参照ください。  
標準在庫プーリのB寸法は、下穴寸法を記載しております。