


Male Connectors MCS MICRO

Pin spacing: 2.5 mm / 0.098 in.

0.08 ... 0.5 mm ²	28 ... 20 AWG
160 V/2.5 kV/2 6 A	150 V/4 A



$L = (\text{pole no.} + 1) \times \text{pin spacing}$

Pole No.	Item No.	Pack. Unit
Male connector, light gray		
2	733-202	200
3	733-203	200
4	733-204	200
5	733-205	100
6	733-206	100
7	733-207	100
8	733-208	100
9	733-209	100
10	733-210	100
12	733-212	50